# MM-TML (EX4,2)R C1 TR/BK - Label

0803979

https://www.phoenixcontact.com/us/products/0803979

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Label, Roll, unmarked, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, Number of individual labels: 1, roll length: 8 m, text field height: 4.2 mm, text field width: 8000 mm, The product is being prepared for compliance with the Cyber Resilience Act (CRA)

## Your advantages

- High-quality and solvent-resistant marking solution for industrial applications that is created by means of thermal transfer printing
- The material is cUL certified
- Easy and efficient material cartridge system: Includes both the material to be printed and the corresponding ink ribbon
- Thanks to the continuous format, a label of the appropriate length can be created flexibly for the relevant application
- Zack marker strips and flat zack marker strips can be marked subsequently with the TML marking foil
- The self-adhesive material in continuous format is particularly suitable for marking terminals without a marker groove

## Commercial data

| | |
|---|---|
| Item number | 0803979 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BG23 |
| Product key | BG211E |

| | |
|---|---|
| GTIN | 4055626212548 |
| Weight per piece (including packing) | 51.5 g |
| Weight per piece (excluding packing) | 50.6 g |
| Customs tariff number | 39173200 |
| Country of origin | CN |

# Technical data

## Notes

Note on application

| | |
|---|---|
| Note on application | As things stand now, we are preparing the product so that, as of December 11, 2027, it will comply with the requirements of the EU Cyber Resilience Act (CRA) based on the information currently available regarding the CRA. |

## Product properties

| | |
|---|---|
| Product type | Terminal marker |
| Product family | MM-TML |
| Special properties | The product is being prepared for compliance with the Cyber Resilience Act (CRA) |

Marking

| | |
|---|---|
| Number of individual labels | 1 |
| Number of individual labels per row | 1 |
| Slot type | flat |
| Identification technology | Thermal transfer |

## Dimensions

| | |
|---|---|
| Length of roll | 8.00 m |
| Height | 4.2 mm |
| Depth | 0.07 mm |

Text field

| | |
|---|---|
| Text field width | 8000 mm |
| Text field height | 4.2 mm |

## Material specifications

| | |
|---|---|
| Foil strength | 23 µm |
| Adhesive | Acrylic |
| Color (Label) | transparent |
| Color (Marking text) | black (RAL 9005) |
| Base element material | Polyester |
| Components | free from silicone, halogen, and cadmium |

## Environmental and real-life conditions

Ambient conditions

| | |
|---|---|
| Ambient temperature (operation) | -40 °C ... 125 °C |
| Recommended ambient temperature (storage/transport) | 21 °C |
| Recommended humidity (storage/transport) | 45 % ... 55 % (Storage in a dry and dark place in the original packaging is recommended) |

Test for substances that would hinder coating with paint or varnish

| | |
|---|---|
| Testing for paint wetting impairment substances (LABS-conformity) | VW PV 3.10.7:2005-02 |
| Result | Test passed |

UV resistance

| | |
|---|---|
| Specification | DIN EN ISO 4892-2:2021-11 (following) |
| Result | Test passed |
| Test duration | 96 h |
| Procedure | Artificial irradiation. |

Wipe resistance of inscriptions

| | |
|---|---|
| Specification | DIN EN 61010-1 (VDE 0411-1):2011-07 |
| | DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |
| Isopropanol (99%) [67-63-0] | Test passed |
| n-Hexane<br>[CAS No. 110-54-3] | Test passed |
| Water + Petroleum ether<br>[CAS No. 64742-82-1] | Test passed |

Testing in a condensation changing climate in the presence of sulfur dioxide

| | |
|---|---|
| Specification | DIN EN ISO 22479:2022-08 |
| Result | Test passed |
| Procedure | Method B |
| Cycles | 2 |

Salt spray test

| | |
|---|---|
| Specification | DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10 |
| Result | Test passed |

## Mounting

| | |
|---|---|
| Mounting type | adhesive |

## Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/0803979

**cULus Recognized**
Approval ID: MH48542

## Classifications

### ECLASS

| | |
|---|---|
| ECLASS-13.0 | 27281101 |
| ECLASS-15.0 | 27281101 |

### ETIM

| | |
|---|---|
| ETIM 10.0 | EC000761 |

### UNSPSC

| | |
|---|---|
| UNSPSC 21.0 | 39131500 |

## Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |

China RoHS

| | |
|---|---|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|---|---|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |

EF3.1 Climate Change

| | |
|---|---|
| CO2e kg | 0.913 kg CO2e |


Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com



Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com