

MM-TMT (EX9,5)R C1 WH/BK - Label

0803983

<https://www.phoenixcontact.com/us/products/0803983>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Label, Roll, white (RAL 9010), unmarked, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: latching, Number of individual labels: 1, roll length: 5.5 m, text field height: 9.5 mm, text field width: 5500 mm, The product is being prepared for compliance with the Cyber Resilience Act (CRA)

Your advantages

- High-quality and solvent-resistant marking solution for industrial applications that is created by means of thermal transfer printing
- The markers in continuous format are suitable for marking products with a tall and flat marker groove
- Easy and efficient material cartridge system: Includes both the material to be printed and the corresponding ink ribbon
- Thanks to the continuous format, a label of the appropriate length can be created flexibly for the relevant application



Commercial data

Item number	0803983
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG23
Product key	BG211E
GTIN	4055626212579
Weight per piece (including packing)	48.5 g

MM-TMT (EX9,5)R C1 WH/BK - Label



0803983

<https://www.phoenixcontact.com/us/products/0803983>

Weight per piece (excluding packing)	49.3 g
Customs tariff number	96121010
Country of origin	CN

Technical data

Notes

Note on application

Note on application	As things stand now, we are preparing the product so that, as of December 11, 2027, it will comply with the requirements of the EU Cyber Resilience Act (CRA) based on the information currently available regarding the CRA.
---------------------	---

Product properties

Product type	Terminal marker
Product family	MM-TMT
Special properties	The product is being prepared for compliance with the Cyber Resilience Act (CRA)

Marking

Number of individual labels	1
Number of individual labels per row	1
Slot type	high
Identification technology	Thermal transfer

Dimensions

Length of roll	5.50 m
Height	15.00 mm
Depth	0.13 mm

Text field

Text field width	5500 mm
Text field height	9.5 mm

Material specifications

Foil strength	125 µm
Color (Label)	white (RAL 9010)
Color (Marking text)	black (RAL 9005)
Base element material	Polyester
Components	free from silicone, halogen, and cadmium

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
Recommended ambient temperature (storage/transport)	-5 °C
Recommended humidity (storage/transport)	25 % ... 80 % (Storage in a dry and dark place in the original packaging is recommended)

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-	VW PV 3.10.7:2005-02
--	----------------------

MM-TMT (EX9,5)R C1 WH/BK - Label



0803983

<https://www.phoenixcontact.com/us/products/0803983>

conformity)	
Result	Test passed

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropanol (99%) [67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN EN ISO 22479:2022-08
Result	Test passed
Procedure	Method B
Cycles	2

Salt spray test

Specification	DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10
Result	Test passed

Mounting

Mounting type	latching
---------------	----------

MM-TMT (EX9,5)R C1 WH/BK - Label



0803983

<https://www.phoenixcontact.com/us/products/0803983>

Classifications

ECLASS

ECLASS-13.0	27281101
ECLASS-15.0	27281101

ETIM

ETIM 10.0	EC000761
-----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

MM-TMT (EX9,5)R C1 WH/BK - Label



0803983

<https://www.phoenixcontact.com/us/products/0803983>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.98 kg CO2e
---------	--------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com