

BMK 20X 8 WH - Fabric label sheet




0805470

<https://www.phoenixcontact.com/us/products/0805470>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Fabric label sheet, Sheet, white (RAL 9010), unmarked, can be labeled with: PLOTMARK, CMS-P1-PLOTTER, mounting type: adhesive, Number of individual labels: 270



Your advantages

- Available in various dimensions
- Self-adhesive labels for labeling by hand or with a plotter
- Secure adhesion even on curved or uneven surfaces as well as round corners
- The material file can be downloaded under the Phoenix Contact marking software under Downloads - "Software update - Marking".
- Labeling service: Phoenix Contact can custom-label all BMK ... markers according to your requirements

Commercial data

Item number	0805470
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	BG13
Product key	BG2414
GTIN	4017918153458
Weight per piece (including packing)	19.84 g
Weight per piece (excluding packing)	19.32 g
Customs tariff number	39199080
Country of origin	BE

BMK 20X 8 WH - Fabric label sheet



0805470

<https://www.phoenixcontact.com/us/products/0805470>

Technical data

Product properties

Product type	Device marker
--------------	---------------

Marking

Number of individual labels	270
Number of individual labels per row	9
Identification technology	Plotter

Dimensions

Width	20 mm
Length	8 mm

Material specifications

Foil strength	66 µm
Adhesive strength	27.9 µm
Adhesive	Acrylic
Color	white (RAL 9010)
Material	Polyester foil
Base element material	Polyester foil
Components	Silicone-free

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 80 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropanol (99%) [67-63-0]	Test passed

BMK 20X 8 WH - Fabric label sheet



0805470

<https://www.phoenixcontact.com/us/products/0805470>

n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1.0 S
Cycles	2

Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed
Test duration	96 h

Mounting

Mounting type	adhesive
---------------	----------

BMK 20X 8 WH - Fabric label sheet



0805470

<https://www.phoenixcontact.com/us/products/0805470>

Classifications

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

BMK 20X 8 WH - Fabric label sheet



0805470

<https://www.phoenixcontact.com/us/products/0805470>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
-----------------------------------------	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com