

GPE 60X30 WH/R - Engraving material



0815292

<https://www.phoenixcontact.com/us/products/0815292>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Engraving material, Sheet, white (RAL 9010), unmarked, can be labeled with: PLOTMARK, ENGRAVING UNIT, CMS-P1-PLOTTER, P1 ENGRAVING UNIT, mounting type: adhesive, Number of individual labels: 9, text field height: 30 mm, text field width: 60 mm

Your advantages

- Labeling service: Phoenix Contact can custom-label all GPE ... markers according to your requirements
- The adhesive foil used ensures good adhesive properties, even on uneven surfaces
- Two-layer material
- The label sheet consists of prefabricated, individual self-adhesive labels
- Can be engraved using the P1 ENGRAVING UNIT
- Can be labeled easily using the CMS-P1-PLOTTER

Commercial data

Item number	0815292
Packing unit	10 pc
Minimum order quantity	1 pc
Sales key	BG19
Product key	BG2415
GTIN	4046356081283
Weight per piece (including packing)	20 g
Weight per piece (excluding packing)	20 g
Customs tariff number	39203000
Country of origin	DE

GPE 60X30 WH/R - Engraving material



0815292

<https://www.phoenixcontact.com/us/products/0815292>

Technical data

Notes

General	Can be labeled with CMS
---------	-------------------------

Product properties

Product type	Device marker
--------------	---------------

Marking

Number of individual labels	9
Number of individual labels per row	3

Dimensions

Width	60.00 mm
Height	30.00 mm
Depth	0.85 mm

Text field

Text field width	60 mm
Text field height	30 mm

Material specifications

Adhesive strength	50 µm
Adhesive	Acrylic
Color	white (RAL 9010)
Material	TRANSPLY-ABS
Base element material	TRANSPLY-ABS
Components	free from silicone and halogen

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 85 °C
Recommended ambient temperature (storage/transport)	20 °C
Recommended humidity (storage/transport)	50 %

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Procedure	Artificial irradiation.

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
Isopropanol (99%) [67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed

GPE 60X30 WH/R - Engraving material



0815292

<https://www.phoenixcontact.com/us/products/0815292>

Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
---	-------------

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	adhesive
---------------	----------

GPE 60X30 WH/R - Engraving material



0815292

<https://www.phoenixcontact.com/us/products/0815292>

Classifications

ECLASS

ECLASS-13.0	27281103
ECLASS-15.0	27281103

ETIM

ETIM 10.0	EC001288
-----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

GPE 60X30 WH/R - Engraving material



0815292

<https://www.phoenixcontact.com/us/products/0815292>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com