ZB 20,3 CUS - Zack marker strip

0824948

https://www.phoenixcontact.com/us/products/0824948

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Zack marker strip, can be ordered: Strip, white (RAL 9010), labeled according to customer specifications, mounting type: latching, for terminal block width: 20.3 mm, Number of individual labels: 5, text field height: 20.25 mm, text field width: 10.5 mm

Commercial data

Item number	0824948
Packing unit	1 pc
Minimum order quantity	50 pc
Note	Made to order (non-returnable)
Sales key	BG24
Product key	BG8112
GTIN	4046356356350
Weight per piece (including packing)	2.537 g
Weight per piece (excluding packing)	2.537 g
Customs tariff number	49119900
Country of origin	DE

Technical data

Product properties

Product type	Terminal marker
Pitch	20.3 mm

Marking

Number of individual labels	5
Number of individual labels per row	5
Number of marker strips	5
Slot type	high

Dimensions

Width	20.25 mm
Height	10.50 mm
Depth	4.20 mm
Pitch	20.3 mm
Length	10.5 mm

Text field

Text field width	10.5 mm
Text field height	20.25 mm

Material specifications

Color	white (RAL 9010)
Material	PA
Flammability rating according to UL 94	V2
Base element material	PA
Components	free from silicone and halogen

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

Standards and regulations


Wipe resistance	DIN EN 61010-1 (VDE 0411-1)

Mounting

Mounting type	latching

Drawings

Schematic diagram



① Horizontal
② Vertical

Classifications

ECLASS

ECLASS-13.0	27281101
ECLASS-15.0	27281101

ETIM

ETIM 10.0	EC000761

UNSPSC

UNSPSC 21.0	39131500

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com