

# FL SWITCH 2316 PN - Industrial Ethernet Switch



1031673

<https://www.phoenixcontact.com/us/products/1031673>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows a version of the product

Managed Switch 2000 series, 16 RJ45 ports 10/100/1000 Mbps, degree of protection: IP20, Ambient temperature (operation): -40 °C ... 70 °C, Supply voltage range: 12 V DC ... 57 V DC, PROFINET Conformance Class B, Extended temperature range, PROFINET mode preset, PROFINET status LEDs, Development process certified in accordance with IEC 62443-4-1, Product certified in accordance with IEC 62443-4-2, The product is being prepared for compliance with the Cyber Resilience Act (CRA)

## Your advantages

- RSTP
- Ambient temperature -40 °C ... 70 °C
- MRP (client and manager)
- VLANs
- DHCP client, DHCP server (pool-based and port-based), DHCP option 82
- Web-based management, SNMP
- Configuration memory
- Easy and fast startup and commissioning with the FL NETWORK MANAGER software
- PROFINET mode preset



## Commercial data

| Item number |
|-------------|
| 1031673     |

# FL SWITCH 2316 PN - Industrial Ethernet Switch



1031673

<https://www.phoenixcontact.com/us/products/1031673>

|                                      |               |
|--------------------------------------|---------------|
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | DN17          |
| Product key                          | DNN121        |
| GTIN                                 | 4055626535265 |
| Weight per piece (including packing) | 572.4 g       |
| Weight per piece (excluding packing) | 572.4 g       |
| Customs tariff number                | 85176200      |
| Country of origin                    | DE            |

# FL SWITCH 2316 PN - Industrial Ethernet Switch




1031673

<https://www.phoenixcontact.com/us/products/1031673>

## Technical data

### Dimensions

|                     |                                                                                    |
|---------------------|------------------------------------------------------------------------------------|
| Dimensional drawing |  |
| Width               | 85 mm                                                                              |
| Height              | 130 mm                                                                             |
| Depth               | 119 mm                                                                             |

### Notes

|                     |                                                                                                                                                                                                                               |
|---------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Note on application | Support by phone or on-site (fee is charged)                                                                                                                                                                                  |
| Note on application | Only for industrial use                                                                                                                                                                                                       |
| Note on application | As things stand now, we are preparing the product so that, as of December 11, 2027, it will comply with the requirements of the EU Cyber Resilience Act (CRA) based on the information currently available regarding the CRA. |

### Utilization restriction

|          |                                                                           |
|----------|---------------------------------------------------------------------------|
| EMC note | EMC: class A product, see manufacturer's declaration in the download area |
|----------|---------------------------------------------------------------------------|

### Material specifications

|                  |                                |
|------------------|--------------------------------|
| Color (Housing)  | gray (RAL 7042)                |
| Color (Cover)    | light gray (RAL 7035)          |
| Housing material | Polycarbonate fiber reinforced |

### Mounting

|               |                   |
|---------------|-------------------|
| Mounting type | DIN rail mounting |
|---------------|-------------------|

### Interfaces

#### Ethernet (RJ45)

|                               |                                   |
|-------------------------------|-----------------------------------|
| Connection method             | RJ45                              |
| Note on the connection method | Auto negotiation and autocrossing |
| Transmission speed            | 10/100/1000 Mbps                  |
| Transmission physics          | Copper                            |
| Transmission length           | 100 m (per segment)               |
| Signal LEDs                   | Data receive, link status         |
| No. of channels               | 16 (RJ45 ports)                   |

### Output data

# FL SWITCH 2316 PN - Industrial Ethernet Switch



1031673

<https://www.phoenixcontact.com/us/products/1031673>

Digital:

|             |              |
|-------------|--------------|
| Output name | Alarm output |
|-------------|--------------|

## Product properties

|                    |                                                                                  |
|--------------------|----------------------------------------------------------------------------------|
| Product type       | Switch                                                                           |
| Product family     | Managed Switch 2000                                                              |
| Type               | Book type                                                                        |
| MTTF               | 379.84 Years (SN 29500 standard, temperature 25°C, operating cycle 21%)          |
|                    | 199.41 Years (SN 29500 standard, temperature 40°C, operating cycle 34.25%)       |
|                    | 27.52 Years (SN 29500 standard, temperature 55°C, operating cycle 100%)          |
| Special properties | Extended temperature range                                                       |
|                    | PROFINET mode preset, PROFINET status LEDs                                       |
|                    | Development process certified in accordance with IEC 62443-4-1                   |
|                    | Product certified in accordance with IEC 62443-4-2                               |
| Signal delay       | The product is being prepared for compliance with the Cyber Resilience Act (CRA) |
|                    | ≥ 1.9 µs (Store-and-Forward mode, 10/100/1000 Mbps, depending on the frame size) |

## Insulation characteristics

|                     |                |
|---------------------|----------------|
| Protection class    | III (VDE 0106) |
| Degree of pollution | 2              |

## Switch functions

|                                  |                                                                                                                                        |
|----------------------------------|----------------------------------------------------------------------------------------------------------------------------------------|
| IP parameterization              | DHCP client                                                                                                                            |
|                                  | DHCP Option 82 (Relay Agent)                                                                                                           |
|                                  | DHCP server (pool-based, port-based)                                                                                                   |
|                                  | BootP                                                                                                                                  |
|                                  | DCP (Discovery and Configuration Protocol)                                                                                             |
| MAC address table                | 8k                                                                                                                                     |
| Signal contact control voltage   | typ. 24 V DC                                                                                                                           |
| PROFINET conformance class       | Conformance Class B                                                                                                                    |
| PROFINET device function         | PROFINET device                                                                                                                        |
|                                  | Fast Startup                                                                                                                           |
| Status and diagnostic indicators | LEDs: US1, US2 (power supply), Fail (alarm contact), 2 LEDs per Ethernet port (link/activity and speed), PROFINET status LEDs (BF, SF) |
| Basic functions                  | Store-and-forward switch, complies with IEEE 802.3                                                                                     |
| Management functions             | Web-based management (HTTP/HTTPS)                                                                                                      |
|                                  | Role-based user management (LDAP, RADIUS)                                                                                              |
|                                  | SNMPv1/v2/v3                                                                                                                           |
|                                  | Command Line Interface (Telnet, SSH)                                                                                                   |
|                                  | RMON History                                                                                                                           |

# FL SWITCH 2316 PN - Industrial Ethernet Switch



1031673

<https://www.phoenixcontact.com/us/products/1031673>

|                      |                                               |
|----------------------|-----------------------------------------------|
| Diagnostic functions | LLDP (Link Layer Discovery Protocol)          |
|                      | SNMP-Traps                                    |
|                      | N:1-Portmirroring                             |
|                      | ACD (Address Conflict Detection)              |
|                      | SysLog                                        |
|                      | CRC-Surveillance                              |
| Filter functions     | Quality of Service (8 priority classes)       |
|                      | Class of Service                              |
|                      | DiffServ/DSCP                                 |
|                      | Port-Priorisierung                            |
|                      | VLAN (up to 32 VLANs)                         |
|                      | IGMP Snooping/Querier (v1/v2)                 |
|                      | Auto-Query-Port                               |
|                      | Extended Multicast Filtering                  |
| Redundancy functions | MRP (Media Redundancy Protocol)               |
|                      | RSTP (Rapid Spanning Tree Protocol)           |
|                      | FRD (Fast Ring Detection)                     |
|                      | Large Tree Support                            |
|                      | LACP (Link Aggregation Control Protocol)      |
|                      | PROFINET S2 system redundancy                 |
| Time synchronization | SNTP (Simple Network Time Protocol)           |
| Additional functions | Jumbo frames (max. 9,600 bytes)               |
|                      | Transmission of MMS and GOOSE (IEC 61850-8-1) |
|                      | Transmission of Modbus/TCP                    |

## Security functions

|               |                                                            |
|---------------|------------------------------------------------------------|
| Port security | MAC-based, RADIUS (IEEE 802.1X), MAC Authentication Bypass |
|---------------|------------------------------------------------------------|

## Electrical properties

|                                                 |                                                                                     |
|-------------------------------------------------|-------------------------------------------------------------------------------------|
| Current consumption                             | 455 mA                                                                              |
| Local diagnostics                               | US1/2 Supply voltage US1, US2 Green LED                                             |
|                                                 | FAIL Div. LED red                                                                   |
|                                                 | LINK Link status Green LED                                                          |
|                                                 | BF Bus errors LED red                                                               |
|                                                 | SF Group error LED red                                                              |
| Maximum power dissipation for nominal condition | 13.2 W ( $U_S = \text{Min}$ , $T_{\text{amb}} = \text{Max}$ , $DO_1 = \text{Max}$ ) |
| Test section                                    | 24 V supply / functional ground 500 V DC 1 min                                      |
|                                                 | Ethernet interface/all other potentials 2.25 kV DC 1 min                            |
| Transmission medium                             | Copper                                                                              |

## Supply

|                         |                                                                |
|-------------------------|----------------------------------------------------------------|
| Supply voltage (DC)     | 24 V DC (redundant)                                            |
| Supply voltage range    | 12 V DC ... 57 V DC                                            |
| Power supply connection | via COMBICON, max. conductor cross-section 1.5 mm <sup>2</sup> |

# FL SWITCH 2316 PN - Industrial Ethernet Switch



1031673

<https://www.phoenixcontact.com/us/products/1031673>

|                             |                                                                             |
|-----------------------------|-----------------------------------------------------------------------------|
| Residual ripple             | 3.6 V <sub>PP</sub> (within the permitted voltage range)                    |
| Max. current consumption    | 1.8 A (U <sub>S</sub> = Min, T <sub>amb</sub> = Max, DO <sub>I</sub> = Max) |
| Typical current consumption | 455 mA (at U <sub>S</sub> = 24 V DC and 25 °C ambient temperature)          |
| Current consumption         | 455 mA                                                                      |

## Function

|                                |              |
|--------------------------------|--------------|
| Signal contact control voltage | typ. 24 V DC |
|--------------------------------|--------------|

## Connection data

|                                   |                                                                                                |
|-----------------------------------|------------------------------------------------------------------------------------------------|
| Connection method                 | Push-in spring connection                                                                      |
| Note on the connection method     | Use only copper connecting cables providing the permitted temperature range (-40 °C ... 75 °C) |
| pluggable                         | yes                                                                                            |
| Conductor cross-section, rigid    | 0.25 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>                                                   |
| Conductor cross-section, flexible | 0.25 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>                                                   |
| Conductor cross-section AWG       | 24 ... 16                                                                                      |
| Stripping length                  | 9 mm                                                                                           |

## Environmental and real-life conditions

### Ambient conditions

|                                          |                                                                         |
|------------------------------------------|-------------------------------------------------------------------------|
| Degree of protection                     | IP20                                                                    |
| Ambient temperature (operation)          | -40 °C ... 70 °C                                                        |
| Ambient temperature (storage/transport)  | -40 °C ... 85 °C                                                        |
| Permissible humidity (operation)         | 10 % ... 95 % (non-condensing)                                          |
| Permissible humidity (storage/transport) | 10 % ... 95 % (non-condensing)                                          |
| Shock (operation)                        | 30g (EN 60068-2-27)                                                     |
| Vibration (operation)                    | in acc. with IEC 60068-2-6: 5g, 150 Hz                                  |
| Air pressure (operation)                 | 80 kPa ... 110 kPa up to 2000 m above mean sea level (Without derating) |
| Air pressure (storage/transport)         | 79 kPa ... 108 kPa up to 2000 m above mean sea level (Without derating) |

## Standards and regulations

|                                                                   |     |
|-------------------------------------------------------------------|-----|
| Free from substances that could impair the application of coating | Yes |
|-------------------------------------------------------------------|-----|

## Approvals

|                       |                                                  |
|-----------------------|--------------------------------------------------|
| Shipbuilding approval | Tested in accordance with IEC 60945 and IACS E10 |
|-----------------------|--------------------------------------------------|

### ATEX

|                |                          |
|----------------|--------------------------|
| Identification | Ⓔ II 3 G Ex ec IIC T4 Gc |
| Certificate    | DEMKO 16 ATEX 1709X      |

### IECEX

|                |                     |
|----------------|---------------------|
| Identification | Ex ec IIC T4 Gc     |
| Certificate    | IECEX ULD 16.0018 X |

### UL, USA/Canada

# FL SWITCH 2316 PN - Industrial Ethernet Switch



1031673

<https://www.phoenixcontact.com/us/products/1031673>

|                |       |
|----------------|-------|
| Identification | cULus |
|----------------|-------|

## UL Ex, USA / Canada

|                |                                                                                                       |
|----------------|-------------------------------------------------------------------------------------------------------|
| Identification | Class I, Division 2, Groups A, B, C, and D, T4<br>Class I, Zone 2, AEx ec IIC T4<br>Ex ec IIC T4 Gc X |
| Certificate    | E366272                                                                                               |
| Note           | UL 60079-0 Ed. 6 / UL 60079-7 Ed. 5, CSA 22.2 No. 60079-0 Ed. 3 / CSA C22.2 No. 60079-7 Ed. 2         |

## EAC Ex

|                |                         |
|----------------|-------------------------|
| Identification | 2Ex e IIC T4 Gc X       |
| Certificate    | RU C-DE.HB49.B.00118/21 |

The following continue to apply for EAC Ex:

|                |                                                                                                                                                                                                                                                                                                                                    |
|----------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Identification | Install the device in a suitable, approved housing with at least IP66 protection.<br>The housing/control cabinet must be equipped with a warning sign prohibiting opening in the potentially explosive area.<br>The operation of devices is permitted if all optical ports are connected or sealed with the supplied filler plugs. |
|----------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

## CCC / China-Ex

|                |                  |
|----------------|------------------|
| Identification | Ex ec IIC T4 Gc  |
| Certificate    | 2022122310115629 |

## Corrosive gas test

|                |                                  |
|----------------|----------------------------------|
| Identification | ISA S71.04.2013 G3 Harsh Group A |
|----------------|----------------------------------|

## UKCA Ex (UKEX)

|                |                          |
|----------------|--------------------------|
| Identification | Ⓔ II 3 G Ex ec IIC T4 Gc |
| Certificate    | PxCIMA22UKEX2702910X     |

## Shipbuilding data

|             |                                                                                         |
|-------------|-----------------------------------------------------------------------------------------|
| Temperature | B                                                                                       |
| Humidity    | B                                                                                       |
| Vibration   | A                                                                                       |
| EMC         | B                                                                                       |
| Enclosure   | Required protection according to the Rules shall be provided upon installation on board |

## EMC data

|                                 |                                                                                                                                                                                                                                                                                                                                          |
|---------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Electromagnetic compatibility   | Conformance with EMC Directive 2014/30/EU                                                                                                                                                                                                                                                                                                |
| Conformance with EMC directives | EN 61000-6-2 EN 61000-4-2 (ESD) Criterion B<br>EN 61000-6-2 EN 61000-4-3 (electromagnetic fields) Criterion A<br>EN 61000-6-2 EN 61000-4-4 (EFT burst) Criterion A<br>EN 61000-6-2 EN 61000-4-5 (surge) Criterion A<br>EN 61000-6-2 EN 61000-4-6 (line noise immunity) Criterion A<br>EN 61000-6-2 EN 61000-6-3 (noise emission) Class B |

# FL SWITCH 2316 PN - Industrial Ethernet Switch



1031673

<https://www.phoenixcontact.com/us/products/1031673>

|                |                                                         |
|----------------|---------------------------------------------------------|
|                | EN 61000-6-2 EN 61000-6-3 (conducted emissions) Class B |
| Noise immunity | EN 61000-6-2                                            |

Noise emission

|                       |              |
|-----------------------|--------------|
| Standards/regulations | EN 61000-6-4 |
|-----------------------|--------------|

Signaling

|                |                                                                                                                                        |
|----------------|----------------------------------------------------------------------------------------------------------------------------------------|
| Status display | LEDs: US1, US2 (power supply), Fail (alarm contact), 2 LEDs per Ethernet port (link/activity and speed), PROFINET status LEDs (BF, SF) |
|----------------|----------------------------------------------------------------------------------------------------------------------------------------|

# FL SWITCH 2316 PN - Industrial Ethernet Switch




1031673

<https://www.phoenixcontact.com/us/products/1031673>

## Drawings

Dimensional drawing



# FL SWITCH 2316 PN - Industrial Ethernet Switch



1031673

<https://www.phoenixcontact.com/us/products/1031673>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1031673>



**DNV GL**

Approval ID: TAA00000YV



**LR**

Approval ID: LR22250919TA



**NK**

Approval ID: TA24215M



**BV**

Approval ID: 48146\_B1 BV

**BSH**

Approval ID: 1045



**RINA**

Approval ID: ELE014724XG001

**ABS**

Approval ID: 21\_2066186\_1\_PDA



**cULus Listed**

Approval ID: E238705

**Cybersecurity Certificate**

Approval ID: 968 CSP 1043.00 25

**ABS**

Approval ID: 26-0501235-PDA



**IECEx**

Approval ID: IECEx ULD 16.0018X

# FL SWITCH 2316 PN - Industrial Ethernet Switch



1031673

<https://www.phoenixcontact.com/us/products/1031673>



## ATEX

Approval ID: DEMKO 16 ATEX 1709X



## CCC

Approval ID: 2022122310115629



## cULus Listed

Approval ID: E366272

# FL SWITCH 2316 PN - Industrial Ethernet Switch



1031673

<https://www.phoenixcontact.com/us/products/1031673>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 19170401 |
| ECLASS-15.0 | 19170401 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC000734 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 43222600 |
|-------------|----------|

# FL SWITCH 2316 PN - Industrial Ethernet Switch



1031673

<https://www.phoenixcontact.com/us/products/1031673>

## Environmental product compliance

### EU RoHS

|                                         |              |
|-----------------------------------------|--------------|
| Fulfills EU RoHS substance requirements | Yes          |
| Exemption                               | 7(a), 7(c)-I |

### China RoHS

|                                        |                                                                                                                                                                                                                                   |
|----------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-50                                                                                                                                                                                                                           |
|                                        | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |                                      |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1)                 |
| SCIP                                | cdeba26b-132a-4c2c-b065-bb5357b5903a |

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)