NBC-PP-G1PGY - DIN rail adapter

1041740

https://www.phoenixcontact.com/us/products/1041740

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



DIN rail adapter, connection method: Quick connection, material: PC-GF10, degree of protection: IP20, without assembled modules

Product description

Compact DIN rail adapter with optional overall shielding braid, with dust protection cover, one-piece design

Your advantages

- Compact design
- For distributing copper and fiber optic cabling
- Front release without special tool
- Assembly without special tools

Commercial data

Item number	1041740
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB18
Product key	ABNLAA
GTIN	4055626598666
Weight per piece (including packing)	30 g
Weight per piece (excluding packing)	29.4 g
Customs tariff number	85366990
Country of origin	DE

Technical data

Notes

Notes on operation	without assembled modules

Product properties

Product type	Patch panel
Set comprises	1100077 NBC-PP-J1PGY-S/R4IDC8
Number of module slots	1
Number of slots	1

Electrical properties

Contact resistance per contact pair	≤ 5 mΩ
Contact resistance	≤ 5 mΩ (Shield-ground, optional)

Connection data

Connection method	Quick connection

Dimensions

Width	18 mm
Height	80 mm
Depth	64.6 mm

Material specifications

Material	PP (Dust protection flap)
Flammability rating according to UL 94	V0
Housing material	PC-GF10
Contact material	CuSn6
Contact surface material	Tin

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
	IP20
Ambient temperature (operation)	-10 °C ... 60 °C
Ambient temperature (storage/transport)	-40 °C ... 60 °C

Mounting

Mounting type	DIN rail mounting
Assembly note	Dust cover not compatible with FO module inserts

Classifications

ECLASS

ECLASS-13.0	27440392
ECLASS-15.0	27440318

ETIM

ETIM 10.0	EC002597

UNSPSC

UNSPSC 21.0	26121600

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

EF3.1 Climate Change

CO2e kg	0.775 kg CO2e

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com