CUC-K-D1ZNI-S/R4GCHP8 - RJ45 coupling

1086108

https://www.phoenixcontact.com/us/products/1086108

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

800 V
IEC



RJ45 coupling, RJ45, Ethernet, CAT6$_A$ (10 Gbps), 8-position, connection method: Coupling, material: Metal, degree of protection: IP20, Keystone design for use with IP20 and IP67 panel mounting frame or integrated directly into the housing panel

Your advantages

- Compact design
- Keystone adapter can be integrated directly into the housing panel
- Rugged design
- 10 Gbps
- Assembly without special tools
- CAT6A in accordance with ISO/IEC 11801
- 360° shielding
- PoE++ compatible

Commercial data

Item number	1086108
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB10
Product key	ABNACB
GTIN	4055626877808
Weight per piece (including packing)	15 g
Weight per piece (excluding packing)	15 g
Customs tariff number	85366930
Country of origin	PL

Technical data

Product properties

Product type	Female insert
Type	RJ45
Number of positions	8
Connection profile	RJ45
Number of slots	2
Cable outlet	straight

Insulation characteristics

Overvoltage category	III
Degree of pollution	2

Electrical properties

Rated voltage (III/3)	72 V (DC)
Rated surge voltage	0.8 kV
Rated current	1 A (at 60 °C)
Max. operating voltage U_{max}	72 V DC
Frequency range	500 MHz
Insulation resistance	≥ 500 MΩ
Nominal current I_N	0.5 A
Contact resistance	200 mΩ (Trunk in to trunk out)
Transmission speed	10 Gbps
Transmission characteristics (category)	$CAT6_A$

Connection data

Connection technology

Connection method	Coupling

Interfaces

Signal type/category	Ethernet $CAT6_A$ (In accordance with ISO/IEC 11801), 10 Gbps

Dimensions

Width	17.8 mm
Height	22.5 mm
Length	27 mm
Drill hole distance, horizontal	2.95 mm
Drill hole distance, vertical	3 mm

Material specifications

Flammability rating according to UL 94	V0
Housing material	Metal
Housing surface material	metal-plated

Contact material	Spring steel
Contact surface material	Gold

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 750

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
	IP20
Ambient temperature (operation)	-25 °C ... 70 °C
Ambient temperature (storage/transport)	60 °C

Standards and regulations

Standards/specifications	IEC 60603-7
	DIN EN 50173-1
	ISO/IEC 11801-Am.1
	IEC 60068-2

Mounting

Mounting type	Snap in

Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/1086108

cUL Recognized
Approval ID: E335024-DUXR8

UL Recognized
Approval ID: E335024-DUXR2

Classifications

ECLASS

ECLASS-13.0	27440390
ECLASS-15.0	27440325

ETIM

ETIM 10.0	EC001134

UNSPSC

UNSPSC 21.0	43222600

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

EF3.1 Climate Change

CO2e kg	1.266 kg CO2e

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com