# SZG 0,6X3,5 VDE - Screwdriver

1205121

https://www.phoenixcontact.com/us/products/1205121

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Screwdriver, slot-headed, graded, for test socket screws, size: 0.6 x 3.5 x 100 mm, 2-component grip, with non-slip grip

## Your advantages

- Screwdriver ideally suited for test socket screws
- For working on or in the vicinity of live parts up to 1000 V AC or 1500 V DC
- The tools feature ergonomic two-component safety handles
- VDE-tested, for maximum safety

## Commercial data

| | |
|---|---|
| Item number | 1205121 |
| Packing unit | 10 pc |
| Minimum order quantity | 1 pc |
| Sales key | BH31 |
| Product key | BH3144 |
| GTIN | 4017918019136 |
| Weight per piece (including packing) | 56.75 g |
| Weight per piece (excluding packing) | 56.75 g |
| Customs tariff number | 82054000 |
| Country of origin | CZ |

## Technical data

### Notes

| | |
|---|---|
| General | Stepped blade |

Environmental Product Compliance

| | |
|---|---|
| California Proposition 65 | Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration |


### Product properties

| | |
|---|---|
| Product type | Screwdriver tools |
| Type | Bladed |
| Product property | Kraftform handle |
| | Two-component handle |
| | Hexagonal non-slip grip |
| | Test sockets with screw head |

### Connection data

| | |
|---|---|
| Output | Test socket screws |

### Dimensions

| | |
|---|---|
| Dimensional drawing |  |
| Width | 33 mm |
| Blade width | 3.5 mm |
| Blade height | 100 mm |
| Length | 198 mm |
| Wrench size | 0 mm |
| Wrench size for mounting | 0 mm |
| Blade thickness | 0.6 mm |

### Material specifications


| | |
|---|---|
| Color | silver |
| Material | alloyed tool steel |

### Standards and regulations


| | |
|---|---|
| Tests | IEC 60900:2004 |

## Drawings

Dimensional drawing




Schematic diagram



## Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/1205121

**EAC**
Approval ID: RU x-DE.xx08.B.02974

**VDE Zeichengenehmigung**
Approval ID: 086858

**EAC**
Approval ID: 7500525.13.12.00701

## Classifications

### ECLASS

| | |
|---|---|
| ECLASS-13.0 | 21040407 |
| ECLASS-15.0 | 21040407 |

### ETIM

| | |
|---|---|
| ETIM 10.0 | EC000158 |

### UNSPSC

| | |
|---|---|
| UNSPSC 21.0 | 27111700 |

## Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE |

EU REACH SVHC

| | |
|---|---|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |

EF3.1 Climate Change

| | |
|---|---|
| CO2e kg | 0.655 kg CO2e |

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com