CRIMPFOX-RCI 6-M - Crimping pliers

1212730

https://www.phoenixcontact.com/us/products/1212730

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimping pliers, compact pliers, for symmetrical insulated cable lugs, 0.5 mm^2 ... 6.0 mm^2 (red, blue, yellow), three marked die stations, unlockable pressure lock, lateral entry

Your advantages

- Unlockable pressure lock
- The color-coded dies clearly indicate the cross section
- Crimping pliers for cable lugs and connectors
- They unlock as soon as the required crimping pressure is reached, therefore ensuring sufficient pressure is applied

Commercial data

Item number	1212730
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3132
GTIN	4046356857895
Weight per piece (including packing)	619.3 g
Weight per piece (excluding packing)	619.3 g
Customs tariff number	82032000
Country of origin	SE

Technical data

Notes

Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

Product properties

Product type	Crimping tool
Compression	Oval crimp
Product property	Unlockable pressure lock
	Color-coded dies

Crimping position 1

Min. cross section	0.5 mm²
Max. cross section	1.5 mm²
AWG min	20
AWG max	16

Crimping position 2

Min. cross section	1.5 mm²
Max. cross section	2.5 mm²
AWG min	16
AWG max	14

Crimping position 3

Min. cross section	4 mm²
Max. cross section	6 mm²
AWG min	12
AWG max	10

Connection data

Conductor connection

Cross section range, metric	0.5 mm² ... 6 mm²
Cross section range AWG	20 ... 10

Dimensions

Width	22 mm
Height	76 mm
Length	204 mm

Material specifications

Color	black

Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/1212730

EAC
Approval ID: RU x-DE.xx08.B.02974

Classifications

ECLASS

ECLASS-13.0	21043811
ECLASS-15.0	21043811

ETIM

ETIM 10.0	EC000168

UNSPSC

UNSPSC 21.0	27111500

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com