

HC-EVO-B06-HLFS-PLBK - Housing



1407619

<https://www.phoenixcontact.com/us/products/1407619>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



HEAVYCON EVO sleeve housing, plastic, with bayonet flange for EVO screw connection, B6, for single locking latch, height: 60.5 mm, without EVO screw connection

Your advantages

- Flexible cable outlet direction, lateral or straight
- Lower costs than metal version
- Low weight
- Lower risk of condensation

Commercial data

Item number	1407619
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF57
Product key	AF7APL
GTIN	4046356776813
Weight per piece (including packing)	58.8 g
Weight per piece (excluding packing)	58.2 g
Customs tariff number	85389099
Country of origin	PL

HC-EVO-B06-HLFS-PLBK - Housing



1407619

<https://www.phoenixcontact.com/us/products/1407619>

Technical data


Notes

General	For contact inserts HC-B6, BB10, DD24, M
---------	--

Product properties

Product type	Housing with locking latch
Housing type	Sleeve housing
Product family	HC-EVO-B
Application	Standard
Type	B6
No. of cable outlets	1
Cable outlet	straight
Pg screw connection	none

Dimensions

Dimensional drawing	
Width	49 mm
Height	60.5 mm
Length	60 mm

Material specifications

Flammability rating according to UL 94	V0 (Housing)
Housing material	PA 6.6-FR

Mechanical properties

Mechanical data	
Locking type	Pin

Mounting

Assembly note	The sleeve base housing must be supplemented with the EVO screw connection. The EVO screw connection is available in four sizes. It facilitates the creation of a straight or a side cable outlet. The EVO screw connection is mounted with the aid of, for example, a pipe wrench
---------------	--

Environmental and real-life conditions

Ambient conditions	
Degree of protection	IP66
Enclosure rating (NEMA)	12 (UL 50e)

HC-EVO-B06-HLFS-PLBK - Housing

1407619

<https://www.phoenixcontact.com/us/products/1407619>



Impact strength	IK08
Ambient temperature (operation)	-40 °C ... 125 °C

HC-EVO-B06-HLFS-PLBK - Housing


1407619

<https://www.phoenixcontact.com/us/products/1407619>



Drawings

Dimensional drawing



Dimensional drawing

HC-EVO-B06-HLFS-PLBK - Housing



1407619

<https://www.phoenixcontact.com/us/products/1407619>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1407619>

DNV

Approval ID: TAE000037S



cUL Recognized

Approval ID: E255026



UL Recognized

Approval ID: E255026



EAC

Approval ID: RU C-DE.AI30.B.01102

HC-EVO-B06-HLFS-PLBK - Housing



1407619

<https://www.phoenixcontact.com/us/products/1407619>

Classifications

ECLASS

ECLASS-13.0	27440202
ECLASS-15.0	27440202

ETIM

ETIM 10.0	EC000437
-----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

HC-EVO-B06-HLFS-PLBK - Housing



1407619
<https://www.phoenixcontact.com/us/products/1407619>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com