

# SACC-M12MS-8CON-PG11-M - Connector



1410666

<https://www.phoenixcontact.com/us/products/1410666>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Connector, Universal, 8-position, Plug straight M12, coding: A, Screw connection, knurl material: Brass, nickel-plated, cable gland Pg11, external cable diameter 8 mm ... 10 mm

## Your advantages

- Safe use in the field, thanks to a high degree of protection
- Screw connection: proven connection technology for a large selection of different conductors

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1410666       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BF30          |
| Product key                          | AF2CAA        |
| GTIN                                 | 4046356904650 |
| Weight per piece (including packing) | 30.4 g        |
| Weight per piece (excluding packing) | 24.82 g       |
| Customs tariff number                | 85366990      |
| Country of origin                    | CN            |

# SACC-M12MS-8CON-PG11-M - Connector



1410666

<https://www.phoenixcontact.com/us/products/1410666>

## Technical data

### Notes

Assembly note

**NOTE:** Observe the permissible bending radii when routing cables, since the degree of protection may be at risk if the bending forces are too high. Reduce mechanical loads upstream of the connector, e.g., by using cable ties.

### Product properties


|                      |                                 |
|----------------------|---------------------------------|
| Product type         | Circular connector (cable-side) |
| Number of positions  | 8                               |
| No. of cable outlets | 1                               |
| Shielded             | no                              |
| Coding               | A                               |
| Cable outlet         | straight                        |
| Pg screw connection  | Pg11                            |

### Insulation characteristics

|                      |    |
|----------------------|----|
| Overvoltage category | II |
| Degree of pollution  | 3  |

### Dimensions

Dimensional drawing



|                          |       |
|--------------------------|-------|
| Width                    | 20 mm |
| Height                   | 20 mm |
| Length                   | 62 mm |
| Wrench size, union nut   | 19 mm |
| Wrench size, counter nut | 17 mm |

### External dimensions

|                  |                |
|------------------|----------------|
| Outside diameter | 8 mm ... 10 mm |
|------------------|----------------|

### Housing

|                  |       |
|------------------|-------|
| Diameter housing | 20 mm |
|------------------|-------|

### Material specifications

|                                        |         |
|----------------------------------------|---------|
| Material Cable gland                   | PA      |
| Flammability rating according to UL 94 | HB      |
| Seal material                          | Silicon |
| Material of grip body                  | PBT     |
| Contact material                       | CuZn    |
| Contact surface material               | Au      |

# SACC-M12MS-8CON-PG11-M - Connector



1410666

<https://www.phoenixcontact.com/us/products/1410666>

|                               |                      |
|-------------------------------|----------------------|
| Contact carrier material      | PA                   |
| Material for screw connection | Brass, nickel-plated |

## Connection data

### Conductor connection

|                                         |                                                                |
|-----------------------------------------|----------------------------------------------------------------|
| Connection method                       | Screw connection                                               |
| Connection cross section                | 0.25 mm <sup>2</sup> ... 0.5 mm <sup>2</sup> (without ferrule) |
|                                         | 0.14 mm <sup>2</sup> ... 0.34 mm <sup>2</sup> (with ferrule)   |
|                                         | 0.25 mm <sup>2</sup> ... 0.5 mm <sup>2</sup> (solid)           |
| Connection cross section AWG            | 24 ... 20 (without ferrule)                                    |
|                                         | 26 ... 22 (with ferrule)                                       |
| Stripping length of the individual wire | 5 mm                                                           |
| Tightening torque                       | 0.4 Nm (M12 knurl)                                             |
|                                         | 0.2 Nm (Screw terminal blocks)                                 |
|                                         | 1 Nm (Pressure screw with sleeve housing)                      |

## Electrical properties

|                                |          |
|--------------------------------|----------|
| Rated surge voltage            | 0.8 kV   |
| Contact resistance             | ≤ 8 mΩ   |
| Insulation resistance          | ≥ 100 MΩ |
| Nominal voltage U <sub>N</sub> | 30 V AC  |
|                                | 30 V DC  |
| Nominal current I <sub>N</sub> | 2 A      |

## Mechanical properties

### Mechanical data

|                             |       |
|-----------------------------|-------|
| Insertion/withdrawal cycles | ≥ 100 |
|-----------------------------|-------|

## Connector

### Connection 1

|                   |          |
|-------------------|----------|
| Head design       | Plug     |
| Head cable outlet | straight |
| Head thread type  | M12      |
| Coding            | A        |

## Interfaces

|                      |           |
|----------------------|-----------|
| Signal type/category | Universal |
|----------------------|-----------|

## Environmental and real-life conditions

### Ambient conditions

|                                                                   |                                  |
|-------------------------------------------------------------------|----------------------------------|
| Degree of protection                                              | IP67                             |
| Ambient temperature (operation) (male connector/female connector) | -40 °C ... 85 °C (Plug / socket) |

# SACC-M12MS-8CON-PG11-M - Connector



1410666


<https://www.phoenixcontact.com/us/products/1410666>

## Standards and regulations

|                          |                 |
|--------------------------|-----------------|
| Standard designation     | M12 connector   |
| Standards/specifications | IEC 61076-2-101 |


## Drawings

Dimensional drawing




Plug, M12 x 1, straight

Schematic diagram



Pin assignment M12 plug, 8-pos., A-coded, view plug side

Schematic diagram



Cable connection side M12 (screw connection)

# SACC-M12MS-8CON-PG11-M - Connector



1410666

<https://www.phoenixcontact.com/us/products/1410666>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1410666>

|  <b>cUL Recognized</b><br>Approval ID: FILE E 221474 |                                |                                |                   |                               |
|---------------------------------------------------------------------------------------------------------------------------------------|--------------------------------|--------------------------------|-------------------|-------------------------------|
|                                                                                                                                       | Nominal voltage U <sub>N</sub> | Nominal current I <sub>N</sub> | Cross section AWG | Cross section mm <sup>2</sup> |
| keine                                                                                                                                 |                                |                                |                   |                               |
|                                                                                                                                       | 30 V                           | 2 A                            | -                 | -                             |

|  <b>UL Recognized</b><br>Approval ID: FILE E 221474 |                                |                                |                   |                               |
|--------------------------------------------------------------------------------------------------------------------------------------|--------------------------------|--------------------------------|-------------------|-------------------------------|
|                                                                                                                                      | Nominal voltage U <sub>N</sub> | Nominal current I <sub>N</sub> | Cross section AWG | Cross section mm <sup>2</sup> |
| keine                                                                                                                                |                                |                                |                   |                               |
|                                                                                                                                      | 30 V                           | 2 A                            | -                 | -                             |

# SACC-M12MS-8CON-PG11-M - Connector



1410666

<https://www.phoenixcontact.com/us/products/1410666>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27440116 |
| ECLASS-15.0 | 27440116 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC002635 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

## Environmental product compliance

## EU RoHS

|                                         |      |
|-----------------------------------------|------|
| Fulfills EU RoHS substance requirements | Yes  |
| Exemption                               | 6(c) |

## China RoHS

|                                        |                                                                                                                                                                                                                                   |
|----------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-50                                                                                                                                                                                                                           |
|                                        | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

## EU REACH SVHC

|                                     |                                       |
|-------------------------------------|---------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1)                  |
| SCIP                                | a8184dd1-bcde-413f-a809-9aedef35cb9e7 |

## EF3.1 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 0.889 kg CO2e |
|---------|---------------|