

# G-INS-M32-M68N-PNES-BK - Cable gland



1411136

<https://www.phoenixcontact.com/us/products/1411136>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable gland, material for screw connection: PA, application: Standard, external cable diameter 15 mm ... 21 mm, shielding: no, connecting thread: M32 x 1.5, color: jet black RAL 9005

## Your advantages

- Plastic material conforms to UL 746C f1

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1411136       |
| Packing unit                         | 5 pc          |
| Minimum order quantity               | 5 pc          |
| Sales key                            | BF68          |
| Product key                          | AF7DCX        |
| GTIN                                 | 4046356922685 |
| Weight per piece (including packing) | 27.1 g        |
| Weight per piece (excluding packing) | 26.7 g        |
| Customs tariff number                | 39269097      |
| Country of origin                    | TR            |

# G-INS-M32-M68N-PNES-BK - Cable gland



1411136

<https://www.phoenixcontact.com/us/products/1411136>

## Technical data

### Mounting

|               |                                                                                                                                         |
|---------------|-----------------------------------------------------------------------------------------------------------------------------------------|
| Assembly note | 1) Mount screw connection support in the housing using the correct torque 2) Insert cable 3) Tighten union nut using the correct torque |
|---------------|-----------------------------------------------------------------------------------------------------------------------------------------|


### Product properties

|                                |                   |
|--------------------------------|-------------------|
| Product type                   | Cable screw gland |
| Application                    | Standard          |
| No. of conductors              | 1                 |
| Manufacturer                   | BIMED             |
| Manufacturer Designation       | BM-EN-24          |
| Shielded                       | no                |
| Execution of the strain relief | A                 |

### Characteristics

|                          |   |
|--------------------------|---|
| Category of shock impact | 4 |
| Design, Strain relief    | A |

### Dimensions

|                                 |                                                                                      |
|---------------------------------|--------------------------------------------------------------------------------------|
| Dimensional drawing             |  |
| Length                          | 50 mm                                                                                |
| Length of the connecting thread | 10 mm                                                                                |
| Hole diameter                   | 32.1 mm ... 32.3 mm                                                                  |
| Wrench size, union nut          | 36 mm                                                                                |
| Wrench size, support            | 36 mm                                                                                |
| Hexagon angular dimension       | 40.9 mm                                                                              |
| Thread type connection side     | M32 x 1.5                                                                            |
| Thread pitch                    | 1.5 mm                                                                               |

### Connection data

|                   |                           |
|-------------------|---------------------------|
| Tightening torque | 6 Nm $\pm$ 1 Nm (Cap nut) |
|                   | 5 Nm (Support sleeve)     |

### Material specifications

|                                        |                  |
|----------------------------------------|------------------|
| Color                                  | black (RAL 9005) |
| Material Housing                       | PA (Housing)     |
| Flammability rating according to UL 94 | V2               |
| Seal material Cable seal               | CR               |

# G-INS-M32-M68N-PNES-BK - Cable gland



1411136

<https://www.phoenixcontact.com/us/products/1411136>

|                               |    |
|-------------------------------|----|
| Material for screw connection | PA |
|-------------------------------|----|

## Cable/line

|                                 |                                |
|---------------------------------|--------------------------------|
| External cable diameter Cable 1 | 15 mm ... 21 mm                |
| External cable diameter         | 16 mm ... 21 mm (for UL 514 B) |
| Halogen-free                    | no                             |

## Environmental and real-life conditions

### Ambient conditions

|                                 |                            |
|---------------------------------|----------------------------|
| Degree of protection            | IP66                       |
|                                 | IP68 (5 bar / 0.5 h)       |
| Enclosure rating (NEMA)         | 1                          |
|                                 | 4                          |
|                                 | 4X                         |
|                                 | 12                         |
|                                 | 13                         |
| Ambient temperature (operation) | -40 °C ... 100 °C (static) |

# G-INS-M32-M68N-PNES-BK - Cable gland


1411136

<https://www.phoenixcontact.com/us/products/1411136>



## Drawings

Dimensional drawing



Dimensional drawing

# G-INS-M32-M68N-PNES-BK - Cable gland



1411136

<https://www.phoenixcontact.com/us/products/1411136>

## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1411136>

### DNV

Approval ID: TAE00003WX



### CSA

Approval ID: 115116



### VDE Zeichengenehmigung

Approval ID: 40024424



### UL Listed

Approval ID: E199260

# G-INS-M32-M68N-PNES-BK - Cable gland



1411136

<https://www.phoenixcontact.com/us/products/1411136>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27140801 |
| ECLASS-15.0 | 27140801 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC000441 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121300 |
|-------------|----------|

# G-INS-M32-M68N-PNES-BK - Cable gland



1411136

<https://www.phoenixcontact.com/us/products/1411136>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

### EF3.1 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 0.081 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)