HC-KIT-A04-R01 - Connector set

1409668

https://www.phoenixcontact.com/us/products/1409668

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Connector set, consisting of: D7 sleeve housing and panel mounting base, 4-pos. plug and socket insert, M20 cable gland

Commercial data

Item number	1409668
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF63
Product key	AF7AFX
GTIN	4046356752411
Weight per piece (including packing)	141.7 g
Weight per piece (excluding packing)	141.7 g
Customs tariff number	85366990
Country of origin	CN

Set consists of

G-INS-M20-S68N-NNES-S - Cable gland

1411163

https://www.phoenixcontact.com/us/products/1411163



Cable gland, material for screw connection: Brass, nickel-plated, application: Standard, external cable diameter 6 mm ... 12 mm, shielding: no, connecting thread: M20 x 1.5, color: silver-colored, with O-ring

HC-A04-I-UT-M - Contact insert

1585236

https://www.phoenixcontact.com/us/products/1585236



Contact insert, number of positions: 4+PE, size: D7, number of connections per position: 1, Pin, Screw connection, 230 V/400 V, 10 A, 0.5 mm^2 ... 2.5 mm^2

HC-STA-D07-HHFS-1STM20-EL-AL - Housing

1419235

https://www.phoenixcontact.com/us/products/1419235



Sleeve housing D7, for single locking latch, material: Die-cast aluminum, salt water resistant, cable outlets: 1, lateral, 1x M20, height: 52.8 mm, cable gland: none, Standard

HC-STA-D07-BWSCF-EL-AL - Housing

1419251

https://www.phoenixcontact.com/us/products/1419251



Panel mounting base D7, with single locking latch, material: Die-cast aluminum, salt water resistant, protective cover material: PA, height: 25.5 mm, cable gland: none, protective cover: yes, Standard, for socket inserts

HC-A04-I-UT-F - Contact insert

1585249

https://www.phoenixcontact.com/us/products/1585249



Contact insert, number of positions: 4+PE, size: D7, number of connections per position: 1, Socket, Screw connection, 230 V/400 V, 10 A, 0.5 mm^2 ... 2.5 mm^2

Technical data

Product properties

Product type	Connector set
Housing type	Complete housing
Application	Power
Type	D7
Number of positions	4
Connection profile	4+PE
No. of cable outlets	1
Seal present	yes
Protective cover	yes
Contact material type	turned
Shielded	yes
Cable outlet	lateral

Insulation characteristics

Overvoltage category	III
Degree of pollution	3


Electrical properties

Rated voltage (III/3)	230 V
Rated surge voltage	4 kV
Rated current	24 A
Nominal voltage U_N	230 V
Nominal current I_N	10 A

Connection data

Connection method	Screw connection
Connection technology	Screw connection
Conductor cross-section	0.5 mm² ... 2.5 mm² (applies to stranded conductors with ferrules)
	0.5 mm² ... 2.5 mm² (applies to stranded conductors with ferrules)
Connection cross section AWG	20 ... 14
Tightening torque	0.25 Nm ... 0.5 Nm

Dimensions

Dimensional drawing	
Width	38 mm
Height	78.3 mm

Length	34.2 mm

Installation dimensions

Width of the assembly cutout	21 mm
Length of the assembly cutout	21 mm

Material specifications

Material Housing	Die-cast aluminum, saltwater-resistant
Flammability rating according to UL 94	V0
Seal material	NBR, conductive
Contact material	Copper alloy
Contact surface material	Ag
Contact carrier material	PC
Locking latch material	PA

Cable/line

External cable diameter	6 mm ... 12 mm
	10 mm ... 12 mm (for UL 514 B)
External cable diameter	9 mm ... 13 mm

Mechanical properties

Mechanical data

Locking type	Latch

Environmental and real-life conditions

Ambient conditions


Degree of protection	IP65
Impact strength	IK06
Ambient temperature (operation)	-40 °C ... 100 °C

Mounting

Mounting type	Screw mounting

Drawings

Dimensional drawing



Dimensional drawing

Classifications

ECLASS

ECLASS-13.0	27440113
ECLASS-15.0	27440113

ETIM

ETIM 10.0	EC002636

UNSPSC

UNSPSC 21.0	39121400

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	065e9cde-91df-4c8f-8209-a35d7406bb88

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com