

MC-35/37-MULTI-67-PV-LG - Cable feed-through plates



1415240
<https://www.phoenixcontact.com/us/products/1415240>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable feed-through plates, no. of conductors: 37, external cable diameter: 4x 6 mm ... 10 mm, 14x 8 mm ... 12 mm, 16x 10 mm ... 14 mm, 2x 12 mm ... 18 mm, 1x 17 mm ... 32 mm, material: galvanized sheet steel (Core), material: TPE-SEBS (external material), color: light gray, length: 222 mm, width: 92 mm, height: 29.5 mm

Commercial data

Item number	1415240
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF67
Product key	AF7CAX
GTIN	4055626039442
Weight per piece (including packing)	297 g
Weight per piece (excluding packing)	291.1 g
Customs tariff number	39269097
Country of origin	FI

MC-35/37-MULTI-67-PV-LG - Cable feed-through plates



1415240

<https://www.phoenixcontact.com/us/products/1415240>

Technical data

Notes

General	incl. mounting screws
General	2 mm thick coated, galvanized sheet steel

Product properties

Product type	Cable feed-through
No. of conductors	37

Connection data

External cable diameter	4x 6 mm ... 10 mm
Tightening torque	1.5 Nm ... 2 Nm (Mounting screws)

Dimensions

Dimensional drawing	
	The technical drawing shows two views of the 16-pin connector. The top view (side profile) shows a length of 222 mm, a total height of 43 mm (with a base of 23 mm and a top section of 20 mm), and a mounting hole diameter of 29.5 mm. The bottom view (top-down) shows a width of 92 mm and a pin pitch of 19.4 mm. The pin array is 16 pins wide and 8 pins high. The distance between the center of the pin array and the mounting holes is 17.5 mm on the sides and 17 mm on the top and bottom. The distance between the center of the pin array and the mounting holes is 15 mm on the sides and 15 mm on the top and bottom. The distance between the center of the pin array and the mounting holes is 15 mm on the sides and 15 mm on the top and bottom.
Width	92 mm
Height	29.5 mm
Length	222 mm
Drill hole distance, horizontal	62 mm
Drill hole distance, vertical	194 mm
Hole diameter	8.5 mm

Material specifications

Color	light gray (RAL 7035)
Material interior	galvanized sheet steel (Core)
Material exterior	TPE-SEBS (external material)
Flammability rating according to UL 94	V0

Cable/line

External cable diameter 6-10 mm	4x 6 mm ... 10 mm
External cable diameter 8-12 mm	14x 8 mm ... 12 mm
External cable diameter 10-14 mm	16x 10 mm ... 14 mm
External cable diameter 12-18 mm	2x 12 mm ... 18 mm
External cable diameter 17-32 mm	1x 17 mm ... 32 mm

Environmental and real-life conditions

MC-35/37-MULTI-67-PV-LG - Cable feed-through plates



1415240

<https://www.phoenixcontact.com/us/products/1415240>

Ambient conditions

Degree of protection	IP66 (Minimum sheet thickness ≥ 2.5 mm)
	IP67 (Minimum sheet thickness ≥ 2.5 mm)
Ambient temperature (operation)	-40 °C ... 100 °C

Mounting

Assembly note	M8 mounting screw, torque: 1.5 - 2.0 Nm, SW5 Allen key
	The mounting screws provided are to be used for mounting.
	Mounting sequence: 1) Fix Multigates with the mounting screws provided (observe torque) 2) Cut a hole in the membrane/cut off the tip of the cone 3) Guide the cable through the opening (from the outside). Withdraw the cable approximately 20 mm (to improve strain relief)


MC-35/37-MULTI-67-PV-LG - Cable feed-through plates



1415240

<https://www.phoenixcontact.com/us/products/1415240>

Drawings



Dimensional drawing


MC-35/37-MULTI-67-PV-LG - Cable feed-through plates



1415240

<https://www.phoenixcontact.com/us/products/1415240>

Dimensional drawing



Wall cutout drawing

MC-35/37-MULTI-67-PV-LG - Cable feed-through plates



1415240

<https://www.phoenixcontact.com/us/products/1415240>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1415240>



EAC-RoHS

Approval ID: RU D-DE.HB35.B.00387

MC-35/37-MULTI-67-PV-LG - Cable feed-through plates



1415240

<https://www.phoenixcontact.com/us/products/1415240>

Classifications

ECLASS

ECLASS-13.0	27400569
ECLASS-15.0	27400569

ETIM

ETIM 10.0	EC001004
-----------	----------

UNSPSC

UNSPSC 21.0	31163000
-------------	----------

MC-35/37-MULTI-67-PV-LG - Cable feed-through plates



1415240

<https://www.phoenixcontact.com/us/products/1415240>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.895 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com