

MC-35-MULTI-65-PVO-BK - Cable feed-through plates



1422351

<https://www.phoenixcontact.com/us/products/1422351>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable feed-through plates, no. of conductors: 35, external cable diameter: 2x 6 mm ... 10 mm, 14x 8 mm ... 12 mm, 16x 10 mm ... 14 mm, 2x 12 mm ... 18 mm, 1x 17 mm ... 32 mm, material: galvanized sheet steel (Core), material: TPE-SEBS (external material), color: black, length: 222 mm, width: 92 mm, height: 17.6 mm

Your advantages

- Oil-resistant according to UL 157

Commercial data

Item number	1422351
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF67
Product key	AF7CAX
GTIN	4055626301860
Weight per piece (including packing)	299.2 g
Weight per piece (excluding packing)	299.2 g
Customs tariff number	39269097
Country of origin	FI

MC-35-MULTI-65-PVO-BK - Cable feed-through plates



1422351

<https://www.phoenixcontact.com/us/products/1422351>

Technical data

Notes

Order information:	incl. mounting screws
General	2 mm thick coated, galvanized sheet steel


Product properties

Product type	Cable feed-through
No. of conductors	35

Connection data

External cable diameter	2x 6 mm ... 10 mm
Tightening torque	1.5 Nm ... 2 Nm (Mounting screws)

Dimensions

Dimensional drawing	
Width	92 mm
Height	17.6 mm
Length	222 mm
Drill hole distance, horizontal	62 mm
Drill hole distance, vertical	193 mm
Hole diameter	8.5 mm

Material specifications

Color	black (RAL 9005)
Material interior	galvanized sheet steel (Core)
Material exterior	TPE-SEBS (external material)
Flammability rating according to UL 94	V0

Cable/line

External cable diameter 6-10 mm	2x 6 mm ... 10 mm
External cable diameter 8-12 mm	14x 8 mm ... 12 mm
External cable diameter 10-14 mm	16x 10 mm ... 14 mm
External cable diameter 12-18 mm	2x 12 mm ... 18 mm
External cable diameter 17-32 mm	1x 17 mm ... 32 mm

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65 (Minimum sheet thickness $\geq$ 2.5 mm)
----------------------	--

MC-35-MULTI-65-PVO-BK - Cable feed-through plates



1422351

<https://www.phoenixcontact.com/us/products/1422351>


Ambient temperature (operation)	-40 °C ... 100 °C
---------------------------------	-------------------

Mounting

Assembly note	M8 mounting screw, torque: 1.5 - 2.0 Nm, SW5 Allen key
	1. Place the multigate in an F21 cutout 2. Install the M8 screws and use M8 nuts if necessary (tightening torque: 1.5 Nm ... 2 Nm) 3. Using a knife or scissors, cut a hole with a diameter 20% smaller than the cable diameter you are using. You can also use a screwdriver (if the cable diameter is greater than 10 mm, use scissors) 4. Push the cable through the membrane from the front 5. Pull the cable back about 20 mm to secure it and ensure it stays in place

Drawings

Dimensional drawing



Wall cutout drawing

**PHOENIX
CONTACT**

<https://www.phoenixcontact.com/us/products/1422351>

Technical drawing of the 1000 Series 12V 100Ah battery, showing side and top views with dimensions in millimeters (mm).

Side View Dimensions:

- Overall Length: 222 mm
- Overall Height: 30 mm
- Terminal Height: 12,4 mm

Top View Dimensions:

- Overall Width: 92 mm
- Terminal Spacing (Left): 42 mm
- Terminal Spacing (Right): 30 mm
- Terminal Diameter: 62 mm
- Overall Length (Top): 194 mm
- Overall Length (Bottom): 154 mm
- Terminal Spacing (Bottom): 52 mm
- Terminal Spacing (Bottom): 86 mm
- Terminal Spacing (Bottom): 120 mm

Oct 4, 2026, 5:30□AM Page 5 (7)

MC-35-MULTI-65-PVO-BK - Cable feed-through plates



1422351

<https://www.phoenixcontact.com/us/products/1422351>

Classifications

ECLASS

ECLASS-15.0	27400569
ECLASS-13.0	27400569

ETIM

ETIM 10.0	EC001004
-----------	----------

UNSPSC

UNSPSC 21.0	31163000
-------------	----------

MC-35-MULTI-65-PVO-BK - Cable feed-through plates



1422351

<https://www.phoenixcontact.com/us/products/1422351>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.782 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com