

1425514

<https://www.phoenixcontact.com/us/products/1425514>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Power connector, degree of protection: IP65/IP67, number of positions: 5, material: Metal, connection method: Spring connection, connection cross section: AWG 18- 13, cable outlet: straight, Universal

Your advantages

- Flexible coding
- Increased temperature range
- Lockable
- One-part housing

Commercial data

Item number	1425514
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB17
Product key	ABNOHA
GTIN	4055626407234
Weight per piece (including packing)	111 g
Weight per piece (excluding packing)	116.745 g
Customs tariff number	85366990
Country of origin	PL

1425514

<https://www.phoenixcontact.com/us/products/1425514>

Technical data

Notes

General	This product corresponds to the PROFINET Cabling and Interconnection Technology Guideline for PROFINET regulations, version 2.00, order no: 2.252, Chapter 11 Connectors for 24 Volt Power Supply Cabling and Chapter 13 Application specific Cabling and Interconnection Technology (AIDA)
---------	---

Product properties

Product type	Data connector (cable side)
Type	MSTB
Number of positions	5
Connection profile	MSTB
Cable outlet	straight

Insulation characteristics

Overvoltage category	I
Degree of pollution	3

Electrical properties

Rated voltage (II/2)	630 V
Rated voltage (III/2)	400 V
Rated voltage (III/3)	24 V
	250 V
Rated surge voltage (II/2)	4 kV
Rated surge voltage (III/2)	4 kV
Rated surge voltage (III/3)	4 kV
Rated current	16 A (at 20 °C)
	16 A
Nominal voltage U_N	24 V
Nominal current I_N	16 A
Transmission medium	Copper
Power transmission	PoE

Connection data

Connection technology

Connection method	Spring connection
Connection cross section AWG	18 ... 13
Conductor cross-section	0.75 mm ² ... 2.5 mm ²

Interfaces

Signal type/category	Universal
----------------------	-----------

CUC-PPC-C2ZNI-SX/24FKP5:FC - Power connector



1425514

<https://www.phoenixcontact.com/us/products/1425514>

Dimensions

Width	31 mm
Height	36 mm
Length	67 mm

Material specifications

Material	Metal
Flammability rating according to UL 94	V0
Seal material	NBR
Housing material	Metal
Housing surface material	nickel-plated
Cable seal material	TPE
Contact material	Copper alloy
Contact surface material	Gold over nickel
Contact carrier material	PA

Cable/line

External cable diameter	9 mm ... 13 mm
Cable cross section	0.75 mm²

Environmental and real-life conditions

Ambient conditions


Degree of protection	IP65/IP67
Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Ambient temperature (assembly)	-10 °C ... 40 °C

1425514

<https://www.phoenixcontact.com/us/products/1425514>

Drawings

Schematic diagram



Pin assignment PROFINET push-pull, power connector, 24 V, flexible coding

Approvals

 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1425514>

 cULus Recognized Approval ID: E118976				
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
keine				
	24 V	16 A	- 14	-

CUC-PPC-C2ZNI-SX/24FKP5:FC - Power connector



1425514

<https://www.phoenixcontact.com/us/products/1425514>

Classifications

ECLASS

ECLASS-13.0	27440290
ECLASS-15.0	27440114

ETIM

ETIM 10.0	EC003083
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.1 Climate Change	
CO2e kg	2.433 kg CO2e