

# SACC-M 8MS-3QO-0,5-VA - Connector



1426313

<https://www.phoenixcontact.com/us/products/1426313>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Connector, 3-position, Plug straight M8, coding: A, Insulation displacement connection, knurl material: Stainless steel 1.4305, external cable diameter 2.5 mm ... 5 mm

## Your advantages

- Safe use in the field, thanks to a high degree of protection
- Insulation displacement connection: innovative and time-saving assembly without stripping the single wire

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1426313       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BF31          |
| Product key                          | AF2BCA        |
| GTIN                                 | 4055626457635 |
| Weight per piece (including packing) | 7.2 g         |
| Weight per piece (excluding packing) | 7 g           |
| Customs tariff number                | 85366990      |
| Country of origin                    | DE            |

# SACC-M 8MS-3QO-0,5-VA - Connector



1426313

<https://www.phoenixcontact.com/us/products/1426313>

## Technical data

### Notes

Assembly note

**NOTE:** Observe the permissible bending radii when routing cables, since the degree of protection may be at risk if the bending forces are too high. Reduce mechanical loads upstream of the connector, e.g., by using cable ties.

### Product properties


|                      |                                 |
|----------------------|---------------------------------|
| Product type         | Circular connector (cable-side) |
| Number of positions  | 3                               |
| No. of cable outlets | 1                               |
| Shielded             | no                              |
| Coding               | A                               |
| Cable outlet         | straight                        |

### Insulation characteristics

|                      |    |
|----------------------|----|
| Overvoltage category | II |
| Degree of pollution  | 3  |

### Dimensions

Dimensional drawing



Length

43.4 mm

### External dimensions

|                  |                              |
|------------------|------------------------------|
| Outside diameter | 2.5 mm ... 5 mm $\pm 0.2$ mm |
|------------------|------------------------------|

### Housing

|                  |         |
|------------------|---------|
| Diameter housing | 12.5 mm |
|------------------|---------|

### Material specifications

|                                        |                        |
|----------------------------------------|------------------------|
| Flammability rating according to UL 94 | HB                     |
| Seal material                          | NBR                    |
| Material of grip body                  | PA 6                   |
| Contact material                       | CuSn                   |
| Contact surface material               | Ni/Au                  |
| Contact carrier material               | TPU GF                 |
| Material for screw connection          | Stainless steel 1.4305 |
| Wire insulation material               | PVC / PE / PP / rubber |

### Connection data

Conductor connection

# SACC-M 8MS-3QO-0,5-VA - Connector



1426313

<https://www.phoenixcontact.com/us/products/1426313>

|                              |                                    |
|------------------------------|------------------------------------|
| Connection method            | Insulation displacement connection |
| Connection cross section     | 0.25 mm² ... 0.5 mm²               |
| Connection cross section AWG | 24 ... 20                          |
| Tightening torque            | 0.6 Nm (Pressure nut)              |
|                              | 0.2 Nm (M8 knurl)                  |

## Electrical properties

|                                |          |
|--------------------------------|----------|
| Rated surge voltage            | 0.8 kV   |
| Contact resistance             | ≤ 5 mΩ   |
| Insulation resistance          | ≥ 100 MΩ |
| Nominal voltage U <sub>N</sub> | 60 V AC  |
|                                | 60 V DC  |
| Nominal current I <sub>N</sub> | 4 A      |

## Mechanical properties

### Mechanical data

|                             |       |
|-----------------------------|-------|
| Insertion/withdrawal cycles | ≥ 100 |
|-----------------------------|-------|

## Connector

### Connection 1

|                   |          |
|-------------------|----------|
| Head design       | Plug     |
| Head cable outlet | straight |
| Head thread type  | M8       |
| Coding            | A        |

## Cable/line

|                         |                 |
|-------------------------|-----------------|
| External cable diameter | 2.5 mm ... 5 mm |
|-------------------------|-----------------|

## Environmental and real-life conditions

### Ambient conditions

|                                                                   |                                  |
|-------------------------------------------------------------------|----------------------------------|
| Degree of protection                                              | IP65                             |
|                                                                   | IP67                             |
|                                                                   | IP69K                            |
| Ambient temperature (operation) (male connector/female connector) | -25 °C ... 80 °C (Plug / socket) |

## Standards and regulations

### M8

|                          |                 |
|--------------------------|-----------------|
| Standard designation     | M8 connector    |
| Standards/specifications | IEC 61076-2-104 |


# SACC-M 8MS-3QO-0,5-VA - Connector

1426313

<https://www.phoenixcontact.com/us/products/1426313>


## Drawings

Dimensional drawing



M8 x 1 male plug, straight version

Functional drawing




# SACC-M 8MS-3QO-0,5-VA - Connector

1426313

<https://www.phoenixcontact.com/us/products/1426313>



Schematic diagram



Pin assignment M8 plug, 3-pos., view male side

# SACC-M 8MS-3QO-0,5-VA - Connector



1426313

<https://www.phoenixcontact.com/us/products/1426313>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27440116 |
| ECLASS-15.0 | 27440116 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC002635 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# SACC-M 8MS-3QO-0,5-VA - Connector



1426313

<https://www.phoenixcontact.com/us/products/1426313>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

### EF3.1 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 0.711 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)