

SACC-M 8MS-3CON-M-SH - Connector



1506901

<https://www.phoenixcontact.com/us/products/1506901>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Connector, Universal, 3-position, shielded, Plug straight M8, coding: A, Solder connection, knurl material: Brass, nickel-plated, external cable diameter 3.5 mm ... 5 mm

Your advantages

- Safe use in the field, thanks to a high degree of protection
- Reliable signal transmission – 360° shielding in environments with electromagnetic interference

Commercial data

Item number	1506901
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF35
Product key	AF2BJA
GTIN	4017918881191
Weight per piece (including packing)	19.62 g
Weight per piece (excluding packing)	17.625 g
Customs tariff number	85366990
Country of origin	DE

SACC-M 8MS-3CON-M-SH - Connector



1506901

<https://www.phoenixcontact.com/us/products/1506901>

Technical data

Notes

Assembly note

NOTE: Observe the permissible bending radii when routing cables, since the degree of protection may be at risk if the bending forces are too high. Reduce mechanical loads upstream of the connector, e.g., by using cable ties.

Product properties


Product type	Circular connector (cable-side)
Number of positions	3
No. of cable outlets	1
Shielded	yes
Coding	A

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Dimensions

Dimensional drawing



Length

50 mm

External dimensions

Outside diameter

3.5 mm ... 5 mm

Housing

Diameter housing

12 mm

Material specifications

Flammability rating according to UL 94	HB
Seal material	NBR
Material of grip body	Brass, nickel-plated
Contact material	CuZn
Contact surface material	Au
Contact carrier material	PA
Material for screw connection	Brass, nickel-plated

Connection data

Conductor connection

Connection method

Solder connection

SACC-M 8MS-3CON-M-SH - Connector



1506901

<https://www.phoenixcontact.com/us/products/1506901>

Connection cross section	0.08 mm ² ... 0.25 mm ² (flexible)
	0.08 mm ² ... 0.25 mm ² (solid)
Connection cross section AWG	28 ... 24 (flexible)
	28 ... 24 (solid)
Stripping length of the individual wire	3 mm
Tightening torque	0.2 Nm (M8 knurl)

Electrical properties

Rated surge voltage	0.8 kV
Contact resistance	≤ 3 mΩ
Insulation resistance	≥ 100 MΩ
Nominal voltage U _N	48 V AC
	60 V DC
Nominal current I _N	4 A

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 100
-----------------------------	-------

Connector

Connection 1

Head design	Plug
Head cable outlet	straight
Head thread type	M8
Coding	A

Interfaces

Signal type/category	Universal
----------------------	-----------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation) (male connector/female connector)	-40 °C ... 85 °C (Plug / socket)

Standards and regulations

Standard designation	M8 connector
Standards/specifications	IEC 61076-2-104

SACC-M 8MS-3CON-M-SH - Connector




1506901

<https://www.phoenixcontact.com/us/products/1506901>


Drawings

Dimensional drawing



Plug M8 x 1, straight, shielded

Functional drawing



Assembly steps for M8 male/female plug and conductor


SACC-M 8MS-3CON-M-SH - Connector

1506901

<https://www.phoenixcontact.com/us/products/1506901>




Schematic diagram



Pin assignment M8 plug, 3-pos., view male side

Diagram

**Attenuation curve of the SACC... male/female connectors**

SACC-M 8MS-3CON-M-SH - Connector



1506901

<https://www.phoenixcontact.com/us/products/1506901>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1506901>

	 UL Listed Approval ID: FILE E 221474			
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
keine				
	60 V	4 A	-	-

	 cUL Listed Approval ID: FILE E 221474			
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
keine				
	60 V	4 A	-	-

SACC-M 8MS-3CON-M-SH - Connector



1506901

<https://www.phoenixcontact.com/us/products/1506901>

Classifications

ECLASS

ECLASS-13.0	27440116
ECLASS-15.0	27440116

ETIM

ETIM 10.0	EC002635
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SACC-M 8MS-3CON-M-SH - Connector



1506901

<https://www.phoenixcontact.com/us/products/1506901>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	97fcf87d-9863-4fef-9c84-3c9f3af85d38

EF3.1 Climate Change

CO2e kg	1.271 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com