SACC-E-MINMS-5CON-PG13/0,5 - Device connector front mounting

1521452

https://www.phoenixcontact.com/us/products/1521452

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator flush-type plug, 5-pos., 7/8", front mounting with Pg13.5 thread, with 0.5 m PVC litz wire, 5 x 0.75 mm^2

Commercial data

Item number	1521452
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB39
Product key	ABRSAA
GTIN	4017918949679
Weight per piece (including packing)	74.8 g
Weight per piece (excluding packing)	52.1 g
Customs tariff number	85366990
Country of origin	DE

Technical data

Mounting

Mounting type	Front mounting (Pg13,5)

Product properties

Product type	Circular connectors (device side)
Number of positions	5
No. of cable outlets	1
Shielded	no
Coding	A
Thread type	7/8"

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Material specifications

Flammability rating according to UL 94	HB
Material grommet GRP	Viton
Contact material	CuZn
Contact surface material	Au
Contact carrier material	PUR
Material for screw connection	Zinc die-cast, nickel-plated

Electrical properties

Contact resistance	≤ 5 mΩ
Insulation resistance	≥ 100 MΩ
Nominal voltage U_N	250 V
Nominal current I_N	9 A

Connection data

Conductor connection

Connection method	Individual wires
Contact connection type	Socket
Conductor cross-section	0.75 mm²

Connector

Connection 1

Head design	Pin
Head cable outlet	straight
Head thread type	7/8"-16UNF

Connection 2

Head design	free cable end

Cable/line

Cable length	0.5 m
Cable type	PVC litz wire
Wire diameter incl. insulation	2.7 mm
Single wire, color	brown, white, blue, black, green-yellow
Cable cross section	0.75 mm²
Conductor structure signal line	24x 0.20 mm
AWG signal line	18
Material wire insulation	PE
Thickness, insulation	0.85 mm (Core insulation)


Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
	IP67
Ambient temperature (operation) (male connector/female connector)	-40 °C ... 85 °C (Plug)
Ambient temperature (operation) (fixed installation)	-40 °C ... 85 °C (cable, fixed installation)


Drawings

Dimensional drawing




Dimensional drawing

Dimensional drawing




Mounting panel with thread

Dimensional drawing



Mounting panel with feed-through hole

Schematic diagram



Pin assignment, plug, 7/8"-16UNF, 5-pos., view of male side

Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/1521452

cUL Recognized
Approval ID: E221474-20070307

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	600 V	8 A	20	-

UL Recognized
Approval ID: E221474-20070307

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	600 V	8 A	20	-

Classifications

ECLASS

ECLASS-13.0	27440103
ECLASS-15.0	27440103

ETIM

ETIM 10.0	EC003570

UNSPSC

UNSPSC 21.0	39121400

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	50f4497e-8cf7-46c0-a056-b8c44bde640c

EF3.1 Climate Change

CO2e kg	1.469 kg CO2e

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com