

# SACC-EC-M12MS-8CON-PG9/0,5 - Device connector front mounting



1513787

<https://www.phoenixcontact.com/us/products/1513787>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector front mounting, Universal, 8-position, Pin, straight, M12-Standard, A-coding, on free cable end, Individual wires, cable length: 0.5 m, 0.25 mm<sup>2</sup>, TPE litz wire, potted, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

## Your advantages

- Preassembled with litz wires for immediate use
- Customer-specific assemblies and litz wire lengths available
- Sealed on the litz wire side for optimum leak-tightness
- For high transmission safety: shield connection to the housing with optional EMC nut

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1513787       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | AB24          |
| Product key                          | ABQCEE        |
| GTIN                                 | 4017918914677 |
| Weight per piece (including packing) | 29.23 g       |
| Weight per piece (excluding packing) | 27.377 g      |
| Customs tariff number                | 85444290      |
| Country of origin                    | DE            |

# SACC-EC-M12MS-8CON-PG9/0,5 - Device connector front mounting



1513787

<https://www.phoenixcontact.com/us/products/1513787>

## Technical data

### Notes

|                    |                                                                                                                                                                                                                                                                                                                                                    |
|--------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Notes on operation | The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration. |
| Order information: | Positioning nut is included in the scope of supply                                                                                                                                                                                                                                                                                                 |
| General            | Contact connection method: Crimp connection                                                                                                                                                                                                                                                                                                        |

### Mounting

|                   |                                        |
|-------------------|----------------------------------------|
| Mounting type     | Front mounting (Pg9, with locking nut) |
| Tightening torque | 2 Nm ... 3 Nm (Installation-side)      |

### Product properties

|                      |                                   |
|----------------------|-----------------------------------|
| Product type         | Circular connectors (device side) |
| Application          | Signal                            |
| Number of positions  | 8                                 |
| No. of cable outlets | 1                                 |
| Shielded             | no                                |
| Coding               | A                                 |
| Thread type          | M12                               |

### Insulation characteristics

|                      |    |
|----------------------|----|
| Overvoltage category | II |
| Degree of pollution  | 3  |

### Material specifications

|                                        |                              |
|----------------------------------------|------------------------------|
| Material Molding compound              | PUR (potted)                 |
| Flammability rating according to UL 94 | V0                           |
| Seal material                          | NBR                          |
| Material of grip body                  | Zinc die-cast, nickel-plated |
| Contact material                       | CuZn                         |
| Contact surface material               | Ni/Au                        |
| Contact carrier material               | PA 66                        |
| Material for screw connection          | Zinc die-cast, nickel-plated |
| Conductor material                     | Tin-plated Cu litz wires     |

### Electrical properties

|                       |                            |
|-----------------------|----------------------------|
| Rated surge voltage   | 0.8 kV                     |
| Contact resistance    | $\leq 3 \text{ m}\Omega$   |
| Insulation resistance | $\geq 100 \text{ M}\Omega$ |

# SACC-EC-M12MS-8CON-PG9/0,5 - Device connector front mounting



1513787

<https://www.phoenixcontact.com/us/products/1513787>

|                           |                  |
|---------------------------|------------------|
| Nominal voltage $U_N$     | 30 V (AC)        |
|                           | 30 V (DC)        |
| Nominal current $I_N$     | 2 A              |
| Max. conductor resistance | 80 m $\Omega$ /m |

## Connection data

### Conductor connection

|                         |                                   |
|-------------------------|-----------------------------------|
| Connection method       | Individual wires                  |
| Contact connection type | Pin                               |
| Conductor cross-section | 0.25 mm <sup>2</sup>              |
| Tightening torque       | 2 Nm ... 3 Nm (Installation-side) |

## Mechanical properties

### Mechanical data

|                             |       |
|-----------------------------|-------|
| Insertion/withdrawal cycles | > 100 |
|-----------------------------|-------|

## Interfaces

|                      |           |
|----------------------|-----------|
| Signal type/category | Universal |
|----------------------|-----------|

## Connector

### Connection 1

|                   |          |
|-------------------|----------|
| Head design       | Pin      |
| Head cable outlet | straight |
| Head thread type  | M12      |
| Head locking type | Standard |
| Coding            | A        |

### Connection 2

|             |                |
|-------------|----------------|
| Head design | free cable end |
|-------------|----------------|

## Cable/line

|                                 |                                                    |
|---------------------------------|----------------------------------------------------|
| Cable length                    | 0.5 m                                              |
| Cable type                      | TPE litz wire                                      |
| Wire diameter incl. insulation  | 1.15 mm $\pm$ 0.07 mm                              |
| Single wire, color              | brown, blue, white, gray, pink, green, yellow, red |
| Cable cross section             | 0.25 mm <sup>2</sup>                               |
| Conductor material              | Tin-plated Cu litz wires                           |
| Conductor structure signal line | 14x 0.15 mm                                        |
| AWG signal line                 | 24                                                 |
| Material wire insulation        | TPE                                                |
| Thickness, insulation           | 0.21 mm (Core insulation)                          |
| Nominal voltage, cable          | 300 V                                              |

# SACC-EC-M12MS-8CON-PG9/0,5 - Device connector front mounting



1513787

<https://www.phoenixcontact.com/us/products/1513787>

|                                 |                                                 |
|---------------------------------|-------------------------------------------------|
| Test voltage, cable             | 2000 V AC                                       |
| Cable resistance                | $\leq 80 \text{ m}\Omega/\text{m}$              |
| Cable insulation resistance     | $\geq 20 \text{ M}\Omega \cdot \text{km}$       |
| Ambient temperature (operation) | -40 °C ... 85 °C (cable, fixed installation)    |
|                                 | -25 °C ... 85 °C (Cable, flexible installation) |

## Environmental and real-life conditions

### Ambient conditions

|                                                                   |                                                 |
|-------------------------------------------------------------------|-------------------------------------------------|
| Degree of protection                                              | IP67                                            |
| Ambient temperature (operation) (male connector/female connector) | -25 °C ... 85 °C (Plug / socket)                |
|                                                                   | -40 °C ... 85 °C (without mechanical actuation) |
| Ambient temperature (operation) (Cable, flexible installation)    | -25 °C ... 85 °C (Cable, flexible installation) |
| Ambient temperature (operation) (Cable, fixed installation)       | -40 °C ... 85 °C (cable, fixed installation)    |
| UL Type Rating                                                    | Type 4 (indoor use only)                        |

## Standards and regulations

|                          |                              |
|--------------------------|------------------------------|
| Standard designation     | M12 circular connector       |
| Standards/specifications | according to IEC 61076-2-101 |

# SACC-EC-M12MS-8CON-PG9/0,5 - Device connector front mounting




1513787

<https://www.phoenixcontact.com/us/products/1513787>


## Drawings

Schematic diagram



Pin assignment M12 plug, 8-pos., view plug side

Circuit diagram



Contact assignment of the M12 plug and the M12 socket

# SACC-EC-M12MS-8CON-PG9/0,5 - Device connector front mounting



1513787

<https://www.phoenixcontact.com/us/products/1513787>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1513787>

|  <b>UL Recognized</b><br>Approval ID: E118976-20100522 |                                |                                |                   |                               |
|-----------------------------------------------------------------------------------------------------------------------------------------|--------------------------------|--------------------------------|-------------------|-------------------------------|
|                                                                                                                                         | Nominal voltage U <sub>N</sub> | Nominal current I <sub>N</sub> | Cross section AWG | Cross section mm <sup>2</sup> |
| keine                                                                                                                                   |                                |                                |                   |                               |
|                                                                                                                                         | 30 V                           | 2 A                            | 24                | -                             |

|  <b>cULus Recognized</b><br>Approval ID: E221474-20140616 |                                |                                |                   |                               |
|--------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------|--------------------------------|-------------------|-------------------------------|
|                                                                                                                                            | Nominal voltage U <sub>N</sub> | Nominal current I <sub>N</sub> | Cross section AWG | Cross section mm <sup>2</sup> |
| keine                                                                                                                                      |                                |                                |                   |                               |
|                                                                                                                                            | 30 V                           | 2 A                            | 24 - 22           | -                             |

# SACC-EC-M12MS-8CON-PG9/0,5 - Device connector front mounting



1513787

<https://www.phoenixcontact.com/us/products/1513787>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27440103 |
| ECLASS-15.0 | 27440103 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC003570 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# SACC-EC-M12MS-8CON-PG9/0,5 - Device connector front mounting



1513787

<https://www.phoenixcontact.com/us/products/1513787>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)