# HC-A04-I-UT-M - Contact insert

1585236

https://www.phoenixcontact.com/us/products/1585236

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact insert, number of positions: 4+PE, size: D7, number of connections per position: 1, Pin, Screw connection, 230 V/400 V, 10 A, 0.5 $mm^2$ ... 2.5 $mm^2$

## Product description

Contact insert
without wire protection, with IP65 sealing screw

## Your advantages

- Shock and vibration-resistant in accordance with DIN EN 61373

## Commercial data

| | |
|---|---|
| Item number | 1585236 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BF61 |
| Product key | AF7ABJ |
| GTIN | 4046356284967 |
| Weight per piece (including packing) | 16.7 g |
| Weight per piece (excluding packing) | 14.3 g |
| Customs tariff number | 85366990 |
| Country of origin | CN |

## Technical data

### Notes

| | |
|---|---|
| General | for housing HC-D7 |
| General | Connectors may be operated only when there is no load/voltage. |

### Mounting

| | |
|---|---|
| Assembly note | To ensure correct use, installation in housing with IP54 protection or better is required |
| | Already includes one IP65 sealing screw |


### Product properties

| | |
|---|---|
| Product type | Contact insert with a fixed no. of positions |
| Series | HC-A |
| Type | D7 |
| Number of positions | 4 |
| Connection profile | 4+PE |
| Contact numbering | 1 - 4 |
| Number of connections per position | 1 |
| Contact material type | turned |
| Screwdriver blade | 0.4 x 2.5 mm |

#### Insulation characteristics

| | |
|---|---|
| Overvoltage category | III |
| Degree of pollution | 3 |

### Dimensions

| | |
|---|---|
| Dimensional drawing |   |
| Width | 28 mm |
| Height | 28.5 mm |
| Length | 21 mm |

#### Mechanical characteristics

| | |
|---|---|
| Contact diameter | 1.6 mm |

### Connection data

#### Connection technology

| | |
|---|---|
| Connection technology | Screw connection |
| Number of connections per position | 1 |
| Connection in acc. with standard | IEC / EN |

Conductor connection

| | |
|---|---|
| Conductor cross-section | 0.5 mm² ... 2.5 mm² |
| Connection cross section AWG | 20 ... 14 |
| Tightening torque | 0.5 Nm ... 0.8 Nm (Mounting screws for mounting in the HEAVYCON housing) |
| | 0.25 Nm ... 0.5 Nm |
| Stripping length of the individual wire | 5 mm |

## Electrical properties

| | |
|---|---|
| Rated voltage (III/3) | 230 V (Conductor-PE) |
| | 400 V (Conductor-Conductor) |
| Rated voltage for power contacts | 230/400 V |
| Rated surge voltage | 4 kV |
| | 4 kV |
| Rated current | 10 A |
| SCCR | 5 kA (UL 2237) |

## Mechanical properties

Mechanical data

| | |
|---|---|
| Insertion/withdrawal cycles | ≥ 500 |

## Material specifications

| | |
|---|---|
| Flammability rating according to UL 94 | V0 |
| Material grommet GRP | NBR, conductive (profile gasket) |
| Contact material | Copper alloy |
| Contact surface material | Ag |
| Contact carrier material | PC |

## Environmental and real-life conditions

Ambient conditions


| | |
|---|---|
| Ambient temperature (operation) | -40 °C ... 125 °C (including heating up of contacts) |

## Standards and regulations

| | |
|---|---|
| Constructional and testing regulations | IEC 61984:2008 |
| | IEC 60664-1:2007 |
| | IEC 60664-1, DIN IEC 60512 |
| Tests | IEC 61984:2008 |
| | IEC 60664-1:2007 |
| | IEC 60664-1, DIN IEC 60512 |
| Standards/regulations | PC: Fire protection in rail vehicles - requirement sets R22, R23, and R24 acc. to DIN EN 45545-2 (Risk level HL1 - HL3) |


## Drawings

Dimensional drawing





Male insert

Schematic diagram




Connector pin assignment connection side: Left pin; right socket

Diagram




Derating diagram

## Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/1585236

**DNV**
Approval ID: TAE000037S

**CSA**
Approval ID: 158887

| | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $mm^2$ |
|---|---|---|---|---|
| keine | | | | |
| | 600 V | 18 A | - 14 | - |

**UL Recognized**
Approval ID: E118976

| | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $mm^2$ |
|---|---|---|---|---|
| keine | | | | |
| | 600 V | 24 A | - | - |

**UL Recognized**
Approval ID: E468743

| | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $mm^2$ |
|---|---|---|---|---|
| keine | | | | |
| | 600 V | 24 A | - | - |

## Classifications

### ECLASS

| | |
|---|---|
| ECLASS-13.0 | 27440205 |
| ECLASS-15.0 | 27440205 |

### ETIM

| | |
|---|---|
| ETIM 10.0 | EC000438 |

### UNSPSC

| | |
|---|---|
| UNSPSC 21.0 | 39121500 |

## Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |

China RoHS

| | |
|---|---|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|---|---|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |


Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com



Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com