

EV-T2G3PC-3AC20A-4,0M2,5EHBK01 - AC charging cable



1627135

<https://www.phoenixcontact.com/us/products/1627135>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



CHARX connect comfort, Type 2, Mobile AC charging cable, 20 A permanent, 480 V AC, with vehicle charging connector and infrastructure charging plug, cable: 4 m, black, spiraled, with protective cap, housing: black, gray, PHOENIX CONTACT logo, IEC 62196-2, for charging electric vehicles (EV) with alternating current (AC) via type 2 vehicle charging inlets

Product description

Mobile AC charging cable with vehicle charging connector and infrastructure charging plug for charging electric vehicles (EV) with alternating current (AC) via type 2 vehicle charging inlets, compatible with type 2 infrastructure charging sockets at charging stations for e-mobility (EVSE)

Your advantages

- Complete product range
- Convenient handling due to the ergonomic, triple award-winning design
- Available with your logo on request - for consistent branding of your charging station
- Longitudinal water tightness reliably prevents water ingress
- Developed and produced in accordance with the IATF 16949 automotive standard and ISO 9001
- Tested in accordance with automotive standards LV124, LV214, and LV215-2
- Tested in accordance with EV Ready 37 requirements
- Laser-marked mating face in accordance with DIN EN 17186

Commercial data

Item number	1627135
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	XWBEBC
GTIN	4055626299471
Weight per piece (including packing)	2,653 g
Weight per piece (excluding packing)	2,498 g
Country of origin	PL

EV-T2G3PC-3AC20A-4,0M2,5EHBK01 - AC charging cable



1627135

<https://www.phoenixcontact.com/us/products/1627135>

Technical data

Product properties

Product type	AC charging cable
Product family	CHARX connect comfort
Type	Mobile AC charging cable with vehicle charging connector and infrastructure charging plug
Design	with protective cap
Charging standard	Type 2
Charging mode	Mode 3, Case B
Affixed logo	PHOENIX CONTACT logo
Customer variations	On request

Electrical properties

Charging power and current (AC charging, 3-phase)

Type of charging current	AC 3-phase
Charging current	20 A AC (3-phase)
Charging power	16.63 kW (3-phase)
Charging power rating	11 W (3-phase, 2.5 mm ²)
Operating voltage	typ. 400 V AC
Rated voltage	480 V

Pin assignment (Power contacts)

Note on the connection method	Crimp connection, cannot be disconnected
Number	5 (L1, L2, L3, N, PE)
Rated voltage	480 V AC
Rated current	20 A


Pin assignment (Signal contacts)

Note on the connection method	Crimp connection, cannot be disconnected
Type of signal transmission	Pulse width modulation
Number	2 (CP, PP)
Rated voltage	30 V AC
Rated current	2 A
Coding	680 Ω (between PE and PP)

Dimensions

Infrastructure charging plug

Dimensional drawing



EV-T2G3PC-3AC20A-4,0M2,5EHBK01 - AC charging cable




1627135

<https://www.phoenixcontact.com/us/products/1627135>

	Infrastructure plug
Width	58 mm
Height	131.8 mm
Depth	215.9 mm

Vehicle charging connector

Dimensional drawing	
	Vehicle connector
Width	70 mm
Height	137 mm
Depth	215.9 mm

Material specifications

Color (Housing)	black (9005)
Color (Handle area)	gray (7042)
Color (Mating face)	black (9005)
Color (Protective cap)	black (9005)
Color (Cable)	black (9005)
Material (Vehicle charging connector)	Plastic
Material (Infrastructure charging plug)	Plastic
Material (Cable outer sheath)	TPE-U
Material (Contact surface)	Silver
Note	The color appearance and gloss level of the charging cable may vary.

Cable/line

Cable length	4 m
Wiring standards/regulations	prEN 50620/DIN EN 50620
Wiring certifications	VDE
Cable type	Class 5
Cable type	spiraled
Cable structure	5 x 2.5 mm ² + 1 x 0.5 mm ²
External cable diameter	12.80 mm ±0.4 mm
Outer sheath, material	TPE-U
Block length	0.63 m ±10 %
Coil diameter	60 mm ±10 %
Effective length	max. 4 m ±5 %
Cable resistance	≤ 0.00798 Ω/m (based on a power core, at an ambient

EV-T2G3PC-3AC20A-4,0M2,5EHBK01 - AC charging cable



1627135

<https://www.phoenixcontact.com/us/products/1627135>

	temperature of 20°C)
Bending radius	min. 192 mm (15x diameter)

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	> 10000
Insertion force	< 100 N
Withdrawal force	< 100 N

Environmental and real-life conditions

Ambient conditions

Degree of protection (Vehicle charging connector)	IP44 (plugged in; when plugged in and ready to operate, the degree of protection is only ensued if both plug-in components are original products from Phoenix Contact or suitable standard-compliant products)
Degree of protection (Infrastructure charging plug)	IP44 (plugged in; when plugged in and ready to operate, the degree of protection is only ensued if both plug-in components are original products from Phoenix Contact or suitable standard-compliant products)
Degree of protection (Protective cap)	IP54
Ambient temperature (operation)	-40 °C ... 50 °C
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Altitude	5000 m (above sea level)

Standards and regulations

Standards/specifications	IEC 62196-2
Note	Compliant with AFIR - EU 2025/656

EV-T2G3PC-3AC20A-4,0M2,5EHBK01 - AC charging cable




1627135

<https://www.phoenixcontact.com/us/products/1627135>


Drawings

Dimensional drawing



Vehicle connector

Dimensional drawing




Infrastructure plug

EV-T2G3PC-3AC20A-4,0M2,5EHBK01 - AC charging cable

1627135

<https://www.phoenixcontact.com/us/products/1627135>

Connection diagram



Pin assignment of Infrastructure Plug

EV-T2G3PC-3AC20A-4,0M2,5EHBK01 - AC charging cable


1627135

<https://www.phoenixcontact.com/us/products/1627135>


Schematic diagram




[I]



[II]



[III]



[IV]



[V]

Operating instructions


EV-T2G3PC-3AC20A-4,0M2,5EHBK01 - AC charging cable



1627135


<https://www.phoenixcontact.com/us/products/1627135>

Schematic diagram



Pin assignment of the Vehicle Connector

Schematic diagram



Terminology definition

EV-T2G3PC-3AC20A-4,0M2,5EHBK01 - AC charging cable



1627135
<https://www.phoenixcontact.com/us/products/1627135>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1627135>

	IECEE CB Scheme Approval ID: DE1-65890			
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
keine				
	480 V	20 A	-	-

EV-T2G3PC-3AC20A-4,0M2,5EHBK01 - AC charging cable



1627135
<https://www.phoenixcontact.com/us/products/1627135>

Classifications

ECLASS

ECLASS-13.0	27144705
ECLASS-15.0	27144705

ETIM

ETIM 10.0	EC002897
-----------	----------

UNSPSC

UNSPSC 21.0	39121500
-------------	----------

EV-T2G3PC-3AC20A-4,0M2,5EHBK01 - AC charging cable



1627135

<https://www.phoenixcontact.com/us/products/1627135>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	93fe8f82-bc01-46ad-879b-cb522c046e7c

EF3.1 Climate Change

CO2e kg	33.03 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com