

CA-1RS1N8A8008 - Cable connector



1623840

<https://www.phoenixcontact.com/us/products/1623840>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows the product with assembled crimp contacts. Please order crimp contacts separately.

M23, Cable connector, application: Signal, series: CA, straight, shielded: yes, Screw locking mechanism, No. of pos.: 16+2+FE, Direction of rotation: Standard, contact connection type: Socket, Crimp connection, cable diameter range: 10 mm ... 14.5 mm, coding: N. This product is in the process of being discontinued. This product must no longer be considered for new projects. Please contact your sales representative for alternatives. Alternative products: 1629197

Your advantages

- Safe use in the field, thanks to high degree of protection
- Connector for flexible on-site assembly
- Consistent EMC protection for reliable transmission of signals
- Crimping connection: vibration- and temperature-resistant assembly

Commercial data

Item number	1623840
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB31
Product key	ABRAEA
GTIN	4055626228532
Weight per piece (including packing)	90 g
Weight per piece (excluding packing)	84.769 g
Customs tariff number	85366990
Country of origin	DE

CA-1RS1N8A8008 - Cable connector



1623840

<https://www.phoenixcontact.com/us/products/1623840>

Technical data

Notes

Order information:	Order crimp contacts 16 x Ø 1 mm, 3 x Ø 1.5 mm separately
--------------------	---

Product properties

Product type	Circular connector (cable-side)
--------------	---------------------------------

Connector

Connection 1

Head design	Socket
-------------	--------

Insulating body

Note	Order information: Order crimp contacts 16 x Ø 1 mm, 3 x Ø 1.5 mm separately	
Coding	N	
Material (Insulating body)	PA 6.6	
Flammability rating according to UL 94	V0	
Insertion/withdrawal cycles	100	
Connection method	Crimp connection	
Contact switching type	Socket	
Application	Signal	
Number of positions	19	
Direction of rotation	Standard	
Connection profile	16+2+FE	
Installation height	2000 m	
Number (Contact group 1)	3	
Contact diameter (Contact group 1)	1.5 mm	
Litz wires Min. cross section (Contact group 1)	0.08 mm ²	
Litz wires Max. cross section (Contact group 1)	1 mm ²	
Rated current Contact (Contact group 1)	10 A (for max. connection cross section)	
Rated voltage Contact (Contact group 1)	48 V AC	
	74 V DC	
Rated surge voltage	1.5 kV	
Overvoltage category	II	
Degree of pollution	3	
Number (Contact group 2)	16	
Contact diameter (Contact group 2)	1 mm	
Litz wires Max. cross section (Contact group 2)	1 mm ²	
Rated current Contact (Contact group 2)	8 A (for max. connection cross section)	
Rated voltage Contact (Contact group 2)	48 V AC	
	48 V AC	
Rated surge voltage	1.5 kV	
Overvoltage category	III	

CA-1RS1N8A8008 - Cable connector



1623840

<https://www.phoenixcontact.com/us/products/1623840>

Degree of pollution	3
---------------------	---

Housing


Type	Cable connector housing
Thread type	M23
Design	straight
Type of locking	Screw locking mechanism
Pg screw connection	none
Material (Housing)	CuZn (Rotating parts)
	GD-Zn (Die-cast parts)
Material (Screw connection)	CuZn
Degree of protection (plugged in)	IP67

Seal

External cable diameter	10 mm ... 14.5 mm
Seal material	NBR

Drawings

Schematic diagram



Connector pin assignment

CA-1RS1N8A8008 - Cable connector



1623840

<https://www.phoenixcontact.com/us/products/1623840>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1623840>

 cUL Recognized Approval ID: E335019-20141210				
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
keine				
Power	48 V	6 A	18	-
Signal	48 V	5 A	18	-

 UL Recognized Approval ID: E335019-20141210				
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
keine				
Power	48 V	10 A	18	-
Signal	48 V	8 A	18	-

CA-1RS1N8A8008 - Cable connector



1623840

<https://www.phoenixcontact.com/us/products/1623840>

Classifications

ECLASS

ECLASS-13.0	27440116
ECLASS-15.0	27440116

ETIM

ETIM 10.0	EC002635
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

CA-1RS1N8A8008 - Cable connector



1623840

<https://www.phoenixcontact.com/us/products/1623840>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com