

CK4,0-ED-6,00ST AG - Crimp contact



1663268

<https://www.phoenixcontact.com/us/products/1663268>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimp contact, Pin, turned, contact diameter: 4 mm, rated current: 40 A, connection cross section: 6 mm² ... 6 mm², AWG 10...10 , contact material: Cu alloy

Commercial data

Item number	1663268
Packing unit	25 pc
Minimum order quantity	25 pc
Sales key	BF65
Product key	AF7AIE
GTIN	4017918123079
Weight per piece (including packing)	3.1 g
Weight per piece (excluding packing)	3.1 g
Customs tariff number	85366990
Country of origin	DE

CK4,0-ED-6,00ST AG - Crimp contact



1663268

<https://www.phoenixcontact.com/us/products/1663268>

Technical data

Notes

Notes on the product family	for HC-M-02, HC-M-03, HC-M-03/04, HC-M-04, HC-Q02, HC-Q03, HC-Q04, and HC-COM-Q4/2 contact carriers
Assembly note	The quality of a crimp connection is determined by DIN EN 60352-2.
Assembly note	Note on crimp connection technology: For flexible wires only. The specified conductor cross-sections refer to the nominal cross-section of the cable used. The wiring space of the crimp connection technology is designed for fine-stranded cables in accordance with VDE 0295 Class 5. Deviating cable structures (e.g., Class 1.2 and 6 or AWG cables) should be checked before use.

Product properties

Product type	Crimp contact
Contact material type	turned

Connection data


Connection technology	
Contact connection type	Pin
Connection method	Crimp connection

Conductor connection	
Stripping length	10 mm
Connection cross section	6 mm ² ... 6 mm ²
Connection cross section AWG	10 ... 10

Material specifications

Material Contact	Cu alloy
Material Contact surface	Ag

Dimensions

Dimensional drawing	
Diameter (Contact diameter)	4 mm

Electrical properties

Rated current	40 A (Take into account the derating of the contact insert used. The rated current corresponds to the maximum possible connection cross-section.)
---------------	---

Mechanical properties

CK4,0-ED-6,00ST AG - Crimp contact



1663268

<https://www.phoenixcontact.com/us/products/1663268>

Mechanical data

Insertion/withdrawal cycles	≥ 500
-----------------------------	-------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------


CK4,0-ED-6,00ST AG - Crimp contact

1663268

<https://www.phoenixcontact.com/us/products/1663268>



Drawings



Dimensional drawing

CK4,0-ED-6,00ST AG - Crimp contact

1663268

<https://www.phoenixcontact.com/us/products/1663268>



Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1663268>



EAC

Approval ID: RU C-DE.AI30.B.01102

CK4,0-ED-6,00ST AG - Crimp contact

1663268

<https://www.phoenixcontact.com/us/products/1663268>



Classifications

ECLASS

ECLASS-13.0	27440204
ECLASS-15.0	27440204

ETIM

ETIM 10.0	EC000796
-----------	----------

UNSPSC

UNSPSC 21.0	39121500
-------------	----------

CK4,0-ED-6,00ST AG - Crimp contact



1663268

<https://www.phoenixcontact.com/us/products/1663268>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.1 Climate Change	
CO2e kg	0.049 kg CO2e

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com