


VS-15-BU-DSUB/16-MPT-0,5 - D-SUB contact insert



1688094

<https://www.phoenixcontact.com/us/products/1688094>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



D-SUB contact insert, shell size 2, with 15 signal contacts, female type of contact, screw connection, straight, for panel mounting frame and sleeve housing with IP67 protection

Commercial data

Item number	1688094
Packing unit	10 pc
Minimum order quantity	1 pc
Sales key	AB19
Product key	ABNCAB
GTIN	4017918179571
Weight per piece (including packing)	18.59 g
Weight per piece (excluding packing)	18.48 g
Customs tariff number	85366990
Country of origin	DE

VS-15-BU-DSUB/16-MPT-0,5 - D-SUB contact insert



1688094

<https://www.phoenixcontact.com/us/products/1688094>

Technical data

Product properties

Product type	Contact insert
Type	D-SUB
Number of positions	15
Connection profile	D-SUB
Number of slots	1
Shielded	yes

Insulation characteristics

Overvoltage category	III
Degree of pollution	2

Electrical properties

Rated voltage (III/3)	60 V
Rated current	5 A
Insulation resistance	$\geq 5000 \text{ M}\Omega$
Contact resistance per contact pair	$\leq 2.5 \text{ m}\Omega$
Transmission medium	Copper
Power transmission	Power

Connection data

Connection method	Screw connection
-------------------	------------------

Dimensions

Width	32.1 mm
Height	48 mm
Length	13 mm

Material specifications

Flammability rating according to UL 94	V0
Housing material	Metal
Housing surface material	metal-plated
Contact material	Copper alloy
Contact surface material	Gold
Contact carrier material	PBTP

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≤ 200
Insertion force per signal contact	$\leq 3.30 \text{ N}$
Extraction force per signal contact	$\leq 2.2 \text{ N}$

VS-15-BU-DSUB/16-MPT-0,5 - D-SUB contact insert



1688094

<https://www.phoenixcontact.com/us/products/1688094>

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-20 °C ... 80 °C

Mounting

Mounting type	Screw mounting
---------------	----------------

VS-15-BU-DSUB/16-MPT-0,5 - D-SUB contact insert


1688094

<https://www.phoenixcontact.com/us/products/1688094>



Drawings

Circuit diagram



Circuit diagram

VS-15-BU-DSUB/16-MPT-0,5 - D-SUB contact insert



1688094

<https://www.phoenixcontact.com/us/products/1688094>

Classifications

ECLASS

ECLASS-13.0	27440302
ECLASS-15.0	27440323

ETIM

ETIM 10.0	EC001132
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	cab0c6ba-8a24-40d8-acda-ab926b35155b

EF3.1 Climate Change

CO2e kg	1.296 kg CO2e
---------	---------------