


# FLKMS-D25 SUB/S - Termination board



2281720  
<https://www.phoenixcontact.com/us/products/2281720>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Termination board, connection 1: D-SUB pin strip 1x 25-position, connection 2: Screw connection 27-position

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 2281720                        |
| Packing unit                         | 5 pc                           |
| Minimum order quantity               | 1 pc                           |
| Note                                 | Made to order (non-returnable) |
| Sales key                            | C422                           |
| Product key                          | DK2182                         |
| GTIN                                 | 4017918054977                  |
| Weight per piece (including packing) | 168.58 g                       |
| Weight per piece (excluding packing) | 168.58 g                       |
| Customs tariff number                | 85369010                       |
| Country of origin                    | DE                             |

# FLKMS-D25 SUB/S - Termination board



2281720

<https://www.phoenixcontact.com/us/products/2281720>

## Technical data

### Product properties

|                |                       |
|----------------|-----------------------|
| Product type   | Interface module      |
| Product family | VARIOFACE             |
| Operating mode | 100% operating factor |

### Insulation characteristics: Air clearances and creepage distances

|                      |                       |
|----------------------|-----------------------|
| Insulation           | Functional insulation |
| Overvoltage category | II                    |
| Pollution degree     | 2                     |

### Electrical properties

|                        |                |
|------------------------|----------------|
| Operating voltage (AC) | $\leq 30$ V AC |
| Operating voltage (DC) | $\leq 60$ V DC |
| Current (per branch)   | $\leq 2$ A     |

### Air clearances and creepage distances

|                          |                         |
|--------------------------|-------------------------|
| Rated insulation voltage | 100 V                   |
| Rated surge voltage      | 0.8 kV (1.2/50 $\mu$ s) |

### Connection data

#### Connection 1 (control level)

|                                  |                 |
|----------------------------------|-----------------|
| Connection in acc. with standard | IEC 60807-2     |
| Connection method                | D-SUB pin strip |
| Screw thread                     | UNC 4-40        |
| Number of connections            | 1               |
| Number of positions              | 25              |
| Insertion/withdrawal cycles      | > 500           |
| Pitch                            | 2.77 mm         |

#### Connection 2 (field level)

|                                                                         |                                                                                |
|-------------------------------------------------------------------------|--------------------------------------------------------------------------------|
| Connection method                                                       | Screw connection                                                               |
| Stripping length                                                        | 7 mm                                                                           |
| Screw thread                                                            | M3                                                                             |
| Number of positions                                                     | 27                                                                             |
| Conductor cross-section rigid                                           | 0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>                                      |
| Conductor cross-section rigid (2 conductors with same cross section)    | 0.2 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>                                    |
| Conductor cross-section flexible                                        | 0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>                                    |
|                                                                         | 0.25 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> (Ferrule without plastic sleeve)  |
|                                                                         | 0.25 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> (Ferrule with plastic sleeve)     |
| Conductor cross-section flexible (2 conductors with same cross section) | 0.2 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>                                    |
|                                                                         | 0.2 mm <sup>2</sup> ... 0.75 mm <sup>2</sup> (Ferrule without plastic sleeve)  |
|                                                                         | 0.5 mm <sup>2</sup> ... 0.5 mm <sup>2</sup> (TWIN ferrule with plastic sleeve) |

# FLKMS-D25 SUB/S - Termination board



2281720

<https://www.phoenixcontact.com/us/products/2281720>

|                             |                   |
|-----------------------------|-------------------|
| Conductor cross-section AWG | 24 ... 12         |
| Tightening torque           | 0.5 Nm ... 0.6 Nm |
| Pitch                       | 5.08 mm           |

## Signaling

|                        |    |
|------------------------|----|
| Status display present | no |
|------------------------|----|

## Dimensions

### Item dimensions

|        |         |
|--------|---------|
| Width  | 67.5 mm |
| Height | 72 mm   |
| Depth  | 77 mm   |

## Environmental and real-life conditions

### Ambient conditions

|                                              |                  |
|----------------------------------------------|------------------|
| Degree of protection (Module)                | IP20             |
| Degree of protection (Installation location) | ≥ IP54           |
| Ambient temperature (operation)              | -20 °C ... 50 °C |
| Ambient temperature (storage/transport)      | -20 °C ... 70 °C |
| Altitude                                     | ≤ 2000 m         |

## Standards and regulations

### Air clearances and creepage distances

|                       |                |
|-----------------------|----------------|
| Standards/regulations | EN IEC 60664-1 |
|-----------------------|----------------|

## Mounting

|                   |                           |
|-------------------|---------------------------|
| Mounting type     | DIN rail mounting         |
| Assembly note     | in rows with zero spacing |
| Mounting position | any                       |

## Notes

|                    |                                                                                                                                                                                                                                                                                |
|--------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Notes on operation | For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met. |
|--------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

# FLKMS-D25 SUB/S - Termination board


2281720

<https://www.phoenixcontact.com/us/products/2281720>



## Drawings

Circuit diagram



# FLKMS-D25 SUB/S - Termination board



2281720

<https://www.phoenixcontact.com/us/products/2281720>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27141152 |
| ECLASS-15.0 | 27141152 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC002780 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# FLKMS-D25 SUB/S - Termination board



2281720

<https://www.phoenixcontact.com/us/products/2281720>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)