


IB IL AI 4/I-PAC - Analog module

2700458

<https://www.phoenixcontact.com/us/products/2700458>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Inline, Analog input terminal, Analog inputs: 4, 0 mA ... 20 mA, 4 mA ... 20 mA, connection technology: 2-conductor, transmission speed in the local bus: 500 kbps, degree of protection: IP20, including Inline connector and labeling field; The product is being prepared for compliance with the Cyber Resilience Act (CRA).

Product description

The terminal is designed for use within an Inline station. It is used to acquire analog current signals.

Your advantages

- 4 analog differential input channels for connecting current signals
- Connection of sensors in 2-conductor technology
- Current ranges: 0 mA ... 20 mA, 4 mA ... 20 mA
- Mean value generation of the inputs
- Process data update of all channels in 250 µs
- Diagnostic and status indicators



Commercial data

Item number	2700458
Packing unit	1 pc

IB IL AI 4/I-PAC - Analog module

2700458


<https://www.phoenixcontact.com/us/products/2700458>



Minimum order quantity	1 pc
Sales key	DR01
Product key	DRI141
GTIN	4046356566544
Weight per piece (including packing)	90 g
Weight per piece (excluding packing)	66 g
Customs tariff number	85389091
Country of origin	DE

Technical data

Dimensions

Dimensional drawing	
Width	12.2 mm
Height	119.8 mm
Depth	71.5 mm
Note on dimensions	Housing dimensions

Notes

Note on application	Only for industrial use
Note on application	As things stand now, we are preparing the product so that, as of December 11, 2027, it will comply with the requirements of the EU Cyber Resilience Act (CRA) based on the information currently available regarding the CRA.

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

Material specifications

Color (Housing)	green (RAL 6021)
-----------------	------------------

Interfaces

Inline local bus

Number of interfaces	2
Connection method	Inline data jumper
Transmission speed	500 kbps
Transmission physics	Copper

System properties

Programming data

Length code (hex)	04
ID code (dec.)	127
Length code (dec)	04
Process data channel	64 bit
Input address area	8 Byte
Output address area	8 Byte
Parameter channel (PCP)	0 Byte

IB IL AI 4/I-PAC - Analog module

2700458

<https://www.phoenixcontact.com/us/products/2700458>



Register length (bus)	64 bit
Fieldbus data telegram (PROFIBUS)	
Required parameter data	10 Byte
Required configuration data	5 Byte

Input data

Analog:

Input name	Analog inputs
Description of the input	Differential inputs, current
Number of inputs	4
Connection method	Inline connector
Connection technology	2-conductor
Process data update	typ. 250 µs (all channels)
A/D conversion time	max. 6.5 µs
A/D converter resolution	12 bit
Limit frequency (3 dB)	300 Hz
Wire-break behavior	Going to 0 mA; open-circuit detection from 4 mA ... 20 mA
Permissible voltage	max. 5.2 V (between positive and negative current connection; corresponds to 50 mA, maximum, through the resistance detectors)
Measured value resolution	13 bits (12 bits + sign bit)
Measured value representation	13 bits (12 bits + sign bit)
Data formats	IB IL, S7-compatible
Current input signal	0 mA ... 20 mA
	4 mA ... 20 mA
Input resistance current input	typ. 113 Ω
Filtering	None or mean value generation over 4, 16, or 32 measured values

Product properties

Product type	I/O component
Product family	Inline
Type	modular
Installation location	Control cabinet
Scope of supply	including Inline connector and labeling field
Operating mode	Process data mode with 4 words
Special properties	The product is being prepared for compliance with the Cyber Resilience Act (CRA)
Diagnostics messages	Failure of the internal I/O supply I/O error message sent to the bus coupler
	I/O supply failure Message in the diagnostic code (in the IB IL format)
	Overrange or underrange Message in the diagnostic code (in the IB IL format)

Configuration invalid Message in the diagnostic code (in the IB IL format)

Insulation characteristics

Overvoltage category	II (IEC 60664-1, EN 60664-1)
Pollution degree	2 (IEC 60664-1, EN 60664-1)

Electrical properties

Maximum power dissipation for nominal condition	1.45 W
---	--------

Potentials: Communications power (U_L)

Supply voltage	7.5 V DC (via voltage jumper)
Current draw	max. 60 mA typ. 55 mA

Potentials: Supply of analog modules (U_{ANA})

Supply voltage	24 V DC
Supply voltage range	19.2 V DC ... 30 V DC (including all tolerances, including ripple)
Current draw	max. 35 mA typ. 30 mA

Electrical isolation/isolation of the voltage ranges

Test voltage: 7.5 V supply (bus logic), 24 V supply U_{ANA} / I/O	500 V AC, 50 Hz, 1 min
Test voltage: 7.5 V supply (bus logic), 24 V supply U_{ANA} / functional ground	500 V AC, 50 Hz, 1 min
Test voltage: I/O/functional ground	500 V AC, 50 Hz, 1 min

Connection data

Connection technology

Connection name	Inline connector
-----------------	------------------

Inline connector

Connection method	Spring-cage connection
Conductor cross-section, rigid	0.08 mm ² ... 1.5 mm ²
Conductor cross-section, flexible	0.08 mm ² ... 1.5 mm ²
Conductor cross-section AWG	28 ... 16
Stripping length	8 mm

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-25 °C ... 55 °C
Degree of protection	IP20
Air pressure (operation)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Air pressure (storage/transport)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Ambient temperature (storage/transport)	-25 °C ... 85 °C
Permissible humidity (operation)	10 % ... 95 % (non-condensing)

IB IL AI 4/I-PAC - Analog module



2700458

<https://www.phoenixcontact.com/us/products/2700458>

Permissible humidity (storage/transport)	10 % ... 95 % (non-condensing)
--	--------------------------------

Mechanical test

Vibration resistance in accordance with EN 60068-2-6/IEC 60068-2-6	5g
Shock in accordance with EN 60068-2-27/IEC 60068-2-27	25g

Standards and regulations

Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
------------------	---------------------------------------

IB IL AI 4/I-PAC - Analog module


2700458

<https://www.phoenixcontact.com/us/products/2700458>




Drawings

Dimensional drawing



Dimensions (in mm)

Connection diagram



Connection example


IB IL AI 4/I-PAC - Analog module

2700458

<https://www.phoenixcontact.com/us/products/2700458>



Block diagram



Internal wiring of the terminal points

IB IL AI 4/I-PAC - Analog module

2700458

<https://www.phoenixcontact.com/us/products/2700458>



Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2700458>



cULus Listed

Approval ID: E140324

IB IL AI 4/I-PAC - Analog module



2700458

<https://www.phoenixcontact.com/us/products/2700458>

Classifications

ECLASS

ECLASS-13.0	27242601
ECLASS-15.0	27242601

ETIM

ETIM 10.0	EC001596
-----------	----------

UNSPSC

UNSPSC 21.0	32151600
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
	6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol(CAS: 119-47-1)
SCIP	96f75740-8cdf-48dd-a88f-cd21f850a933

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
 586 Fulling Mill Road
 Middletown, PA 17057, United States
 (+717) 944-1300
info@phoenixcon.com