

IB IL 24 PSDI 16-PAC - Safety module

2700994

<https://www.phoenixcontact.com/us/products/2700994>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Safety-related digital input module, IP20 protection, for the SafetyBridge V3 and PROFIsafe system. The module has 8 safe digital inputs for two-channel assignment or 16 safe digital inputs for single-channel assignment.

Product description

The safety module is an input module from the Inline product range designed for use at any point within a SafetyBridge or PROFIsafe system. The transmission speed of the safety module can be set to 500 kBaud or 2 Mbaud using a switch. One transmission speed must be used consistently within a station. The module has eight safe digital inputs for two-channel assignment or sixteen digital inputs for single-channel assignment.

Your advantages

- SIL 3 in accordance with EN IEC 62061
- SIL 3 according to IEC/EN 61508
- PL e in accordance with EN ISO 13849-1



Commercial data

Item number	2700994
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN03

IB IL 24 PSDI 16-PAC - Safety module



2700994

<https://www.phoenixcontact.com/us/products/2700994>

Product key	DNA421
GTIN	4046356678995
Weight per piece (including packing)	400 g
Weight per piece (excluding packing)	222 g
Customs tariff number	85389091
Country of origin	DE

IB IL 24 PSDI 16-PAC - Safety module




2700994

<https://www.phoenixcontact.com/us/products/2700994>

Technical data

Dimensions

Dimensional drawing	
Width	48.8 mm
Height	141 mm
Depth	71.5 mm
Note on dimensions	Housing dimensions

Notes

Note on application	Only for industrial use
Note on application	As things stand now, we are preparing the product so that, as of December 11, 2027, it will comply with the requirements of the EU Cyber Resilience Act (CRA) based on the information currently available regarding the CRA.

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

Material specifications

Color (Housing)	yellow (RAL 1018)
-----------------	-------------------

Interfaces

Inline local bus

No. of channels	2
Connection method	Inline data jumper
Transmission speed	500 kbps / 2 Mbps (can be switched)

System properties

Programming data

Length code (hex)	04
ID code (dec.)	163
Length code (dec)	04
Process data channel	8 Byte ((Operating mode: SafetyBridge))
Input address area	8 Byte ((Operating mode: SafetyBridge))
Output address area	8 Byte ((Operating mode: SafetyBridge))
Parameter channel (PCP)	0 Byte ((Operating mode: SafetyBridge))
Register length (bus)	8 Byte ((Operating mode: SafetyBridge))

IB IL 24 PSDI 16-PAC - Safety module



2700994

<https://www.phoenixcontact.com/us/products/2700994>

Fieldbus data telegram

Required parameter data	1 Byte ((Operating mode: SafetyBridge))
Required configuration data	5 Byte ((Operating mode: SafetyBridge))

Input data

Digital:

Input name	Digital inputs
Description of the input	IEC 61131-2 type 3
Number of inputs	8 (for 2-channel assignment) 16 (for 1-channel assignment)
Cable length	max. 500 m (200 m from the clock output to the safe input (total based on forward and return path))
Connection method	Spring-cage connection
Connection technology	2-, 3-conductor
Input voltage	24 V DC (via clock outputs UT1 and UT2 or external supply)
Input voltage range	-3 V DC ... 30 V DC
Input voltage range "0" signal	-3 V DC ... 5 V DC
Input voltage range "1" signal	11 V DC ... 30 V DC
Typical input current per channel	2.7 mA (at 24 V)

Product properties

Product type	I/O component
Product family	Inline
Application	Functional safety
Type	modular
Special properties	The product is being prepared for compliance with the Cyber Resilience Act (CRA)

Electrical properties

Transmission medium	Copper
---------------------	--------

Potentials: Communications power (U_L)

Supply voltage	7.5 V DC (see safety data)
Current draw	max. 190 mA

Potentials: Main circuit supply (U_M)

Supply voltage	24 V DC
Supply voltage range	19.2 V DC ... 30 V DC (including all tolerances, including ripple)
Current draw	max. 415 mA typ. 15 mA (plus current consumption of the inputs when supplied via the clock outputs, plus current consumption of the connected initiators when via through the clock outputs)

Supply: Module electronics

Supply voltage	24 V DC (via voltage jumper)
Supply voltage range	19.2 V DC ... 30 V DC

Connection data

Connection technology

Connection name	Inline connector
pluggable	yes

Inline connector

Connection method	Spring-cage connection
pluggable	yes
Conductor cross-section, rigid	0.2 mm² ... 1.5 mm²
Conductor cross-section, flexible	0.2 mm² ... 1.5 mm²
Conductor cross-section AWG	24 ... 16

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-25 °C ... 55 °C
Degree of protection	IP20
Air pressure (operation)	80 kPa ... 108 kPa (up to 2000 m above sea level)
Air pressure (storage/transport)	66 kPa ... 108 kPa (up to 3500 m above sea level)
Ambient temperature (storage/transport)	-25 °C ... 70 °C
Permissible humidity (operation)	10 % ... 85 % (Take suitable measures against increased air humidity within the permitted temperature range.)
Permissible humidity (storage/transport)	10 % ... 85 % (Take suitable measures against increased air humidity within the permitted temperature range.)

Standards and regulations

Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
------------------	---------------------------------------

Characteristics

Safety data: EN ISO 13849

Performance level (PL)	max. e (two channel; dependent in parameterization and wiring)
------------------------	--

IB IL 24 PSDI 16-PAC - Safety module


2700994

<https://www.phoenixcontact.com/us/products/2700994>




Drawings

Dimensional drawing



Dimensions (in mm)

Connection diagram



Connection example for an emergency stop circuit

IB IL 24 PSDI 16-PAC - Safety module



2700994

<https://www.phoenixcontact.com/us/products/2700994>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2700994>



cULus Listed

Approval ID: E140324

PROFIsafe

Approval ID: Z20207



Functional Safety

Approval ID: 968/FSP 2449.00/22

TUEV RH FS

Approval ID: 968/EZ650.17/26

IB IL 24 PSDI 16-PAC - Safety module



2700994

<https://www.phoenixcontact.com/us/products/2700994>

Classifications

ECLASS

ECLASS-13.0	27242604
ECLASS-15.0	27242604
ECLASS-15.0 ASSET	27250101

ETIM

ETIM 10.0	EC001599
-----------	----------

UNSPSC

UNSPSC 21.0	32151600
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	ac39e2af-d1fd-4067-8231-514b66a902ba

EF3.1 Climate Change

CO2e kg	16.1 kg CO2e
---------	--------------