TC EXTENDER PT-IQ-2S - Surge protection plug

2702258

https://www.phoenixcontact.com/us/products/2702258

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

24 V

IEC



Replaceable surge protection module, only for Ethernet extender TC EXTENDER 6004 ETH-2S (2702255), 2 SHDSL ports, two-wire protection for floating SHDSL cables, two-level protective circuit

ELEKTROGERÄTE RÜCKNAHME

Commercial data

Item number	2702258
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN24
Product key	DNC442
GTIN	4055626057705
Weight per piece (including packing)	86 g
Weight per piece (excluding packing)	48.68 g
Customs tariff number	85363090
Country of origin	DE

Technical data

Notes

Note on application

Note on application	Only for industrial use

Product properties

Product type	Replacement plug
IEC test classification	B1
	C1
	C2
	C3
	D1
Type	Male
Wire pairs per module	2

Insulation characteristics

Overvoltage category	II
Pollution degree	2

Electrical properties

Nominal voltage U_N	24 V DC

Connection data

Connection method	pluggable

Dimensions

Width	22 mm
Height	96 mm
Depth	80 mm

Material specifications

Color (Housing)	white aluminium (RAL 9006)

Protective circuit

Direction of action	Line-Line & Line-Earth Ground
Nominal voltage U_N	24 V DC
Nominal discharge current I_n (8/20) µs (line-line)	1 kA (C1, 300 pulses)
Nominal discharge current I_n (8/20) µs (line-ground)	1 kA
Pulse discharge current I_{imp} (10/350) µs (line-earth)	500 A (D1)
Total discharge current I_{Total} (8/20) µs	9 kA
Nominal pulse current Ian (10/1000) µs (line-line)	100 A (B1)
Nominal pulse current Ian (10/1000) µs (line-earth)	100 A

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20

Approvals

Conformity/Approvals

Noxious gas test	ISA-S71.04-1985 G3 Harsh Group A

Standards and regulations

Standard designation	Surge protective devices in the low-voltage range, in telecommunications and signaling networks
Standards/specifications	IEC 61643-21

Air clearances and creepage distances


Standards/specifications	IEC 60664-1

Mounting

Mounting type	Plug-in mounting


Drawings

Schematic diagram



Function elements

Schematic diagram



Replacement of protection module

Classifications

ECLASS

ECLASS-13.0	27171592
ECLASS-15.0	27171592

ETIM

ETIM 10.0	EC002497

UNSPSC

UNSPSC 21.0	39121600

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	2,2',6,6'-tetrabromo-4,4'-isopropylidenediphenol(CAS: 79-94-7)

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com