# EB 10- DIK GY - Insertion bridge

2715937

https://www.phoenixcontact.com/us/products/2715937

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Insertion bridge, pitch: 6.15 mm, number of positions: 10, color: gray

## Commercial data

| | |
|---|---|
| Item number | 2715937 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Sales key | BE19 |
| Product key | BE1Z2X |
| GTIN | 4017918061685 |
| Weight per piece (including packing) | 4.4 g |
| Weight per piece (excluding packing) | 4.266 g |
| Customs tariff number | 85366990 |
| Country of origin | PL |

## Technical data

### Product properties

| | |
|---|---|
| Product type | Insertion bridge |
| Number of positions | 10 |
| Pitch | 6.15 mm |
| Potentials | 10 |

### Dimensions

| | |
|---|---|
| Pitch | 6.15 mm |

### Material specifications

| | |
|---|---|
| Color | gray (RAL 7042) |
| Material | Copper |
| Flammability rating according to UL 94 | V0 |
| Insulating material | PA |
| Static insulating material application in cold | -60 °C |
| Relative insulation material temperature index (Elec., UL 746 B) | 130 °C |
| Fire protection for rail vehicles (DIN EN 45545-2) R22 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R23 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R24 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R26 | HL 1 - HL 3 |
| Surface flammability NFPA 130 (ASTM E 162) | passed |
| Specific optical density of smoke NFPA 130 (ASTM E 662) | passed |
| Smoke gas toxicity NFPA 130 (SMP 800C) | passed |

### Mounting

| | |
|---|---|
| Mounting type | Screw mounting |

## Classifications

### ECLASS

| | |
|---|---|
| ECLASS-13.0 | 27250303 |
| ECLASS-15.0 | 27250303 |

### ETIM

| | |
|---|---|
| ETIM 10.0 | EC000489 |

### UNSPSC

| | |
|---|---|
| UNSPSC 21.0 | 39121400 |

## Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |

China RoHS

| | |
|---|---|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|---|---|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |


Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com



Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com