

DK-BIC-35 - Feed-through terminal block



2749880

<https://www.phoenixcontact.com/us/products/2749880>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Feed-through terminal block for VAL and FLT applications

Your advantages

- Biconnect feed-through terminal block
- For wiring mixed combinations of lightning and surge arresters
- As a system extension for FLASHTRAB and VALVETRAB applications

Commercial data

Item number	2749880
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	CL18
Product key	CL132Z
GTIN	4017918108212
Weight per piece (including packing)	90.8 g
Weight per piece (excluding packing)	71.43 g
Customs tariff number	85363010
Country of origin	IN

DK-BIC-35 - Feed-through terminal block



2749880
<https://www.phoenixcontact.com/us/products/2749880>

Technical data

Notes

General		
Note		The nominal cross section for rated load current is 35 mm².

Product properties

Product type	Feed-through terminal block
Type	DIN rail module, one-piece
Number of connections	2
Number of rows	1

Insulation characteristics		
Overvoltage category		III
Pollution degree		2


Electrical properties

Rated voltage (III/3)	500 V AC/DC
-----------------------	-------------

Connection data

Connection method	Screw connection
Screw thread	M5
Tightening torque	... 4.5 Nm
Stripping length	14.5 mm
Conductor cross-section rigid	0.5 mm² ... 35 mm²
Cross section AWG	20 ... 2 (converted acc. to IEC)
Conductor cross-section flexible	0.5 mm² ... 25 mm²
Nominal cross section	25 mm²
Nominal current	125 A (30 °C)
Nominal voltage	500 V AC
	500 V DC

Dimensions

Dimensional drawing	
Width	17.7 mm
Height	89.8 mm
Depth	65.5 mm (incl. DIN rail 7.5 mm)
Horizontal pitch	1 HP

DK-BIC-35 - Feed-through terminal block



2749880

<https://www.phoenixcontact.com/us/products/2749880>

Material specifications

Color	black (RAL 9005)
Flammability rating according to UL 94	V-0
Housing material	PA 6.6-FR

Mechanical properties

Mechanical data

Open side panel	No
-----------------	----

Protective circuit

Maximum continuous operating voltage U_C	500 V AC
	500 V DC
Impulse discharge current (10/350) μ s, charge	50 As
Impulse discharge current (10/350) μ s, specific energy	2.5 MJ/ Ω
Impulse discharge current (10/350) μ s, peak value I_{imp}	100 kA

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 85 °C

Standards and regulations

Air clearances and creepage distances

Standards/regulations	DIN VDE 0110-1 / IEC 60664-1
Standards/specifications	EN 60947-7-1
Note	2009
Standards/specifications	IEC 61643-11
Note	2011
Standards/specifications	EN 61643-11
Note	2012

Mounting

Mounting type	DIN rail: 35 mm
---------------	-----------------


DK-BIC-35 - Feed-through terminal block

2749880

<https://www.phoenixcontact.com/us/products/2749880>

Drawings

Dimensional drawing



Circuit diagram



DK-BIC-35 - Feed-through terminal block



2749880

<https://www.phoenixcontact.com/us/products/2749880>

Classifications

ECLASS

ECLASS-13.0	27250101
ECLASS-15.0	27250101

ETIM

ETIM 10.0	EC000897
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

DK-BIC-35 - Feed-through terminal block



2749880

<https://www.phoenixcontact.com/us/products/2749880>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com