LDP- 12- 24DC - Plug-in module

2833657

https://www.phoenixcontact.com/us/products/2833657

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Plug-in module, with freewheeling diode and yellow LED, polarity: A1+, A2-, input voltage: 12 ... 24 V DC ±20 %

Your advantages

- Mechanical coding to protect against mismatching
- Attenuation of reverse voltage induced in coil

Commercial data

Item number	2833657
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	C463
Product key	DKF346
GTIN	4017918933845
Weight per piece (including packing)	2.58 g
Weight per piece (excluding packing)	2 g
Customs tariff number	85363010
Country of origin	CN

Technical data

Product properties

Product type	Plug-in module
Product family	ESSENTIAL edition

Input data


Input voltage range	12 V DC ... 24 V DC
Protective circuit	Freewheeling diode, LED

Mounting

Mounting type	Plug-in mounting
Mounting position	any

Drawings

Circuit diagram



Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/2833657

cUL Recognized
Approval ID: E140324

UL Recognized
Approval ID: E140324

EAC
Approval ID: RU C-DE.A*30.B.01742

Classifications

ECLASS

ECLASS-13.0	27371692
ECLASS-15.0	27371692

ETIM

ETIM 10.0	EC002586

UNSPSC

UNSPSC 21.0	39122300

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

EF3.1 Climate Change

CO2e kg	0.239 kg CO2e

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com