

# MINI MCR-SL-PT100-UI-200-NC - Temperature measuring transducer



2864370

<https://www.phoenixcontact.com/us/products/2864370>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



MCR temperature transducer, configurable, for Pt 100 temperature sensors, with screw-connection, not configured

## Your advantages

- Power supply possible via the foot element (TBUS)
- Optimized temperature measuring range of -50°C to +200°C for increased accuracy
- For 2-, 3-, 4-conductor Pt 100 sensors in accordance with IEC 60751
- Error indication via diagnostic LED and analog signal
- Pt 100 signals to create standard signals
- 3-way isolation
- Highly-compact temperature transducer for electrical isolation, conversion, amplification, and filtering of
- Input and output signals can be configured via DIP switches

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 2864370       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | C403          |
| Product key                          | DK1135        |
| GTIN                                 | 4046356046480 |
| Weight per piece (including packing) | 62.6 g        |
| Weight per piece (excluding packing) | 58.57 g       |
| Customs tariff number                | 85437090      |
| Country of origin                    | DE            |

# MINI MCR-SL-PT100-UI-200-NC - Temperature measuring transducer



2864370

<https://www.phoenixcontact.com/us/products/2864370>

## Technical data

### Notes

#### Utilization restriction

|          |                                                                           |
|----------|---------------------------------------------------------------------------|
| EMC note | EMC: class A product, see manufacturer's declaration in the download area |
|----------|---------------------------------------------------------------------------|

### Product properties

|                |                         |
|----------------|-------------------------|
| Product type   | Temperature transmitter |
| Product family | MINI Analog             |
| Configuration  | DIP switches            |

### System properties

#### Functionality

|               |              |
|---------------|--------------|
| Configuration | DIP switches |
|---------------|--------------|

### Electrical properties

|                                                 |                                                   |
|-------------------------------------------------|---------------------------------------------------|
| Electrical isolation                            | 3-way isolation                                   |
| Electrical isolation between input and output   | yes                                               |
| Maximum power dissipation for nominal condition | 235.5 mW                                          |
| Protective circuit                              | Transient protection                              |
| Step response (0–99%)                           | < 200 ms                                          |
| Maximum temperature coefficient                 | < 0.02 %/K                                        |
| Transmission error in the set measuring range   | $((50 \text{ K} / \Delta \text{ Temp}) + 0.05)\%$ |
| Transmission error in the full measuring range  | ≤ 0.25 %                                          |

#### Electrical isolation

|                      |    |
|----------------------|----|
| Overvoltage category | II |
| Pollution degree     | 2  |

#### Electrical isolation Input/output/power supply IEC/EN 61010

|                          |                         |
|--------------------------|-------------------------|
| Standards/regulations    | IEC/EN 61010            |
| Rated insulation voltage | 50 V AC/DC              |
| Test voltage             | 1.5 kV AC (50 Hz, 60 s) |
| Insulation               | Basic insulation        |

#### Supply

|                          |                                                                                                                                                                                                                 |
|--------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Nominal supply voltage   | 24 V DC                                                                                                                                                                                                         |
| Supply voltage range     | 19.2 V DC ... 30 V DC (The DIN rail connector (ME 6,2 TBUS-2 1,5/5-ST-3,81 GN, item no. 2869728) can be used to bridge the supply voltage. It can be snapped onto a 35 mm DIN rail in accordance with EN 60715) |
| Max. current consumption | < 21 mA (at 24 V DC)                                                                                                                                                                                            |
| Power consumption        | < 500 mW                                                                                                                                                                                                        |

# MINI MCR-SL-PT100-UI-200-NC - Temperature measuring transducer



2864370

<https://www.phoenixcontact.com/us/products/2864370>

## Input data

### Signal

|                  |   |
|------------------|---|
| Number of inputs | 1 |
|------------------|---|

### Measurement

|                                               |                                  |
|-----------------------------------------------|----------------------------------|
| Sensor types (RTD) that can be used           | Pt 100 (IEC 60751/EN 60751)      |
| Temperature measuring range                   | min. 50 K                        |
| Temperature measuring range: Pt 100           | -50 °C ... 200 °C (configurable) |
| Sensor input current                          | 1 mA (constant)                  |
| Max. permissible overall conductor resistance | 10 Ω (Per cable)                 |
| Connection technology                         | 2-, 3-, 4-conductor              |

## Output data

### Signal: Voltage/current

|                                 |                                                                                          |
|---------------------------------|------------------------------------------------------------------------------------------|
| Number of outputs               | 1                                                                                        |
| Configurable/programmable       | Yes                                                                                      |
| Voltage output signal           | 0 V ... 5 V                                                                              |
|                                 | 1 V ... 5 V                                                                              |
|                                 | 0 V ... 10 V                                                                             |
|                                 | 10 V ... 0 V                                                                             |
| Max. voltage output signal      | ≈  V  |
| Open-circuit voltage            | ≈  V  |
| Current output signal           | 0 mA ... 20 mA                                                                           |
|                                 | 4 mA ... 20 mA                                                                           |
|                                 | 20 mA ... 0 mA                                                                           |
|                                 | 20 mA ... 4 mA                                                                           |
| Max. current output signal      | 23 mA                                                                                    |
| Short-circuit current           | ≈  mA |
| Load/output load voltage output | > 10 kΩ                                                                                  |
| Load/output load current output | < 500 Ω (at 20 mA)                                                                       |
| Ripple                          | < 20 mV <sub>PP</sub> (at 500 Ω)                                                         |
|                                 | < 20 mV <sub>PP</sub> (at 10 kΩ)                                                         |

## Connection data

|                                  |                                             |
|----------------------------------|---------------------------------------------|
| Connection method                | Screw connection                            |
| Stripping length                 | 12 mm                                       |
| Screw thread                     | M3                                          |
| Conductor cross-section rigid    | 0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |
| Conductor cross-section flexible | 0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |
| Conductor cross-section AWG      | 26 ... 12                                   |

## Dimensions


# MINI MCR-SL-PT100-UI-200-NC - Temperature measuring transducer



2864370

<https://www.phoenixcontact.com/us/products/2864370>

Dimensional drawing



|        |          |
|--------|----------|
| Width  | 6.2 mm   |
| Height | 93.1 mm  |
| Depth  | 101.2 mm |

## Material specifications

|                                                        |                  |
|--------------------------------------------------------|------------------|
| Color                                                  | green (RAL 6021) |
| Housing material                                       | PBT              |
| Fire protection for rail vehicles (DIN EN 45545-2) R22 | HL 1 - HL 2      |
| Fire protection for rail vehicles (DIN EN 45545-2) R23 | HL 1 - HL 2      |
| Fire protection for rail vehicles (DIN EN 45545-2) R24 | HL 1 - HL 2      |

## Environmental and real-life conditions

### Ambient conditions

|                                         |                               |
|-----------------------------------------|-------------------------------|
| Degree of protection                    | IP20                          |
| Ambient temperature (operation)         | -20 °C ... 65 °C              |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C              |
| Altitude                                | ≤ 2000 m                      |
| Permissible humidity (operation)        | 5 % ... 95 % (non-condensing) |

## Approvals

### CE

|             |              |
|-------------|--------------|
| Certificate | CE-compliant |
|-------------|--------------|

### UL, USA/Canada

|                |                                       |
|----------------|---------------------------------------|
| Identification | UL 508 Recognized                     |
|                | Class I, Div. 2, Groups A, B, C, D T5 |

## EMC data

|                               |                                                                      |
|-------------------------------|----------------------------------------------------------------------|
| Electromagnetic compatibility | Conformance with EMC directive                                       |
| Noise immunity                | EN 61000-6-2                                                         |
| Note                          | When being exposed to interference, there may be minimal deviations. |

### Noise emission

|                       |              |
|-----------------------|--------------|
| Standards/regulations | EN 61000-6-4 |
|-----------------------|--------------|

### Electrostatic discharge

# MINI MCR-SL-PT100-UI-200-NC - Temperature measuring transducer



2864370

<https://www.phoenixcontact.com/us/products/2864370>

|                       |              |
|-----------------------|--------------|
| Standards/regulations | EN 61000-4-2 |
|-----------------------|--------------|

## Electrostatic discharge

|          |                                                                   |
|----------|-------------------------------------------------------------------|
| Comments | Safety measures must be taken to prevent electrostatic discharge. |
|----------|-------------------------------------------------------------------|

## Electromagnetic HF field

|                                              |                          |
|----------------------------------------------|--------------------------|
| Designation                                  | Electromagnetic RF field |
| Standards/regulations                        | EN 61000-4-3             |
| Typical deviation from the upper range value | 10 %                     |

## Fast transients (burst)

|                                              |                         |
|----------------------------------------------|-------------------------|
| Designation                                  | Fast transients (burst) |
| Standards/regulations                        | EN 61000-4-4            |
| Typical deviation from the upper range value | 10 %                    |

## Surge current load (surge)

|                       |              |
|-----------------------|--------------|
| Standards/regulations | EN 61000-4-5 |
|-----------------------|--------------|

## Surge current load (surge)

|          |             |
|----------|-------------|
| Comments | Criterion B |
|----------|-------------|

## Conducted interference

|                                              |                         |
|----------------------------------------------|-------------------------|
| Designation                                  | Conducted interferences |
| Standards/regulations                        | EN 61000-4-6            |
| Typical deviation from the upper range value | 10 %                    |

## Standards and regulations

|                      |                 |
|----------------------|-----------------|
| Electrical isolation | 3-way isolation |
|----------------------|-----------------|

## Mounting

|                   |                   |
|-------------------|-------------------|
| Mounting type     | DIN rail mounting |
| Mounting position | any               |


# MINI MCR-SL-PT100-UI-200-NC - Temperature measuring transducer



2864370

<https://www.phoenixcontact.com/us/products/2864370>

## Drawings




# MINI MCR-SL-PT100-UI-200-NC - Temperature measuring transducer

2864370

<https://www.phoenixcontact.com/us/products/2864370>

Block diagram



# MINI MCR-SL-PT100-UI-200-NC - Temperature measuring transducer



2864370

<https://www.phoenixcontact.com/us/products/2864370>

## Approvals

 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2864370>



**cUL Recognized**  
Approval ID: E238705



**UL Recognized**  
Approval ID: E238705



**cUL Listed**  
Approval ID: E199827



**UL Listed**  
Approval ID: E199827

# MINI MCR-SL-PT100-UI-200-NC - Temperature measuring transducer



2864370

<https://www.phoenixcontact.com/us/products/2864370>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27210129 |
| ECLASS-15.0 | 27210129 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC002919 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 41112100 |
|-------------|----------|

# MINI MCR-SL-PT100-UI-200-NC - Temperature measuring transducer



2864370

<https://www.phoenixcontact.com/us/products/2864370>

## Environmental product compliance

### EU RoHS

|                                         |              |
|-----------------------------------------|--------------|
| Fulfills EU RoHS substance requirements | Yes          |
| Exemption                               | 7(a), 7(c)-I |

### China RoHS

|                                        |                                                                                                                                                                                                                                   |
|----------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-50                                                                                                                                                                                                                           |
|                                        | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |                                      |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1)                 |
| SCIP                                | f6907ea8-b097-4e94-b902-511f0e9879ab |

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)