PT 2-TELE - Surge protection device

2882828

https://www.phoenixcontact.com/us/products/2882828

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.





Surge protective device, consisting of plug and base element, for protecting a double wire from analog and digital telecommunications interfaces (VDSL up to 50 Mbps, on short paths (< 300 m) up to 100 Mbps).

Product description

Surge protection plug for DIN rail mounting, 2-section pluggable, normal mode voltage coarse and fine protection for 2-conductor analog telecommunication interface as well as common mode voltage coarse protection to ground.

Your advantages

- Easy testing and documentation with CHECKMASTER 2 with pluggable protective modules
- Maximum ease of maintenance, thanks to the 2-piece design
- Easy selection for all possible demands in MCR applications with a complete product portfolio

ELEKTROGERÄTE RÜCKNAHME

Commercial data

Item number	2882828
Packing unit	10 pc
Minimum order quantity	1 pc
Sales key	CL03

Product key	CL3121
GTIN	4046356115148
Weight per piece (including packing)	74.2 g
Weight per piece (excluding packing)	60.035 g
Customs tariff number	85363010
Country of origin	DE

Technical data

Product properties

Product type	Surge protection for information technology
Product family	PLUGTRAB PT
IEC test classification	B2
	C1
	C2
	C3
	D1
Type	DIN rail module, two-section, divisible
Number of positions	2
Surge protection fault message	none
Wire pairs per module	1

Insulation characteristics

Overvoltage category	III
Pollution degree	2


Electrical properties

Nominal voltage U_N	185 V DC
	130 V AC

Connection data

Connection method	Screw connection
Screw thread	M3
Tightening torque	0.5 Nm
Conductor cross-section flexible	0.2 mm² ... 2.5 mm²
Conductor cross-section rigid	0.2 mm² ... 4 mm²
Conductor cross-section AWG	24 ... 12

Dimensions

Dimensional drawing	
Width	17.7 mm
Height	90 mm
Depth	65.5 mm
Horizontal pitch	1 HP

Material specifications

Color	black (RAL 9005)

	black (RAL 9005)
Flammability rating according to UL 94	V-0
Housing material	PA 6.6

Mechanical properties

Mechanical data

Open side panel	No

Protective circuit

Direction of action	Line-Line & Line-Earth Ground
Nominal voltage U_N	185 V DC
	130 V AC
Maximum continuous operating voltage U_C	185 V DC
	130 V AC
Rated current	450 mA AC (45 °C)
	130 mA DC (45 °C)
Operating effective current I_C at U_C	≤ 10 µA
Protective conductor current I_{PE}	≤ 10 µA
Nominal discharge current I_n (8/20) µs (line-line)	10 kA
Nominal discharge current I_n (8/20) µs (line-ground)	10 kA
Pulse discharge current I_{imp} (10/350) µs (line-line)	1 kA
Pulse discharge current I_{imp} (10/350) µs (line-earth)	1 kA
Total discharge current I_{Total} (8/20) µs	18 kA
Max. discharge current I_{max} (8/20) µs maximum (line-earth)	18 kA
Nominal pulse current Ian (10/700) µs (line-line)	100 A
Nominal pulse current Ian (10/700) µs (line-earth)	100 A
Output voltage limitation at 1 kV/µs (line-line) spike	≤ 300 V
Output voltage limitation at 1 kV/µs (line-earth) spike	≤ 300 V
Output voltage limitation at 1 kV/µs (line-line) static	≤ 300 V
Output voltage limitation at 1 kV/µs (line-earth) static	≤ 300 V
Residual voltage at I_n (conductor-conductor)	≤ 160 V (C2 - 10 kV / 5 kA)
Residual voltage at I_n (conductor-ground)	≤ 200 V (C2 - 10 kV / 5 kA)
Voltage protection level U_p (line-line)	≤ 250 V (B2 - 1 kV / 25 A)
	≤ 300 V (B2 - 4 kV / 100 A)
	≤ 270 V (C1 - 1 kV / 500 A)
	≤ 300 V (C2 - 2 kV/1 kA)
	≤ 320 V (C2 - 4 kV / 2 kA)
	≤ 330 V (C2 - 10 kV / 5 kA)
Voltage protection level U_p (line-earth)	≤ 250 V (B2 - 1 kV / 25 A)
	≤ 300 V (B2 - 4 kV / 100 A)
	≤ 270 V (C1 - 1 kV / 500 A)
	≤ 300 V (C2 - 2 kV/1 kA)
	≤ 320 V (C2 - 4 kV / 2 kA)
	≤ 330 V (C2 - 10 kV / 5 kA)

Response time t_A (line-line)	≤ 500 ns
Response time t_A (line-earth)	≤ 500 ns
Input attenuation aE, sym.	typ. 0.4 dB (≤ 5 MHz / 100 Ω)
Cut-off frequency fg (3 dB), sym. in 100 Ω system	typ. 20 MHz
Capacity (Core-Core)	typ. 30 pF (f=1 MHz / V_R= 0 V)
Capacity (Core-Earth)	typ. 30 pF (f=1 MHz / V_R= 0 V)
Resistance per path	2.2 Ω ±10 %
Surge protection fault message	none
Impulse durability (line-line)	B2 - 4 kV / 100 A
	C1 - 1 kV / 500 A
	C2 - 10 kV / 5 kA
	C3 - 25 A
	D1 - 1 kA
Impulse durability (line-earth)	B2 - 4 kV / 100 A
	C1 - 1 kV / 500 A
	C2 - 10 kV / 5 kA
	C3 - 25 A
	D1 - 1 kA

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Altitude	≤ 2000 m (amsl)

Standards and regulations


Standards/specifications	IEC 61643-21
Note	2000
Standards/specifications	EN 61643-21
Note	2002

Mounting


Mounting type	DIN rail: 35 mm

Drawings


Dimensional drawing



Application drawing



Diagram



Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/2882828

UL Listed
Approval ID: FILE E 477688

cUL Listed
Approval ID: FILE E 477688

Classifications

ECLASS

ECLASS-13.0	27171503
ECLASS-15.0	27171503

ETIM

ETIM 10.0	EC001466

UNSPSC

UNSPSC 21.0	39121600

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	124fdb5c-fa63-4f66-8343-b4bac01df1b5

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com