

# MINI MCR-2-I-I-ILP - Input isolator



2901994  
<https://www.phoenixcontact.com/us/products/2901994>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



1-channel input loop-powered 2-way isolator with plug-in connection technology for the electrical isolation of analog signals. Input signal = output signal: 0(4) mA ... 20 mA. Screw connection technology.

## Product description

Single-channel input-loop-powered 2-way isolator with plug-in connection technology for the electrical isolation and filtering of analog signals. The input-loop-powered isolator allows operation with active sensor technology with a supply voltage of 9.6 V DC ... 30 V DC. The device is powered via the current loop of the sensor. Input signal = output signal: 0(4) mA ... 20 mA. The measuring transducer supports NFC communication.

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 2901994       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | C404          |
| Product key                          | DK1121        |
| GTIN                                 | 4046356648653 |
| Weight per piece (including packing) | 115.3 g       |
| Weight per piece (excluding packing) | 106 g         |
| Customs tariff number                | 85437090      |
| Country of origin                    | DE            |

# MINI MCR-2-I-I-ILP - Input isolator



2901994

<https://www.phoenixcontact.com/us/products/2901994>

## Technical data

### Notes

#### Note on application

|                     |                                                                                                                                                                                                                               |
|---------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Note on application | As things stand now, we are preparing the product so that, as of December 11, 2027, it will comply with the requirements of the EU Cyber Resilience Act (CRA) based on the information currently available regarding the CRA. |
|---------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

#### Utilization restriction

|          |                                                                           |
|----------|---------------------------------------------------------------------------|
| EMC note | EMC: class A product, see manufacturer's declaration in the download area |
|----------|---------------------------------------------------------------------------|

### Product properties

|                 |                    |
|-----------------|--------------------|
| Product type    | Signal conditioner |
| Product family  | MINI Analog Pro    |
| No. of channels | 1                  |

### Electrical properties

|                                               |                                                                         |
|-----------------------------------------------|-------------------------------------------------------------------------|
| Electrical isolation                          | 2-way isolation                                                         |
| Electrical isolation between input and output | yes                                                                     |
| Limit frequency (3 dB)                        | 100 Hz                                                                  |
| Signal transmission behavior                  | In = Out                                                                |
| Maximum temperature coefficient               | $\leq 0.002\text{ \%}/\text{K}$ (of measured value / 100 $\Omega$ load) |
| Maximum transmission error                    | $\leq 0.1\text{ \%}$ (of final value)                                   |
| Additional error, load-dependent              | $< 0.075\text{ \%}$ (of measured value / 100 $\Omega$ load)             |

#### Electrical isolation

|                      |    |
|----------------------|----|
| Overvoltage category | II |
| Pollution degree     | 2  |

#### Electrical isolation Input/output IEC/EN 61010-1

|                          |                       |
|--------------------------|-----------------------|
| Standards/regulations    | IEC/EN 61010-1        |
| Rated insulation voltage | 300 V <sub>rms</sub>  |
| Test voltage             | 3 kV AC (50 Hz, 60 s) |
| Insulation               | Reinforced insulation |

#### Supply

|                      |                                                                   |
|----------------------|-------------------------------------------------------------------|
| Supply voltage range | 9.6 V DC ... 30 V DC (loop-powered, no external supply necessary) |
| Power consumption    | 600 mW                                                            |

### Input data

#### Signal: Current

|                           |    |
|---------------------------|----|
| Number of inputs          | 1  |
| Configurable/programmable | no |

# MINI MCR-2-I-I-ILP - Input isolator



2901994

<https://www.phoenixcontact.com/us/products/2901994>

|                          |                            |
|--------------------------|----------------------------|
| Current input signal     | 0 mA ... 20 mA             |
|                          | 4 mA ... 20 mA             |
| Response current         | ~ 200 µA (-15°C ... +70°C) |
|                          | ~ 350 µA (-40°C ... -15°C) |
| Input voltage limitation | 30 V                       |
| Voltage dissipation      | 3.1 V (I = 20 mA)          |

## Output data

Signal: Current

|                                 |                                      |
|---------------------------------|--------------------------------------|
| Number of outputs               | 1                                    |
| Configurable/programmable       | no                                   |
| Current output signal           | 0 mA ... 20 mA                       |
|                                 | 4 mA ... 20 mA                       |
| Load/output load current output | < 600 Ω (at I = 20 mA output signal) |

## Connection data

|                                  |                                        |
|----------------------------------|----------------------------------------|
| Connection method                | Screw connection                       |
| Stripping length                 | 10 mm                                  |
| Screw thread                     | M3                                     |
| Conductor cross-section rigid    | 0.2 mm² ... 1.5 mm² (with ferrule)     |
|                                  | 0.14 mm² ... 2.5 mm² (without ferrule) |
| Conductor cross-section flexible | 0.14 mm² ... 2.5 mm²                   |
| Conductor cross-section AWG      | 24 ... 12 (flexible)                   |
| Tightening torque                | 0.5 Nm ... 0.6 Nm                      |

## Ex data

|                       |        |
|-----------------------|--------|
| Ex installation (EPL) | Gc     |
|                       | Div. 2 |

## Dimensions

|        |           |
|--------|-----------|
| Width  | 6.2 mm    |
| Height | 109.81 mm |
| Depth  | 119.2 mm  |

## Material specifications

|                                                        |                 |
|--------------------------------------------------------|-----------------|
| Color                                                  | gray (RAL 7042) |
| Housing material                                       | PBT             |
| Fire protection for rail vehicles (DIN EN 45545-2) R22 | HL 1 - HL 2     |
| Fire protection for rail vehicles (DIN EN 45545-2) R23 | HL 1 - HL 2     |
| Fire protection for rail vehicles (DIN EN 45545-2) R24 | HL 1 - HL 2     |

## Environmental and real-life conditions

Ambient conditions

|                      |                           |
|----------------------|---------------------------|
| Degree of protection | IP20 (not assessed by UL) |
|----------------------|---------------------------|

# MINI MCR-2-I-I-ILP - Input isolator



2901994

<https://www.phoenixcontact.com/us/products/2901994>

|                                         |                               |
|-----------------------------------------|-------------------------------|
| Ambient temperature (operation)         | -40 °C ... 70 °C              |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C              |
| Altitude                                | < 2000 m                      |
| Permissible humidity (operation)        | 5 % ... 95 % (non-condensing) |

## Approvals

### CE

|             |              |
|-------------|--------------|
| Certificate | CE-compliant |
|-------------|--------------|

### ATEX

|                |                        |
|----------------|------------------------|
| Identification | II 3 G Ex ec IIC T4 Gc |
| Certificate    | BVS 19 ATEX E 079 X    |

### IECEX

|                |                    |
|----------------|--------------------|
| Identification | Ex ec IIC T4 Gc    |
| Certificate    | IECEX BVS 19.0068X |

### CCC / China-Ex

|                |                 |
|----------------|-----------------|
| Identification | Ex ec IIC T4 Gc |
|----------------|-----------------|

### UL, USA/Canada

|                |                                       |
|----------------|---------------------------------------|
| Identification | UL 508 Listed                         |
|                | Class I, Div. 2, Groups A, B, C, D T6 |
|                | Class I, Zone 2, Group IIC T6         |

### EAC Ex

|                |                                 |
|----------------|---------------------------------|
| Identification | Ex ec IIC T4 Gc                 |
| Certificate    | BY/112 02.01 TP012 103.01 00079 |

## EMC data

|                               |                                                                      |
|-------------------------------|----------------------------------------------------------------------|
| Electromagnetic compatibility | Conformance with EMC directive                                       |
| Noise immunity                | EN 61000-6-2                                                         |
| Note                          | When being exposed to interference, there may be minimal deviations. |

### Noise emission

|                       |              |
|-----------------------|--------------|
| Standards/regulations | EN 61000-6-4 |
|-----------------------|--------------|

## Standards and regulations

|                      |                 |
|----------------------|-----------------|
| Electrical isolation | 2-way isolation |
|----------------------|-----------------|

### GB Standard

|                       |             |
|-----------------------|-------------|
| Standards/regulations | GB/T 3836.1 |
|                       | GB/T 3836.3 |

## Mounting

|                   |                   |
|-------------------|-------------------|
| Mounting type     | DIN rail mounting |
| Mounting position | any               |


# MINI MCR-2-I-I-ILP - Input isolator

2901994


<https://www.phoenixcontact.com/us/products/2901994>

## Drawings

Application drawing



Block diagram



# MINI MCR-2-I-I-ILP - Input isolator



2901994

<https://www.phoenixcontact.com/us/products/2901994>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2901994>



**EAC**

Approval ID: RU C-DE.A\*30.B.01082



**UL Listed**

Approval ID: E238705



**cUL Listed**

Approval ID: E238705



**IECEx**

Approval ID: IECEx BVS 19.0068X



**cUL Listed**

Approval ID: FILE E 196811



**UL Listed**

Approval ID: E196811



**ATEX**

Approval ID: BVS 19 ATEX E 079 X



**EAC Ex**

Approval ID: TP012 103.01 00079



**CCC**

Approval ID: 2021122310114155

# MINI MCR-2-I-I-ILP - Input isolator

2901994

<https://www.phoenixcontact.com/us/products/2901994>



## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27210120 |
| ECLASS-15.0 | 27210120 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC002653 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121000 |
|-------------|----------|

# MINI MCR-2-I-I-ILP - Input isolator



2901994

<https://www.phoenixcontact.com/us/products/2901994>

## Environmental product compliance

### EU RoHS

|                                         |              |
|-----------------------------------------|--------------|
| Fulfills EU RoHS substance requirements | Yes          |
| Exemption                               | 7(a), 7(c)-I |

### China RoHS

|                                        |                                                                                                                                                                                                                                   |
|----------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-50                                                                                                                                                                                                                           |
|                                        | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |                                      |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1)                 |
| SCIP                                | a7fb1e42-0ff9-4ffe-8a95-48b83a5aa925 |

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)