

MINI MCR-2-PTB - Power terminal block



2902066

<https://www.phoenixcontact.com/us/products/2902066>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Power terminal with plug-in connection technology for delivering the supply voltage to the DIN rail connector. Monitoring of the supply voltages in combination with the fault monitoring module. Screw connection technology

Product description

The power terminal with plug-in connection technology is used to deliver the supply voltage to the DIN rail connector. Two separate voltage inputs permit a redundant and diode-decoupled power supply up to a maximum current of 3.2 A. The FM power terminal offers the additional functions of monitoring in combination with the MINI MCR-2-FM-RC(-PT) fault monitoring module (Order No.: 2904504, 2904508), the flexible, redundant supply of one or both module sides, and an extended supply voltage range of 9.6...30 V DC. The power terminal supports NFC communication.

Commercial data

Item number	2902066
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	C404
Product key	DK112Z
GTIN	4046356649933
Weight per piece (including packing)	118 g
Weight per piece (excluding packing)	98 g
Customs tariff number	85389099
Country of origin	DE

MINI MCR-2-PTB - Power terminal block



2902066

<https://www.phoenixcontact.com/us/products/2902066>

Technical data

Notes

Note on application

Note on application

As things stand now, we are preparing the product so that, as of December 11, 2027, it will comply with the requirements of the EU Cyber Resilience Act (CRA) based on the information currently available regarding the CRA.

Utilization restriction

EMC note

EMC: class A product, see manufacturer's declaration in the download area

Product properties

Product type

Feed-in module

Electrical properties

Maximum temperature coefficient

< 0.01 %/K

Input data

Input voltage range DC

9.9 V DC ... 30 V DC

Max. input current

3.2 A

Reverse polarity protection

yes

Output data

Output voltage range

9.6 V DC ... 29.7 V DC

Connection data

Input

Connection method

Screw connection

Conductor cross-section, rigid min.

0.14 mm²

Conductor cross-section, rigid max.

2.5 mm²

Conductor cross-section flexible min.

0.14 mm²

Conductor cross-section flexible max.

2.5 mm²

Conductor cross-section AWG min.

24

Conductor cross-section AWG max.

12

Stripping length

10 mm

Screw thread

M3

Tightening torque, min

0.5 Nm

Tightening torque max

0.6 Nm

Interfaces

Interface

NFC interface

Signaling

MINI MCR-2-PTB - Power terminal block



2902066

<https://www.phoenixcontact.com/us/products/2902066>

Operating voltage display	Green LED (PWR 1)
	Green LED (PWR 2)
Error indication	Red LED (ERR 1)
	Red LED (ERR 2)

Dimensions

Width	6.2 mm
Height	109.81 mm
Depth	119.2 mm

Material specifications

Housing material	PBT
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 2
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 2
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 2

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20 (not assessed by UL)
Ambient temperature (operation)	-40 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Maximum altitude	≤ 2000 m
Permissible humidity (operation)	5 % ... 95 % (non-condensing)

Approvals

CE

Certificate	CE-compliant
-------------	--------------

ATEX

Identification	Ex II 3 G Ex ec IIC T4 Gc
Certificate	BVS 20 ATEX E 014X

IECEx

Identification	Ex ec IIC T4 Gc
Certificate	IECEx BVS 20.0010X

CCC / China-Ex

Identification	Ex ec IIC T4 Gc
----------------	-----------------

UL, USA/Canada

Identification	UL 508 Listed
	Class I, Div. 2, Groups A, B, C, D T6
	Class I, Zone 2, Group IIC T6

Shipbuilding approval

Certificate	DNV GL TAA00002UA
-------------	-------------------

MINI MCR-2-PTB - Power terminal block



2902066

<https://www.phoenixcontact.com/us/products/2902066>

EAC Ex

Identification	Ex ec IIC T4 Gc
Certificate	BY/112 02.01 TP012 103.01 00079

Shipbuilding data

Temperature	B
Humidity	B
Vibration	A
EMC	A
Enclosure	Required protection according to the Rules shall be provided upon installation on board

EMC data

Electromagnetic compatibility	Conformance with EMC directive
Noise immunity	EN 61000-6-2
Note	When being exposed to interference, there may be minimal deviations.

Noise emission

Standards/regulations	EN 61000-6-4
-----------------------	--------------

Electrostatic discharge

Standards/regulations	EN 61000-4-2
-----------------------	--------------

Electrostatic discharge

Comments	Safety measures must be taken to prevent electrostatic discharge.
----------	---

Electromagnetic HF field

Designation	Electromagnetic RF field
Standards/regulations	EN 61000-4-3

Fast transients (burst)

Designation	Fast transients (burst)
Standards/regulations	EN 61000-4-4

Surge current load (surge)

Standards/regulations	EN 61000-4-5
-----------------------	--------------

Conducted interference

Designation	Conducted interferences
Standards/regulations	EN 61000-4-6

Standards and regulations

Standard designation	GB Standard
Standards/specifications	GB/T 3836.1
	GB/T 3836.3

MINI MCR-2-PTB - Power terminal block



2902066

<https://www.phoenixcontact.com/us/products/2902066>

Mounting

Mounting type	DIN rail mounting
Assembly note	The DIN rail connector can be used for bridging the supply voltage. It can be snapped onto a 35 mm EN 60715 DIN rail.
Mounting position	any

MINI MCR-2-PTB - Power terminal block


2902066

<https://www.phoenixcontact.com/us/products/2902066>



Drawings

Block diagram



MINI MCR-2-PTB - Power terminal block



2902066

<https://www.phoenixcontact.com/us/products/2902066>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2902066>



UL Listed

Approval ID: FILE E 238705



cUL Listed

Approval ID: FILE E 238705

DNV

Approval ID: TAA00002UA



IECEx

Approval ID: IECEx BVS 20.0010X



cUL Listed

Approval ID: E196811



UL Listed

Approval ID: E196811



ATEX

Approval ID: BVS 20 ATEX E 014X



EAC Ex

Approval ID: TP012 103.01 00079



CCC

Approval ID: 2022122313115968

MINI MCR-2-PTB - Power terminal block



2902066

<https://www.phoenixcontact.com/us/products/2902066>

Classifications

ECLASS

ECLASS-13.0	27371392
ECLASS-15.0	27371392

ETIM

ETIM 10.0	EC002886
-----------	----------

UNSPSC

UNSPSC 21.0	39121100
-------------	----------

MINI MCR-2-PTB - Power terminal block



2902066

<https://www.phoenixcontact.com/us/products/2902066>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
	2,2',6,6'-tetrabromo-4,4'-isopropylidenediphenol(CAS: 79-94-7)
SCIP	8dfa4e6a-956d-4070-b6ae-c7b4a2f60968

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com