

RAD-AO4-IFS - I/O extension module



2901538
<https://www.phoenixcontact.com/us/products/2901538>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Radioline - I/O extension module, 4 analog current or voltage outputs (0/4 mA ... 20 mA, 0 V ... 10 V). Product is being prepared for compliance with the Cyber Resilience Act (CRA).

Your advantages

- Easy startup via thumbwheel
- Channel-to-channel electrical isolation
- Extended temperature range of -40 °C ... +70 °C
- Easy module replacement even during operation (hot swap)
- Approved for use in zone 2



ELEKTROGERÄTE
RÜCKNAHME

Commercial data

Item number	2901538
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN26
Product key	DNC61D
GTIN	4046356609166

RAD-AO4-IFS - I/O extension module



2901538

<https://www.phoenixcontact.com/us/products/2901538>

Weight per piece (including packing)	175 g
Weight per piece (excluding packing)	123.91 g
Customs tariff number	85177900
Country of origin	DE

RAD-AO4-IFS - I/O extension module



2901538


<https://www.phoenixcontact.com/us/products/2901538>

Set consists of

ME 17,5 TBUS 1,5/ 5-ST-3,81 KMGY - DIN rail bus connector

2713645

<https://www.phoenixcontact.com/us/products/2713645>



DIN rail bus connector, color: light gray, nominal current: 8 A (parallel contacts), rated voltage (III/2): 125 V, number of positions: 5, product range: TBUS5-17,5..., pitch: 3.81 mm, mounting: DIN rail mounting, locking: without, mounting method: without, type of packaging: packed in cardboard, Item with gold-plated contacts, bus connectors for connecting with electronics housings, 5 parallel contacts

RAD-AO4-IFS - I/O extension module



2901538

<https://www.phoenixcontact.com/us/products/2901538>

Technical data

Notes

Note on application

Note on application	Only for industrial use
Note on application	As things stand now, we are preparing the product so that, as of December 11, 2027, it will comply with the requirements of the EU Cyber Resilience Act (CRA) based on the information currently available regarding the CRA.

Product properties

Product type	Extension module
MTTF	999 Years (SN 29500 standard, temperature 25°C, operating cycle 21%)
	404 Years (SN 29500 standard, temperature 40°C, operating cycle 34.25%)
	156 Years (SN 29500 standard, temperature 40°C, operating cycle 100%)

Insulation characteristics

Overvoltage category	II
Degree of pollution	2

Electrical properties

Rated insulation voltage	60 V (In accordance with EN/IEC 60079-7)
Electrical isolation	50 V (Rated insulation voltage (in each case between the analog outputs / TBUS supply, reinforced insulation in accordance with EN 61010))
	300 V (Rated insulation voltage (to adjacent devices, basic insulation in accordance with EN/IEC 61010))
Test voltage for analog I/Os	1.5 kV AC (50 Hz, 1 min.)
Maximum power dissipation for nominal condition	2.76 W
Transient surge protection	yes

Supply

Supply voltage range	19.2 V DC ... 30.5 V DC (DIN rail bus connector)
Max. current consumption	≤ 115 mA (At 24 V DC, at 25°C)

Output data

Analog

Output name	Analog outputs
Number of outputs	4
Voltage output signal	0 V ... 10 V
Max. voltage output signal	~ 10.83 V
Current output signal	0 mA ... 20 mA
	4 mA ... 20 mA

RAD-AO4-IFS - I/O extension module

2901538

<https://www.phoenixcontact.com/us/products/2901538>



Max. current output signal	~ 21.67 mA
Load	≥ 10 kΩ
	≤ 500 Ω
Resolution	16 bit
Precision	≤ 0.02 % (at 25 °C)
	typ. 0.5 % (Voltage output)
Temperature coefficient, typical	typ. 0.0025 %/K (at -40 °C ... +70 °C)
Protective circuit	Transient protection of outputs

Connection data

Tightening torque	0.5 Nm ... 0.6 Nm
	5 lb _F -in. ... 7 lb _F -in.
Connection method	Screw connection
Stripping length	7 mm
Conductor cross-section, rigid min.	0.2 mm²
Conductor cross-section, rigid max.	2.5 mm²
Conductor cross-section flexible min.	0.2 mm²
Conductor cross-section flexible max.	2.5 mm²
Conductor cross-section AWG min.	24
Conductor cross-section AWG max.	14
Tightening torque	0.5 Nm ... 0.6 Nm
	5 lb _F -in. ... 7 lb _F -in.

Signaling

Status display	LED supply voltage, PWR (green)
	Green LED (bus communication, DAT)
	LED periphery error, ERR (red)

Dimensions

Dimensional drawing	
Width	17.5 mm
Height	113 mm
Depth	114.5 mm

Material specifications

Color (Housing)	gray (RAL 7042)
Material (Housing)	PA 6.6-FR

RAD-AO4-IFS - I/O extension module



2901538

<https://www.phoenixcontact.com/us/products/2901538>

Flammability rating according to UL 94	V0
--	----

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 70 °C (>55°C derating, see technical documentation) -40 °F ... 158 °F (>131°F derating, see technical documentation)
Ambient temperature (storage/transport)	-40 °C ... 85 °C -40 °F ... 185 °F
Altitude	2000 m
Permissible humidity (operation)	20 % ... 85 %
Permissible humidity (storage/transport)	20 % ... 85 %
Shock	16g, 11 ms
Vibration (operation)	in accordance with IEC 60068-2-6: 5g, 10 Hz ... 150 Hz

Approvals

CE

Certificate	CE-compliant
-------------	--------------

ATEX

Identification	⚡ II 3 G Ex ec IIC T4 Gc
Certificate	IBExU 15 ATEX B008 X
Note	Please follow the special installation instructions in the documentation!

IECEx

Identification	Ex ec IIC T4 Gc
Certificate	IECEx IBE 13.0019X

UL, USA/Canada

Identification	508 Listed Class I, Div. 2, Groups A, B, C, D T4A Class I, Zone 2, IIC T4
----------------	---

CCC / China-Ex

Identification	Ex ec IIC T4 Gc
Certificate	2022122310115625

KC approval for South Korea

Certificate	R-R-PCK-2901538
-------------	-----------------

KC-s

Certificate	KTL 20-KA4BO-0148X
-------------	--------------------

Corrosive gas test

Identification	ISA-S71.04-1985 G3 Harsh Group A
----------------	----------------------------------

RAD-AO4-IFS - I/O extension module



2901538

<https://www.phoenixcontact.com/us/products/2901538>

EMC data

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
Noise immunity	EN 61000-6-2

Noise emission

Standards/regulations	EN 61000-6-4
-----------------------	--------------

Standards and regulations

EMC

Standard designation	EMC – Immunity for industrial areas
Standards/specifications	EN 61000-6-2

EMC

Standard designation	EMC interference emissions for industrial environments
Standards/specifications	EN 61000-6-4

Explosive atmospheres

Standard designation	Ex areas, essential requirements
Standards/specifications	EN 60079-0

Explosive atmospheres

Standard designation	Ex areas, type of protection n
Standards/specifications	EN 60079-15

Mounting

Mounting type	DIN rail mounting
Assembly note	on standard DIN rail NS 35 in accordance with EN 60715
Mounting position	any
Useable DIN rail type	DIN rail: 35 mm

RAD-AO4-IFS - I/O extension module


2901538

<https://www.phoenixcontact.com/us/products/2901538>



Drawings

Dimensional drawing



Slim design


RAD-AO4-IFS - I/O extension module

2901538

<https://www.phoenixcontact.com/us/products/2901538>




Application drawing



Wireless module in I/O data mode

Application drawing



Wireless module in PLC/Modbus RTU mode


RAD-AO4-IFS - I/O extension module

2901538

<https://www.phoenixcontact.com/us/products/2901538>



Application drawing



Wireless module in PLC/Modbus RTU dual mode


RAD-AO4-IFS - I/O extension module

2901538

<https://www.phoenixcontact.com/us/products/2901538>



Functional drawing



Assignment of analog inputs and analog outputs


RAD-AO4-IFS - I/O extension module

2901538

<https://www.phoenixcontact.com/us/products/2901538>



Schematic diagram



Function elements


RAD-AO4-IFS - I/O extension module

2901538

<https://www.phoenixcontact.com/us/products/2901538>



Schematic diagram




DIP switches

RAD-AO4-IFS - I/O extension module



2901538
<https://www.phoenixcontact.com/us/products/2901538>

Schematic diagram



Thumbwheel


RAD-AO4-IFS - I/O extension module

2901538

<https://www.phoenixcontact.com/us/products/2901538>



Circuit diagram



Basic circuit diagram

RAD-AO4-IFS - I/O extension module



2901538

<https://www.phoenixcontact.com/us/products/2901538>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2901538>



UL Listed

Approval ID: E238705



cUL Listed

Approval ID: E238705



KC

Approval ID: R-R-PCK-2901538



cUL Listed

Approval ID: E196811



UL Listed

Approval ID: E196811



ATEX

Approval ID: IBExU15ATEXB008 X



KC-s

Approval ID: 20-KA4BO-0148X



IECEx

Approval ID: IECEx IBE 13.0019X



CCC

Approval ID: 2022122310115625

RAD-AO4-IFS - I/O extension module



2901538

<https://www.phoenixcontact.com/us/products/2901538>

Classifications

ECLASS

ECLASS-13.0	27242601
ECLASS-15.0	27242601

ETIM

ETIM 10.0	EC001596
-----------	----------

UNSPSC

UNSPSC 21.0	32151602
-------------	----------

RAD-AO4-IFS - I/O extension module



2901538

<https://www.phoenixcontact.com/us/products/2901538>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	a615c633-202d-48ff-a597-87e0ec513a15

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com