

RIF-2-RPT-LV-24AC/2X21 - Relay module



2903313

<https://www.phoenixcontact.com/us/products/2903313>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Preamsembled relay module with Push-in connection, consisting of: relay base, power contact relay, plug-in display/interference suppression module, and retaining bracket. Contact switching type: 2 changeover contacts. Input voltage: 24 V AC

Product description

The pluggable electromechanical and solid-state relays in the RIFLINE complete product range and the base are recognized and approved in accordance with UL 508. The relevant approvals can be called up at the individual components in question.

Commercial data

Item number	2903313
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	C465
Product key	DK652A
GTIN	4046356732505
Weight per piece (including packing)	109.1 g
Weight per piece (excluding packing)	109.1 g
Customs tariff number	85364110
Country of origin	CN

RIF-2-RPT-LV-24AC/2X21 - Relay module



2903313

<https://www.phoenixcontact.com/us/products/2903313>

Set consists of

RIF-2-BPT/4X21 - Relay base

2900934

<https://www.phoenixcontact.com/us/products/2900934>



Relay base RIF-2..., for industrial relay with 2 or 4 changeover contacts, Push-in connection, plug-in option for input/interference suppression modules, for mounting on NS 35/7,5

REL-IR/L- 24AC/2X21/MS - Single relay

1819069

<https://www.phoenixcontact.com/us/products/1819069>



Plug-in industrial relay with power contacts, 2 changeover contacts, test button, status LED, mechanical switching position indicator, input voltage: 24 V AC

RIF-2-RPT-LV-24AC/2X21 - Relay module

2903313

<https://www.phoenixcontact.com/us/products/2903313>



RIF-V-12-24 UC - Plug-in module

2900945

<https://www.phoenixcontact.com/us/products/2900945>



Plug-in module, for mounting on RIF-1, RIF-2, RIF-3, and RIF-4, with varistor, input voltage: 12 V AC ... 24 V AC / DC $\pm 20\%$

RIF-RH-2-L - Retaining bracket

1899071

<https://www.phoenixcontact.com/us/products/1899071>



Relay retaining bracket, with ejector function and holder for marking material, suitable for RIF-2 relay base, for industrial relay with 28 mm height

RIF-2-RPT-LV-24AC/2X21 - Relay module



2903313

<https://www.phoenixcontact.com/us/products/2903313>

Technical data

Product properties

Product type	Relay Module
Product family	RIFLINE complete
Application	Universal
Operating mode	100% operating factor
Mechanical service life	1x 10 ⁷ cycles

Insulation characteristics: Air clearances and creepage distances between the control circuit and the load circuit

Insulation	Safe isolation
Overvoltage category	III
Pollution degree	2

Insulation characteristics: Air clearances and creepage distances between the load circuits

Insulation	Basic insulation
Overvoltage category	III
Pollution degree	2

Data management status

Date of last data management	18.09.2026
------------------------------	------------

Electrical properties

Maximum power dissipation for nominal condition	1.58 W
Test voltage (Winding/contact)	2.5 kV AC (50 Hz, 1 min., winding/contact)
Test voltage (open contact)	1.2 kV AC (50 Hz, 1 min., open contact)
Test voltage (Changeover contact/changeover contact)	2 kV AC (50 Hz, 1 min., changeover contact/changeover contact)

Air clearances and creepage distances between the control circuit and the load circuit

Rated insulation voltage	250 V _{rms}
Rated surge voltage	4 kV

Air clearances and creepage distances between the load circuits

Rated insulation voltage	250 V _{rms}
Rated surge voltage	4 kV

Input data

Coil side

Nominal input voltage U _N	24 V AC
Input voltage range	19.2 V AC ... 38.4 V AC
Drive and function	monostable
Drive (polarity)	non-polarized
Typical input current at U _N	45 mA AC
Typical response time	15 ms
Typical release time	10 ms

RIF-2-RPT-LV-24AC/2X21 - Relay module



2903313

<https://www.phoenixcontact.com/us/products/2903313>

Typical release voltage	5.8 V
Coil voltage	24 V
Status display	Yellow LED
Bouncing time	10 ms

Output data

Switching

Contact switching type	2 changeover contacts
Type of switch contact	Single contact
Contact material	AgNi
Maximum switching voltage	250 V AC
	300 V DC
Minimum switching voltage	12 V
Limiting continuous current	12 A
Maximum inrush current	24 A
Min. switching current	10 mA
Interrupting rating (ohmic load) max.	288 W (24 V DC)
	130 W (48 V DC)
	90 W (60 V DC)
	66 W (110 V DC)
	88 W (220 V DC)
	3000 VA (250 V AC)
Switching capacity	4 A (24 V, DC13)
	2 A (250 V, AC15)

Connection data

Connection method	Push-in connection
Stripping length	8 mm
Conductor cross-section rigid	0.14 mm ² ... 1.5 mm ²
Conductor cross-section flexible	0.14 mm ² ... 1.5 mm ²
	0.14 mm ² ... 1.5 mm ² (Ferrule with plastic sleeve)
	0.14 mm ² ... 1 mm ² (Ferrule with plastic sleeve, two conductors on double terminal block)
Conductor cross-section AWG	26 ... 16 (solid)
	26 ... 16 (flexible)

Dimensions

Item dimensions

Width	31 mm
Height	96 mm
Depth	67.5 mm

Material specifications

Color	gray (RAL 7042)
-------	-----------------

RIF-2-RPT-LV-24AC/2X21 - Relay module



2903313

<https://www.phoenixcontact.com/us/products/2903313>

Flammability rating according to UL 94 (Housing)	V0 (Housing)
--	--------------

Environmental and real-life conditions

Ambient conditions

Degree of protection (Relay base)	IP20 (Relay base)
Degree of protection (Relay)	RT II (Relay)
Ambient temperature (operation)	-40 °C ... 50 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C

Standards and regulations

Air clearances and creepage distances between the control circuit and the load circuit

Standards/regulations	IEC 60947-5-1
-----------------------	---------------

Air clearances and creepage distances between the load circuits


Standards/regulations	IEC 60947-5-1
-----------------------	---------------

Mounting

Mounting type	DIN rail mounting
Assembly note	in rows with zero spacing
Mounting position	any

Drawings


Diagram



① DC coil (observe contact derating)


② AC coil (observe contact derating)

Operating voltage range



Interrupting rating


Diagram



① 250 V AC, Ohmic load

Electrical service life

Circuit diagram



AC coils

RIF-2-RPT-LV-24AC/2X21 - Relay module



2903313

<https://www.phoenixcontact.com/us/products/2903313>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2903313>



CSA

Approval ID: 76787

DNV

Approval ID: TAA000018V

RIF-2-RPT-LV-24AC/2X21 - Relay module



2903313

<https://www.phoenixcontact.com/us/products/2903313>

Classifications

ECLASS

ECLASS-13.0	27371601
ECLASS-15.0	27371601

ETIM

ETIM 10.0	EC001437
-----------	----------

UNSPSC

UNSPSC 21.0	39122300
-------------	----------

RIF-2-RPT-LV-24AC/2X21 - Relay module



2903313
<https://www.phoenixcontact.com/us/products/2903313>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes
Exemption	7(c)-I
China RoHS	
Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com