

# RIF-2-RPT-LDP-24DC/2X21 - Relay module



2903315

<https://www.phoenixcontact.com/us/products/2903315>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Preamsembled relay module with Push-in connection, consisting of: relay base, power contact relay, and retaining bracket. Contact switching type: 2 changeover contacts. Input voltage: 24 V DC

## Product description

The pluggable electromechanical and solid-state relays in the RIFLINE complete product range and the base are recognized and approved in accordance with UL 508. The relevant approvals can be called up at the individual components in question.

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 2903315       |
| Packing unit                         | 10 pc         |
| Minimum order quantity               | 10 pc         |
| Sales key                            | C465          |
| Product key                          | DK652A        |
| GTIN                                 | 4046356732178 |
| Weight per piece (including packing) | 108.83 g      |
| Weight per piece (excluding packing) | 100 g         |
| Customs tariff number                | 85364110      |
| Country of origin                    | CN            |

# RIF-2-RPT-LDP-24DC/2X21 - Relay module



2903315

<https://www.phoenixcontact.com/us/products/2903315>

## Set consists of

### RIF-2-BPT/4X21 - Relay base

2900934

<https://www.phoenixcontact.com/us/products/2900934>



Relay base RIF-2..., for industrial relay with 2 or 4 changeover contacts, Push-in connection, plug-in option for input/interference suppression modules, for mounting on NS 35/7,5

---

### REL-IR/LDP- 24DC/2X21/MS - Single relay

1819045

<https://www.phoenixcontact.com/us/products/1819045>



Plug-in industrial relay with power contacts, 2 changeover contacts, test button, status LED, freewheeling diode, mechanical switching position indicator, polarity: A1+, A2-, input voltage: 24 V DC

# RIF-2-RPT-LDP-24DC/2X21 - Relay module



2903315

<https://www.phoenixcontact.com/us/products/2903315>

## RIF-RH-2-L - Retaining bracket

1899071

<https://www.phoenixcontact.com/us/products/1899071>



Relay retaining bracket, with ejector function and holder for marking material, suitable for RIF-2 relay base, for industrial relay with 28 mm height

# RIF-2-RPT-LDP-24DC/2X21 - Relay module



2903315

<https://www.phoenixcontact.com/us/products/2903315>

## Technical data

### Product properties

|                         |                           |
|-------------------------|---------------------------|
| Product type            | Relay Module              |
| Product family          | RIFLINE complete          |
| Application             | Universal                 |
| Operating mode          | 100% operating factor     |
| Mechanical service life | 1x 10 <sup>7</sup> cycles |

#### Insulation characteristics:

|                      |                |
|----------------------|----------------|
| Insulation           | Safe isolation |
| Overvoltage category | III            |
| Pollution degree     | 2              |

#### Insulation characteristics:

|                      |                  |
|----------------------|------------------|
| Insulation           | Basic insulation |
| Overvoltage category | III              |
| Pollution degree     | 2                |

#### Data management status

|                              |            |
|------------------------------|------------|
| Date of last data management | 18.09.2026 |
|------------------------------|------------|

### Electrical properties

|                                                      |                                                                |
|------------------------------------------------------|----------------------------------------------------------------|
| Maximum power dissipation for nominal condition      | 1.01 W                                                         |
| Test voltage (Winding/contact)                       | 2.5 kV AC (50 Hz, 1 min., winding/contact)                     |
| Test voltage (open contact)                          | 1.2 kV AC (50 Hz, 1 min., open contact)                        |
| Test voltage (Changeover contact/changeover contact) | 2 kV AC (50 Hz, 1 min., changeover contact/changeover contact) |
| Rated insulation voltage                             | 250 V <sub>rms</sub>                                           |
| Rated surge voltage                                  | 4 kV                                                           |
| Rated insulation voltage                             | 250 V <sub>rms</sub>                                           |
| Rated surge voltage                                  | 4 kV                                                           |

### Input data

#### Coil side

|                                         |                       |
|-----------------------------------------|-----------------------|
| Nominal input voltage U <sub>N</sub>    | 24 V DC               |
| Input voltage range                     | 18 V DC ... 40.8 V DC |
| Drive and function                      | monostable            |
| Drive (polarity)                        | polarized             |
| Typical input current at U <sub>N</sub> | 32 mA DC              |
| Typical response time                   | 15 ms                 |
| Typical release time                    | 18 ms                 |
| Typical release voltage                 | 2.4 V                 |
| Coil voltage                            | 24 V                  |
| Status display                          | Yellow LED            |

# RIF-2-RPT-LDP-24DC/2X21 - Relay module



2903315

<https://www.phoenixcontact.com/us/products/2903315>

|               |       |
|---------------|-------|
| Bouncing time | 10 ms |
|---------------|-------|

## Output data

### Switching

|                                       |                                                                                                                  |
|---------------------------------------|------------------------------------------------------------------------------------------------------------------|
| Contact switching type                | 2 changeover contacts                                                                                            |
| Type of switch contact                | Single contact                                                                                                   |
| Contact material                      | AgNi                                                                                                             |
| Maximum switching voltage             | 250 V AC<br>300 V DC                                                                                             |
| Minimum switching voltage             | 12 V                                                                                                             |
| Limiting continuous current           | 12 A                                                                                                             |
| Maximum inrush current                | 24 A                                                                                                             |
| Min. switching current                | 10 mA                                                                                                            |
| Interrupting rating (ohmic load) max. | 288 W (24 V DC)<br>130 W (48 V DC)<br>90 W (60 V DC)<br>66 W (110 V DC)<br>88 W (220 V DC)<br>3000 VA (250 V AC) |
| Switching capacity                    | 4 A (24 V, DC13)<br>2 A (250 V, AC15)                                                                            |

## Connection data

|                                  |                                                                                                                                                                                                                                                 |
|----------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Connection method                | Push-in connection                                                                                                                                                                                                                              |
| Stripping length                 | 8 mm                                                                                                                                                                                                                                            |
| Conductor cross-section rigid    | 0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>                                                                                                                                                                                                    |
| Conductor cross-section flexible | 0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup><br>0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> (Ferrule with plastic sleeve)<br>0.14 mm <sup>2</sup> ... 1 mm <sup>2</sup> (Ferrule with plastic sleeve, two conductors on double terminal block) |
| Conductor cross-section AWG      | 26 ... 16 (solid)<br>26 ... 16 (flexible)                                                                                                                                                                                                       |

## Dimensions

### Item dimensions

|        |         |
|--------|---------|
| Width  | 31 mm   |
| Height | 96 mm   |
| Depth  | 67.5 mm |

## Material specifications

|                                                  |                 |
|--------------------------------------------------|-----------------|
| Color                                            | gray (RAL 7042) |
| Flammability rating according to UL 94 (Housing) | V0 (Housing)    |

## Environmental and real-life conditions

# RIF-2-RPT-LDP-24DC/2X21 - Relay module



2903315

<https://www.phoenixcontact.com/us/products/2903315>

## Ambient conditions

|                                         |                   |
|-----------------------------------------|-------------------|
| Degree of protection (Relay base)       | IP20 (Relay base) |
| Degree of protection (Relay)            | RT II (Relay)     |
| Ambient temperature (operation)         | -40 °C ... 60 °C  |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C  |

## Standards and regulations


|                       |               |
|-----------------------|---------------|
| Standards/regulations | IEC 60947-5-1 |
| Standards/regulations | IEC 60947-5-1 |

## Mounting


|                   |                           |
|-------------------|---------------------------|
| Mounting type     | DIN rail mounting         |
| Assembly note     | in rows with zero spacing |
| Mounting position | any                       |

## Drawings

Diagram




Operating voltage range




Interrupting rating

Diagram



Electrical service life

Circuit diagram



DC coils

# RIF-2-RPT-LDP-24DC/2X21 - Relay module



2903315

<https://www.phoenixcontact.com/us/products/2903315>

## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2903315>

### DNV

Approval ID: TAA000018V

# RIF-2-RPT-LDP-24DC/2X21 - Relay module



2903315

<https://www.phoenixcontact.com/us/products/2903315>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27371601 |
| ECLASS-15.0 | 27371601 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC001437 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39122300 |
|-------------|----------|

# RIF-2-RPT-LDP-24DC/2X21 - Relay module



2903315  
<https://www.phoenixcontact.com/us/products/2903315>

## Environmental product compliance

|                                         |                                                                                                                                                                                                                                   |
|-----------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS                                 |                                                                                                                                                                                                                                   |
| Fulfills EU RoHS substance requirements | Yes                                                                                                                                                                                                                               |
| Exemption                               | 7(c)-I                                                                                                                                                                                                                            |
| China RoHS                              |                                                                                                                                                                                                                                   |
| Environment friendly use period (EFUP)  | EFUP-50                                                                                                                                                                                                                           |
|                                         | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |
| EU REACH SVHC                           |                                                                                                                                                                                                                                   |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt%                                                                                                                                                                                                        |

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)