# VIP-2/PT/FLK20 - Termination board

2903790

https://www.phoenixcontact.com/us/products/2903790

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

VARIOFACE module, with push-in connections and flat-ribbon cable connector, for mounting on NS 35 rails, with pin strip and short and long locking latches for socket strips, 20-pos.

## Commercial data

| | |
|---|---|
| Item number | 2903790 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | C423 |
| Product key | DK2121 |
| GTIN | 4046356796644 |
| Weight per piece (including packing) | 106 g |
| Weight per piece (excluding packing) | 125 g |
| Customs tariff number | 85366990 |
| Country of origin | US |

# Technical data

## Product properties

| | |
|---|---|
| Product type | Interface module |
| Product family | VARIOFACE Professional |
| Number of positions | 20 |
| No. of channels | 2 |
| | 4 |
| | 8 |
| | 16 |

### Insulation characteristics

| | |
|---|---|
| Overvoltage category | II |
| Pollution degree | 2 |

## Electrical properties

| | |
|---|---|
| Operating voltage (AC) | ≤ 25 V AC |
| Operating voltage (DC) | ≤ 60 V DC |
| Current (per branch) | ≤ 1 A |
| Rated surge voltage | 0.6 kV |

## Connection data

### Field level

| | |
|---|---|
| Connection method | Push-in connection |
| Stripping length | 8 mm |
| Conductor cross-section rigid | 0.14 mm² ... 2.5 mm² |
| Conductor cross-section flexible | 0.14 mm² ... 2.5 mm² |
| Conductor cross-section AWG | 26 ... 14 |

### Controller level

| | |
|---|---|
| Connection method | IDC/FLK pin strip |
| Number of connections | 1 |
| Number of positions | 20 |
| Pitch | 2.54 mm |

## Signaling

| | |
|---|---|
| Status display | no |
| Status display present | no |

## Dimensions

### Item dimensions

| | |
|---|---|
| Width | 57.1 mm |
| Height | 72.1 mm |
| Depth | 56 mm |

## Material specifications

| | |
|---|---|
| Color | gray (RAL 7042) |
| Flammability rating according to UL 94 | V0 |
| Housing insulation material | Polyamide PA non-reinforced |

## Environmental and real-life conditions

Ambient conditions

| | |
|---|---|
| Ambient temperature (operation) | -20 °C ... 50 °C |
| Ambient temperature (storage/transport) | -20 °C ... 70 °C |

## Standards and regulations

| | |
|---|---|
| Standards/regulations | IEC 60664 |
| | DIN EN 50178 |

## Mounting

| | |
|---|---|
| Mounting type | DIN rail mounting |
| Mounting position | any |

## Notes

| | |
|---|---|
| Notes on operation | For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met. |

## Drawings

Circuit diagram



## Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/2903790

**CSA**
Approval ID: 2122203

| | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $mm^2$ |
|---|---|---|---|---|
| keine | | | | |
| | 125 V | 1 A | 26 - 14 | - |

**cUL Recognized**
Approval ID: E238705

| | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $mm^2$ |
|---|---|---|---|---|
| keine | | | | |
| | 125 V | 1 A | 26 - 14 | - |

**UL Recognized**
Approval ID: E238705

| | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $mm^2$ |
|---|---|---|---|---|
| keine | | | | |
| | 125 V | 1 A | 26 - 14 | - |

**CSAus**
Approval ID: 2122203

| | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $mm^2$ |
|---|---|---|---|---|
| keine | | | | |
| | 125 V | 1 A | 26 - 14 | - |

## Classifications

### ECLASS

| | |
|---|---|
| ECLASS-13.0 | 27141152 |
| ECLASS-15.0 | 27141152 |

### ETIM

| | |
|---|---|
| ETIM 10.0 | EC002780 |

### UNSPSC

| | |
|---|---|
| UNSPSC 21.0 | 39121400 |

## Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |

China RoHS

| | |
|---|---|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|---|---|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |


Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com



Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com