SCK-M-U-1500V - PV string monitoring module

2903591

https://www.phoenixcontact.com/us/products/2903591

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

CRA-READY



SCK measuring module for monitoring photovoltaic systems, 1 x voltage measurement up to 1500 V DC, 1 x analog output (2 V ... 10 V). Product is being prepared for compliance with the Cyber Resilience Act (CRA).

Product description

In PV system monitoring, PV string measurement plays a central role in increasing efficiency. Detect malfunctions and take countermeasures: the SOLARCHECK PV string monitoring system reliably provides you with information on the performance of your photovoltaic system. The system enables you to respond immediately to power losses in individual strings, which may be caused by damaged panels or defective contacts and cabling, for example.

Your advantages

- Low costs and wiring effort, as an additional power supply unit is not required in the device connection box
- Space-saving installation with the compact design
- Easy integration into monitoring systems with Modbus/RTU communication
- Monitoring of remote indication contacts by means of an additional digital input

Commercial data

Item number	2903591
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	C447
Product key	CMMD12
GTIN	4046356752398
Weight per piece (including packing)	146.6 g
Weight per piece (excluding packing)	116 g
Customs tariff number	90303370
Country of origin	DE

Technical data

Notes

Note on application

Note on application	As things stand now, we are preparing the product so that, as of December 11, 2027, it will comply with the requirements of the EU Cyber Resilience Act (CRA) based on the information currently available regarding the CRA.

Product properties

Product type	Voltage transducer
Product family	SOLARCHECK

Insulation characteristics

Pollution degree	2

Electrical properties

Protective circuit	Surge protection; 33 V suppressor diode

Supply

Nominal supply voltage	24 V DC -10 % ... +25 % (or via SSCK-M-I-8S-20A)
Supply voltage range	21.6 V DC ... 30 V DC
Own current consumption	8 mA (typical)
	65 mA (maximum)

Input data

Measurement

Number of inputs	1
Input voltage range	0 V DC ... 1500 V DC (CAT III)
	0 V DC ... 1000 V DC (UL)
Input resistance of voltage input	2x 20 MΩ
Connection method	Screw connection
Impulse form	DC voltage
Temperature coefficient, typical	< 0.01 %/K
Maximum transmission error	± 1 % (after additional tuning (valid for 100 - 1,500 V DC))

Output data

Signal: analog

Voltage output signal	2 V DC ... 10 V DC
Load	10 kΩ
Cable type	Twisted, shielded

Connection data

Connection method	Screw connection

Stripping length	8 mm
Conductor cross-section rigid	0.2 mm² ... 2.5 mm²
Conductor cross-section flexible	0.2 mm² ... 2.5 mm²
Conductor cross-section AWG	24 ... 12
Tightening torque	0.5 Nm ... 0.6 Nm

Dimensions

Width	22.5 mm
Height	102 mm
Depth	128.5 mm

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-20 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Altitude	≤ 2000 m
Permissible humidity (operation)	≤ 95 % (non-condensing)

Approvals

CE

Certificate	CE-compliant

UL, USA/Canada

Identification	508 Listed

UL, USA

Identification	1741 Recognized

EMC data

Electromagnetic compatibility	Conformance with EMC directive
Low Voltage Directive	Conformance with Low Voltage Directive
Noise immunity	EN 61000-6-2
Note	When being exposed to interference, there may be minimal deviations.

Noise emission

Standards/regulations	EN 61000-6-4

Standards and regulations

Standards/regulations	EN 61010-1
	EN 61010-2-30


Mounting

Mounting type	DIN rail: 35 mm

	DIN rail mounting

Drawings

Block diagram



Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/2903591

UL Recognized
Approval ID: FILE E 325209

EAC
Approval ID: RU*DE.*08.B.01536/19

UL Listed
Approval ID: E140324

cUL Listed
Approval ID: E140324

UL Recognized
Approval ID: FILE E 325209

cUL Listed
Approval ID: E140324

UL Listed
Approval ID: E140324

Classifications

ECLASS

ECLASS-13.0	27210125
ECLASS-15.0	27210125

ETIM

ETIM 10.0	EC002477

UNSPSC

UNSPSC 21.0	39121000

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	N,N-dimethylacetamide(CAS: 127-19-5)
	Lead(CAS: 7439-92-1)
	2,2',6,6'-tetrabromo-4,4'-isopropylidenediphenol(CAS: 79-94-7)
SCIP	68c42f43-49d8-452d-b48c-8eb78674784b

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com