# MACX MCR-VAC-PT - Voltage measuring transducers

2906244

https://www.phoenixcontact.com/us/products/2906244

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



MACX MCR voltage transducer, for AC voltages from 0 V ... 20 V AC to 0 ... 660 V AC, output signal: 0 V ... 10 V/0(4) ... 20 mA

## Product description

MACX MCR voltage measuring transducers capture DC or AC voltages and convert them into standard analog signals. The MACX MCR-VAC voltage measuring transducer captures sinusoidal AC voltages from 0 V AC to 660 V AC. Eight finely graded voltage measuring ranges provide optimum measuring accuracy. The 3-way electrical isolation ensures high operational safety.

## Your advantages

- Adjustable voltage ranges
- Bidirectional output signals
- 3-way isolation
- ZERO/SPAN adjustment ±20 %
- Tool-free parameterization of measured values
- Teach-in configuration of the measured value range

## Commercial data

| | |
|---|---|
| Item number | 2906244 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | C445 |
| Product key | CMMB11 |
| GTIN | 4055626050911 |
| Weight per piece (including packing) | 153 g |
| Weight per piece (excluding packing) | 153.6 g |
| Customs tariff number | 85437090 |
| Country of origin | DE |

## Technical data

### Product properties

| | |
|---|---|
| Product type | Voltage transducer |

### Electrical properties

| | |
|---|---|
| Alignment span | ± 20 % |
| Alignment zero | ± 20 % |
| Protective circuit | Surge protection; 33 V suppressor diode |
| Step response (10-90%) | < 180 ms |
| Maximum temperature coefficient | < 0.015 %/K |
| Maximum transmission error | < 1 % (from an upper range value, 15 Hz ... 65 Hz) |
| | < 1.3 % (from an upper range value, 65 Hz ... 405 Hz) |

Electrical isolation

| | |
|---|---|
| Pollution degree | 2 |

Electrical isolation Measuring circuit to supply circuit and output IEC 61010-2-030

| | |
|---|---|
| Standards/regulations | IEC 61010-2-030 |
| Test voltage | 5.3 kV AC (50 Hz, 60 s) |
| Measuring category | II (1000 V) |
| | III (600 V) |
| | IV (300 V) |
| Insulation | Reinforced insulation |

Electrical isolation Supply circuit to output circuit IEC 61010-1

| | |
|---|---|
| Standards/regulations | IEC 61010-1 |
| Test voltage | 2.2 kV AC (50 Hz, 60 s) |
| Overvoltage category | III (300 V) |
| | IV (150 V) |
| Insulation | Basic insulation |

Supply

| | |
|---|---|
| Nominal supply voltage | 24 V DC (-20 % ... +25 %) |
| Supply voltage range | 19.2 V DC ... 30 V DC |
| Max. current consumption | < 45 mA |

### Input data

Measurement

| | |
|---|---|
| Configurable/programmable | Yes |
| Input voltage range | 0 V AC ... 550 V AC |
| Maximum input voltage | + 660 V AC |
| Frequency range | 15 Hz ... 405 Hz |
| Input resistance of voltage input | 5500 kΩ |
| Impulse form | AC voltage |

Measurement

| | |
|---|---|
| Input voltage range | 0 V AC ... 370 V AC |
| Input resistance of voltage input | 3700 kΩ |

Measurement

| | |
|---|---|
| Input voltage range | 0 V AC ... 250 V AC |
| Input resistance of voltage input | 2500 kΩ |

Measurement

| | |
|---|---|
| Input voltage range | 0 V AC ... 170 V AC |
| Input resistance of voltage input | 1700 kΩ |

Measurement

| | |
|---|---|
| Input voltage range | 0 V AC ... 120 V AC |
| Input resistance of voltage input | 1200 kΩ |

Measurement

| | |
|---|---|
| Input voltage range | 0 V AC ... 80 V AC |
| Input resistance of voltage input | 800 kΩ |

Measurement

| | |
|---|---|
| Input voltage range | 0 V AC ... 54 V AC |
| Input resistance of voltage input | 800 kΩ |

Measurement

| | |
|---|---|
| Input voltage range | 0 V AC ... 36 V AC |
| Input resistance of voltage input | 800 kΩ |

Measurement

| | |
|---|---|
| Input voltage range | 0 V AC ... 24 V AC |
| Input resistance of voltage input | 240 kΩ |

## Output data

Signal: Voltage

| | |
|---|---|
| Voltage output signal | 0 V ... 10 V |
| | 2 V ... 10 V |
| Max. voltage output signal | ≤ 11 V |
| Load/output load voltage output | > 10 kΩ |
| Ripple | 50 mV |

Signal: Current

| | |
|---|---|
| Current output signal | 0 mA ... 20 mA |
| | 4 mA ... 20 mA |
| Max. current output signal | ≤ 22 mA |
| Load/output load current output | < 500 Ω |
| Max. capacitive load | < 1000 pF |
| Max. inductive load | < 1 mH |

## Connection data

| | |
|---|---|
| Connection method | Push-in connection |
| Stripping length | 8 mm |
| Conductor cross-section rigid | 0.2 mm² ... 1.5 mm² |
| Conductor cross-section flexible | 0.2 mm² ... 1.5 mm² |
| Conductor cross-section AWG | 24 ... 16 |

## Dimensions

| | |
|---|---|
| Width | 22.5 mm |
| Height | 118 mm |
| Depth | 114 mm |

## Material specifications

| | |
|---|---|
| Color | gray (RAL 7042) |

## Environmental and real-life conditions

### Ambient conditions

| | |
|---|---|
| Degree of protection | IP20 |
| Ambient temperature (operation) | -25 °C ... 60 °C |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C (non-condensing) |
| Altitude | ≤ 2000 m |
| Permissible humidity (operation) | 10 % ... 95 % (non-condensing) |

## Approvals

### CE

| | |
|---|---|
| Certificate | CE-compliant |

### UL, USA/Canada

| | |
|---|---|
| Identification | UL 61010 Listed |

## EMC data

| | |
|---|---|
| Electromagnetic compatibility | Conformance with EMC directive |
| Low Voltage Directive | Conformance with Low Voltage Directive |
| Noise immunity | EN 61000-6-2 |
| Note | When being exposed to interference, there may be minimal deviations. |

### Noise emission


| | |
|---|---|
| Standards/regulations | EN 61000-6-4 |

## Mounting

| | |
|---|---|
| Mounting type | DIN rail mounting |
| Assembly note | can be aligned with spacing = 10 mm |
| Mounting position | any |

## Drawings

Block diagram



## Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/2906244

**UL Listed**
Approval ID: E330267

**cUL Listed**
Approval ID: FILE E 330267

## Classifications

### ECLASS

| | |
|---|---|
| ECLASS-13.0 | 27210125 |
| ECLASS-15.0 | 27210125 |

### ETIM

| | |
|---|---|
| ETIM 10.0 | EC002477 |

### UNSPSC

| | |
|---|---|
| UNSPSC 21.0 | 39121000 |

## Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 7(a), 7(c)-I |

China RoHS

| | |
|---|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|---|---|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| SCIP | c7e36447-54cd-4d1f-b581-2b41388250bc |

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com