# FLT-SEC-T1+T2-1S-350/25-FM - Type 1+2 special combined lightning current and surge arrester

2905466

https://www.phoenixcontact.com/us/products/2905466

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Plug-in lightning and surge arrester combination, in accordance with Type 1+2/Class I+II, for 1-phase power supply networks, with separate N and PE (L1, PE, N).

## Your advantages

- Surge protection family for universal use with optimum energy coordination from the lightning current arrester to the device protection
- Easy to maintain due to consistently pluggable protection modules
- Excellent level of information provided by mechanical/visual status indicator and remote indication contact
- Optimum protective effect in the event of high-energy lightning currents, thanks to spark gap technology with low residual voltage characteristic
- Maximum protection against dynamic overvoltages for sensitive devices, thanks to direct coordination with varistor arresters connected in parallel

## Commercial data

| | |
|---|---|
| Item number | 2905466 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | CL01 |
| Product key | CL1241 |
| GTIN | 4046356950169 |
| Weight per piece (including packing) | 654.3 g |
| Weight per piece (excluding packing) | 631.5 g |
| Customs tariff number | 85363030 |
| Country of origin | DE |

## Technical data

### Product properties

| | |
|---|---|
| Product type | Arrester combination |
| Product family | SEC Family |
| IEC test classification | I + II |
| | T1 + T2 |
| EN type | T1 + T2 |
| IEC power supply system | TN-S |
| | TT |
| Type | DIN rail module, two-section, divisible |
| Number of positions | 2 |
| Surge protection fault message | Optical, remote indicator contact |
| Number of ports | One |

Insulation characteristics

| | |
|---|---|
| Overvoltage category | III |
| Pollution degree | 2 |

### Electrical properties

| | |
|---|---|
| Nominal frequency $f_N$ | 50 Hz (60 Hz) |

Indicator/remote signaling

| | |
|---|---|
| Connection name | Remote fault indicator contact |
| Switching function | Changeover contact |
| Operating voltage | 12 V AC ... 250 V AC |
| | 125 V DC (200 mA DC) |
| Operating current | 10 mA AC ... 1 A AC |
| | 1 A DC (30 V DC) |

### Connection data


| | |
|---|---|
| Connection method | Screw connection |
| Screw thread | M5 |
| Tightening torque | 4.5 Nm |
| Stripping length | 18 mm |
| Conductor cross-section flexible | 2.5 mm² ... 35 mm² |
| Conductor cross-section rigid | 2.5 mm² ... 35 mm² |
| Conductor cross-section AWG | 13 ... 2 |
| Connection method | Fork-type cable lug |
| Conductor cross-section flexible | 1.5 mm² ... 16 mm² |

Remote fault indicator contact

| | |
|---|---|
| Connection method | Plug-in/screw connection via COMBICON |

| | |
|---|---|
| Screw thread | M2 |
| Tightening torque | 0.25 Nm |
| Stripping length | 7 mm |
| Conductor cross-section flexible | 0.14 mm² ... 1.5 mm² |
| Conductor cross-section rigid | 0.14 mm² ... 1.5 mm² |
| Conductor cross-section AWG | 28 ... 16 |

## Dimensions

| | |
|---|---|
| Dimensional drawing |  |
| Width | 71.2 mm |
| Height | 95.2 mm |
| Depth | 74.5 mm (incl. DIN rail 7.5 mm) |
| Horizontal pitch | 4 HP |

## Material specifications

| | |
|---|---|
| Color (Male connector) | light gray (RAL 7035) |
| Color (Base element) | gray (RAL 7042) |
| Flammability rating according to UL 94 | V-0 |
| CTI value of material | 600 |
| Insulating material | PA6.6-FR 20% GF |
| | PBT-FR |
| Material group | I |
| Housing material | PA 6.6-FR 20 % GF |
| | PBT-FR |

## Mechanical properties

Mechanical data

| | |
|---|---|
| Open side panel | No |

## Protective circuit

| | |
|---|---|
| Mode of protection | L-N |
| | L-PE |
| | N-PE |
| Direction of action | 1L-N & N-PE |
| Nominal voltage $U_N$ | 240 V AC (TN-S) |
| | 240 V AC (TT) |
| Nominal frequency $f_N$ | 50 Hz (60 Hz) |
| Maximum continuous operating voltage $U_C$ | 350 V AC |

| | |
|---|---|
| Rated load current $I_L$ | 125 A (< 55 °C) |
| Protective conductor current $I_{PE}$ | ≤ 0.01 mA |
| Operating effective current $I_C$ at $U_N$ | ≤ 0.01 mA |
| Nominal discharge current $I_n$ (8/20) µs (L-N) | 25 kA |
| Nominal discharge current $I_n$ (8/20) µs (L-PE) | 25 kA |
| Nominal discharge current $I_n$ (8/20) µs (N-PE) | 100 kA |
| Impulse discharge current (10/350) µs (L-N), charge | 12.5 As |
| Impulse discharge current (10/350) µs (L-N), specific energy | 160 kJ/Ω |
| Impulse discharge current (10/350) µs (L-N), peak current value $I_{imp}$ | 25 kA |
| Impulse discharge current (10/350) µs (L-PE), charge | 12.5 As |
| Impulse discharge current (10/350) µs (L-PE), specific energy | 160 kJ/Ω |
| Impulse discharge current (10/350) µs (L-PE), peak current value $I_{imp}$ | 25 kA |
| Impulse discharge current (10/350) µs (N-PE), charge | 50 As |
| Impulse discharge current (10/350) µs (N-PE), specific energy | 2500 kJ/Ω |
| Impulse discharge current (10/350) µs (N-PE), peak current value $I_{imp}$ | 100 kA |
| Follow current quenching capacity $I_{fi}$ (L-N) | 25 kA (264 V AC) |
| | 3 kA (350 V AC) |
| Follow current interrupt rating $I_{fi}$ (N-PE) | 100 A (350 V AC) |
| Short-circuit current rating $I_{SCCR}$ | 25 kA (264 V AC) |
| | 3 kA (350 V AC) |
| Voltage protection level $U_p$ (L-N) | ≤ 1.5 kV |
| Voltage protection level $U_p$ (L-PE) | ≤ 2.2 kV |
| Voltage protection level $U_p$ (N-PE) | ≤ 1.5 kV |
| Residual voltage $U_{res}$ (L-N) | ≤ 1.5 kV (at $I_n$) |
| | ≤ 1.2 kV (at 10 kA) |
| | ≤ 1 kV (at 5 kA) |
| | ≤ 0.9 kV (at 3 kA) |
| Residual voltage $U_{res}$ (L-PE) | ≤ 2.2 kV (at $I_n$) |
| | ≤ 2 kV (at 10 kA) |
| | ≤ 1.8 kV (at 5 kA) |
| | ≤ 1.6 kV (at 3 kA) |
| Residual voltage $U_{res}$ (N-PE) | ≤ 1.5 kV (at $I_n$) |
| | ≤ 1 kV (at 10 kA) |
| | ≤ 0.9 kV (at 5 kA) |
| | ≤ 0.8 kV (at 3 kA) |
| TOV behavior at $U_T$ (L-N) | 415 V AC (5 s / withstand mode) |
| | 457 V AC (120 min / safe failure mode) |
| TOV behavior at $U_T$ (N-PE) | 1200 V AC (200 ms / withstand mode) |
| Response time $t_A$ (L-N) | ≤ 25 ns |
| Response time $t_A$ (L-PE) | ≤ 100 ns |

| | |
|---|---|
| Response time $t_A$ (N-PE) | ≤ 100 ns |
| Max. backup fuse with V-type through wiring | 125 A (gG) |
| Max. backup fuse with branch wiring | 315 A (gG) |

Additional technical data

| | |
|---|---|
| Maximum discharge current $I_{max}$ (8/20) µs | 100 kA |

## Environmental and real-life conditions

Ambient conditions

| | |
|---|---|
| Degree of protection | IP20 (only when all terminal points are used) |
| Ambient temperature (operation) | -40 °C ... 80 °C |
| Ambient temperature (storage/transport) | -40 °C ... 80 °C |
| Altitude | ≤ 2000 m (amsl) |
| Permissible humidity (operation) | 5 % ... 95 % |
| Shock (operation) | 30g (Half-sine / 11 ms / 3x ±X, ±Y, ±Z) |
| Vibration (operation) | 5g (5 - 500 Hz/2.5 h/X, Y, Z) |

## Approvals

UL specifications

| | |
|---|---|
| Maximum continuous operating voltage MCOV (L-N) | 264 V AC |
| Maximum continuous operating voltage MCOV (L-G) | 264 V AC |
| Maximum continuous operating voltage MCOV (N-G) | 350 V AC |
| Short-circuit current rating (SCCR) | 50 kA |
| Voltage protection rating VPR (L-N) | 1200 V |
| Voltage protection rating VPR (L-G) | 1500 V |
| Voltage protection rating VPR (N-G) | 1200 V |
| Nominal discharge current $I_n$ | 20 kA |
| Mode of protection | L-N |
| | L-G |
| | N-G |
| Nominal voltage | 240 V AC |
| Rated load current $I_L$ | 50 A |
| Power distribution system | Single phase |
| Nominal frequency | 50/60 Hz |
| SPD Type | 2CA |

UL indicator/remote signaling

| | |
|---|---|
| Operating voltage | 125 V AC |
| AC operating current | 1 A AC |

UL connection data

| | |
|---|---|
| Tightening torque | 40 $lb_f$-in. |
| Conductor cross-section AWG | 3 ... 2 |

## Standards and regulations

| | |
|---|---|
| Standards/specifications | IEC 61643-11 |
| Note | 2011 |

EN 61643-11


| | |
|---|---|
| Standards/specifications | EN 61643-11 |
| Note | 2012 |

## Mounting

| | |
|---|---|
| Mounting type | DIN rail: 35 mm |

## Drawings


Dimensional drawing



Product drawing



Circuit diagram



## Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/2905466

**cUL Recognized**
Approval ID: FILE E 330181

**UL Recognized**
Approval ID: FILE E 330181

**IECEE CB Scheme**
Approval ID: NL-58252

**CCA**
Approval ID: NTR-NL 7736

**UAE-RoHS**
Approval ID: 23-10-88887

## Classifications

### ECLASS

| | |
|---|---|
| ECLASS-13.0 | 27171204 |
| ECLASS-15.0 | 27171204 |

### ETIM

| | |
|---|---|
| ETIM 10.0 | EC001457 |

### UNSPSC

| | |
|---|---|
| UNSPSC 21.0 | 39121600 |

## Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 6(c) |

China RoHS

| | |
|---|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|---|---|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| SCIP | 8090eb22-576d-4dd7-bd5b-ae38816cb202 |


Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com



Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com