PT 5-HF-24DC-ST - Surge protection device

2906002

https://www.phoenixcontact.com/us/products/2906002

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.





PT protective plug with HF protective circuit for 4 signal wires. Nominal voltage: 24 V DC

Your advantages

- Easy testing and documentation with CHECKMASTER 2 with pluggable protective modules
- Maximum ease of maintenance, thanks to the 2-piece design
- Easy selection for all possible demands in MCR applications with a complete product portfolio
- The signal is not influenced during maintenance work, thanks to the impedance-neutral insertion and removal of protective plugs

Commercial data

Item number	2906002
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	CL03
Product key	CL3121
GTIN	4055626013398
Weight per piece (including packing)	35.5 g
Weight per piece (excluding packing)	22.05 g
Customs tariff number	85363010
Country of origin	DE

Technical data

Product properties

Product type	Surge protection for information technology
Product family	PLUGTRAB PT
IEC test classification	C1
	C2
	C3
	D1
Type	Male
Number of positions	5
Wire pairs per module	2

Insulation characteristics

Overvoltage category	III
Pollution degree	2


Electrical properties

Nominal voltage U_N	24 V DC

Connection data

Connection method	Screw connection (in connection with the base element)
Screw thread	M3
Tightening torque	0.8 Nm
Conductor cross-section flexible	0.2 mm² ... 2.5 mm²
Conductor cross-section rigid	0.2 mm² ... 4 mm²
Conductor cross-section AWG	24 ... 12

Dimensions

Dimensional drawing	
Width	17.7 mm
Height	45 mm
Depth	52 mm
Horizontal pitch	1 HP

Material specifications

Color	black (RAL 9005)
Flammability rating according to UL 94	V-0
Housing material	PA 6.6

Mechanical properties

Mechanical data

Open side panel	No

Protective circuit

Direction of action	Line-Line & Line-Signal Ground/Shield & optional Signal Ground/Shield-Earth Ground
Nominal voltage U_N	24 V DC
Maximum continuous operating voltage U_C	28 V DC
Rated current	450 mA (45 °C)
Operating effective current I_C at U_C	≤ 5 µA
Protective conductor current I_{PE}	≤ 5 µA (with PT 2X2-BE)
	≤ 1 µA (with PT 2X2+F-BE)
Nominal discharge current I_n (8/20) µs (line-line)	10 kA
Nominal discharge current I_n (8/20) µs (line-ground)	10 kA (with PT 2X2+F-BE)
	10 kA (with PT 2X2-BE)
Pulse discharge current I_{imp} (10/350) µs	2.5 kA (with PT 2X2-BE)
	2.5 kA (with PT 2X2+F-BE)
Total discharge current I_{Total} (8/20) µs	20 kA
Nominal pulse current Ian (10/1000) µs (line-line)	25 A
Voltage protection level U_p (line-line)	≤ 150 V (C1 - 1 kV / 500 A)
	≤ 165 V (C2 - 10 kV / 5 kA)
	≤ 450 V (C2 - 10 kA)
	≤ 50 V (C3 - 25 A)
Voltage protection level U_p (line-earth)	≤ 150 V (C1 - 1 kV / 500 A)
	≤ 700 V (C1 - 1 kV / 500 A with PT 2X2+F-BE)
	≤ 165 V (C2 - 10 kV / 5 kA)
	≤ 900 V (C2 - 10 kV / 5 kA with PT 2X2+F-BE)
	≤ 450 V (C2 - 10 kA)
	≤ 1000 V (C2 - 10 kA with PT 2X2+F-BE)
	≤ 50 V (C3 - 25 A)
	≤ 800 V (C3 - 25 A with PT 2X2+F-BE)
Voltage protection level U_p (line-signal ground)	≤ 150 V (C1 - 1 kV / 500 A)
	≤ 150 V (C1 - 1 kV / 500 A with PT 2X2+F-BE)
	≤ 165 V (C2 - 10 kV / 5 kA)
	≤ 165 V (C2 - 10 kV / 5 kA with PT 2X2-BE)
	≤ 450 V (C2 - 10 kA)
	≤ 450 V (C2 - 10 kV / 5 kA with PT 2X2-BE)
	≤ 50 V (C3 - 25 A)
	≤ 50 V (C3 - 25 A with PT 2X2-BE)
Response time t_A (line-line)	≤ 500 ns
Response time t_A (line-earth)	≤ 500 ns
Input attenuation aE, sym.	typ. 0.3 dB (≤ 13 MHz / 100 Ω)

Cut-off frequency fg (3 dB), sym. in 100 Ω system	typ. 70 MHz
Capacity (Core-Core)	typ. 23 pF
Resistance per path	2.2 Ω ±10 %
Surge protection fault message	none
Max. required back-up fuse	500 mA (T)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Altitude	≤ 2000 m (amsl)

Standards and regulations


Standards/specifications	EN 61643-21/A2
Note	2013
Standards/specifications	IEC 61643-21/A2
Note	2012

Mounting

Mounting type	on base element


Drawings

Dimensional drawing



The figure shows the complete module consisting of a base element and connector

Circuit diagram



Classifications

ECLASS

ECLASS-13.0	27171503
ECLASS-15.0	27171503

ETIM

ETIM 10.0	EC001466

UNSPSC

UNSPSC 21.0	39121600

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	aee37143-61f4-4454-bad8-06e456adba78

EF3.1 Climate Change

CO2e kg	42.144 kg CO2e

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com