

TTC-6P-3-HF-M-12DC-UT-I - Surge protection device



2906744

<https://www.phoenixcontact.com/us/products/2906744>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



2,5 mm²



SCREW



600 mA

IEC



12 V

IEC



Surge protection, consisting of protective plug and base element, with integrated status indicator and knife disconnection for three signal wires with common reference potential. For HF applications and telecommunications interfaces without supply voltage, EX e approval for zone 2. Can be used in safety-related circuits up to SIL 3.

Your advantages

- Space-saving and cost-saving with a narrow overall width of just 6 mm
- Continuous monitoring of protective devices, plus mechanical status indicator with optional remote signaling
- Finding the right product for all possible requirements in MCR applications is easy, thanks to the complete range of products with customized features
- Easy testing and documentation with CHECKMASTER 2 with pluggable protective modules
- The signal is not influenced during maintenance work, thanks to the impedance-neutral insertion and removal of protective plugs

Commercial data

Item number	2906744
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	CL23
Product key	CL2161
GTIN	4055626134765
Weight per piece (including packing)	57 g
Weight per piece (excluding packing)	46.5 g
Customs tariff number	85363010
Country of origin	DE

Technical data

Product properties

Product type	Surge protection for information technology
Product family	TERMITRAB complete
IEC test classification	C1
	C2
	C3
	D1
Type	DIN rail module, two-section, divisible

Insulation characteristics

Overvoltage category	III
Pollution degree	2

Electrical properties

Nominal voltage U_N	12 V DC
-----------------------	---------


Connection data

Connection method	Screw connection
Screw thread	M3
Tightening torque	0.5 Nm ... 0.6 Nm
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section rigid	0.2 mm ² ... 4 mm ²
Conductor cross-section AWG	24 ... 12

Ex data

Maximum input current	600 mA (T4 / $\leq 30\text{ °C}$)
	500 mA (T4 / $> 30\text{ °C} \dots \leq 50\text{ °C}$)
	400 mA (T4 / $> 50\text{ °C} \dots \leq 70\text{ °C}$)
Maximum input voltage	15 V DC
Altitude	$\leq 2000\text{ m}$ (amsl)
Ambient temperature (operation)	$-40\text{ °C} \dots 70\text{ °C}$ (T4)

Dimensions

Dimensional drawing	
Width	6.2 mm +0.1 mm
Height	105.8 mm
Depth	100 mm (incl. DIN rail 7.5 mm)

TTC-6P-3-HF-M-12DC-UT-I - Surge protection device



2906744

<https://www.phoenixcontact.com/us/products/2906744>

Material specifications

Color (Base element)	gray (RAL 7042)
Color (Male connector)	light gray (RAL 7035)
Flammability rating according to UL 94	V-0
Insulating material	PBT
Housing material	PBT

Mechanical properties

Mechanical data

Open side panel	No
-----------------	----

Protective circuit

Direction of action	Line-Line & Line-Signal Ground/Shield & optional Signal Ground/Shield-Earth Ground
Nominal voltage U_N	12 V DC
Maximum continuous operating voltage U_C	15 V DC 10 V AC
Rated current	600 mA (56 °C)
Operating effective current I_C at U_C	$\leq 100 \mu A$
Protective conductor current I_{PE}	$\leq 200 \mu A$
Nominal discharge current I_n (8/20) μs (line-line)	5 kA
Nominal discharge current I_n (8/20) μs (line-ground)	5 kA
Pulse discharge current I_{imp} (10/350) μs (line-line)	0.5 kA
Pulse discharge current I_{imp} (10/350) μs (line-earth)	0.5 kA
Total discharge current I_{Total} (8/20) μs	10 kA
Voltage protection level U_p (line-line)	$\leq 145 V$ (C1 - 1 kV / 500 A) $\leq 260 V$ (C2 - 10 kV / 5 kA) $\leq 25 V$ (C3 - 25 A) $\leq 30 V$ (C3 - 100 A)
Voltage protection level U_p (line-earth)	$\leq 80 V$ (C1 - 1 kV / 500 A) $\leq 95 V$ (C2 - 10 kV / 5 kA) $\leq 25 V$ (C3 - 25 A) $\leq 30 V$ (C3 - 100 A)
Voltage protection level U_p static (line-line)	$\leq 40 V$ (C1 - 1 kV / 500 A) $\leq 95 V$ (C2 - 10 kV / 5 kA)
Voltage protection level U_p static (line-earth)	$\leq 40 V$ (C1 - 1 kV / 500 A) $\leq 95 V$ (C2 - 10 kV / 5 kA)
Response time t_A (line-line)	$\leq 1 ns$
Response time t_A (line-earth)	$\leq 1 ns$
Input attenuation aE, sym.	typ. 0.3 dB ($\leq 8.7 MHz/150 \Omega$)
Input attenuation aE, asym.	typ. 0.3 dB ($\leq 10.5 MHz/150 \Omega$)
Cut-off frequency f_g (3 dB), sym. in 150 Ω system	typ. 60 MHz
Cut-off frequency f_g (3 dB), asym. (PE) in 150 Ω system	typ. 60 MHz

TTC-6P-3-HF-M-12DC-UT-I - Surge protection device



2906744

<https://www.phoenixcontact.com/us/products/2906744>

Capacity (Core-Core)	typ. 32 pF
Capacity (Core-Earth)	typ. 32 pF
Resistance per path	1.65 Ω $\pm$ 20 %
Surge protection fault message	optical
Max. required back-up fuse	630 mA (FF)
Impulse durability (line-line)	C1 - 1 kV / 500 A
	C2 - 10 kV / 5 kA
	C3 - 100 A
Impulse durability (line-earth)	C1 - 1 kV / 500 A
	C2 - 10 kV / 5 kA
	C3 - 100 A
	D1 - 500 A
Pulse reset time (line-line)	$\leq$ 30 ms
Pulse reset time (line-earth)	$\leq$ 30 ms

Additional technical data

Max. total discharge current $I_{\text{total max}}$ (8/20) μ s	20 kA (1x - non Ex)
--	---------------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Altitude	$\leq$ 4000 m (amsl)
Permissible humidity (operation)	5 % ... 95 %

Approvals

Conformity/Approvals

UL, USA / Canada	Class I, Div. 2, Groups A, B, C, D T4A
------------------	--

Standards and regulations

Standards/specifications	IEC 61643-21
Note	2000 + corrigendum 2001 + A1:2008, modified + A2:2012

EN 61643-21

Standards/specifications	EN 61643-21
Note	2001 + A1:2009 + A2:2013
Standards/specifications	IEC 60079-0
Note	2017
Standards/specifications	IEC 60079-7
Note	2017
Standards/specifications	EN IEC 60079-0
Note	2018
Standards/specifications	EN IEC 60079-7

TTC-6P-3-HF-M-12DC-UT-I - Surge protection device



2906744

<https://www.phoenixcontact.com/us/products/2906744>

Note	2015 + A1:2018
------	----------------

Mounting

Mounting type	DIN rail: TH 35 - 7.5 mm
---------------	--------------------------


TTC-6P-3-HF-M-12DC-UT-I - Surge protection device



2906744
https://www.phoenixcontact.com/us/products/2906744

Drawings

Dimensional drawing




Schematic diagram

TTC-6P-3-HF-M-...-I									
Category	1oo1 architecture, HFT=0				1oo2 architecture, HFT=1				
	PFD _{AVG}	PFH	Used budget of SIL 2 SIF		PFD _{AVG}	PFH	CCF	Used budget of SIL 3 SIF	
			PFD _{AVG}	PFH				PFD _{AVG}	PFH
	1.30x10 ⁻⁴	2.31x10 ⁻⁸ 1/h	1.3 %	2.3 %	6.52x10 ⁻⁶	1.16x10 ⁻⁹ 1/h	5 %	1.3 %	2.3 %
					1.30x10 ⁻⁵	2.31x10 ⁻⁸ 1/h	10 %	1.3 %	2.3 %
Calculation based on exida report, Phoenix Contact 16/06-072 R022 V4R2 exida Profile 1, FMEDA Analysis 2, T _{proof} : 1 year, MT: 10 years, MTTR: 24 hours, PTC: 99%									
Used standards IEC/EN 61508, edition 2010 (device specific) IEC/EN 61511, edition 2016 + COR1:2016 + A1:2017 (system specific)									

Functional safety scenarios

Diagram




Diagram

Derating for Ex-areas (Zone 2, EX ec)

ϑ [°C]	I [mA]
$\leq 30^{\circ}\text{C}$	600 mA
$> 30^{\circ}\text{C} \dots \leq 50^{\circ}\text{C}$	500 mA
$> 50^{\circ}\text{C} \dots \leq 70^{\circ}\text{C}$	400 mA

Circuit diagram



Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2906744>



CSA

Approval ID: 70136717



DNV GL

Approval ID: TAE000027G



UL Listed

Approval ID: FILE E 138168



CSAus

Approval ID: 70136717

UAE-RoHS

Approval ID: 22-06-16783

Functional Safety

Approval ID: 16-06-072 R022 V4R3



IECEx

Approval ID: IECEx BVS 21.0057X



ATEX

Approval ID: BVS 21 ATEX E 052 X



UKCA-EX

Approval ID: DEKRA 23UKEX7003X



cULus Listed

Approval ID: File E 333250



CCC

Approval ID: 2022122304116080

TTC-6P-3-HF-M-12DC-UT-I - Surge protection device



2906744

<https://www.phoenixcontact.com/us/products/2906744>



NEPSI-EX

Approval ID: HT25-037

TTC-6P-3-HF-M-12DC-UT-I - Surge protection device



2906744

<https://www.phoenixcontact.com/us/products/2906744>

Classifications

ECLASS

ECLASS-13.0	27171503
ECLASS-15.0	27171503

ETIM

ETIM 10.0	EC001466
-----------	----------

UNSPSC

UNSPSC 21.0	39121600
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	9796e9a6-ca5f-453e-b032-110b81bc09cd

EF3.1 Climate Change

CO2e kg	1.362 kg CO2e
---------	---------------