


# REL-MR-110DC/21-21 - Single relay



2961202

<https://www.phoenixcontact.com/us/products/2961202>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Plug-in miniature power relay, with power contact, 2 changeover contacts, input voltage 110 V DC

## Your advantages

- RT III-proof (wash-proof)
- Switching current of up to 8 A

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 2961202       |
| Packing unit                         | 10 pc         |
| Minimum order quantity               | 10 pc         |
| Sales key                            | C460          |
| Product key                          | DK6935        |
| GTIN                                 | 4017918158002 |
| Weight per piece (including packing) | 16 g          |
| Weight per piece (excluding packing) | 16.125 g      |
| Customs tariff number                | 85364900      |
| Country of origin                    | CZ            |

## Technical data

### Product properties

|                         |                           |
|-------------------------|---------------------------|
| Product type            | Single relay              |
| Operating mode          | 100% operating factor     |
| Mechanical service life | 3x 10 <sup>7</sup> cycles |

### Insulation characteristics

|                      |                  |
|----------------------|------------------|
| Insulation           | Basic insulation |
| Overvoltage category | III              |
| Pollution degree     | 3                |

### Data management status

|                              |            |
|------------------------------|------------|
| Date of last data management | 01.04.2026 |
|------------------------------|------------|

### Electrical properties

|                                                 |                           |
|-------------------------------------------------|---------------------------|
| Service life electrical                         | see diagram               |
| Maximum power dissipation for nominal condition | 0.45 W                    |
| Test voltage (Winding/contact)                  | 5 kV AC (50 Hz, 1 min.)   |
| Test voltage (Contact/contact)                  | 2.5 kV AC (50 Hz, 1 min.) |
| Test voltage (open contact)                     | 1 kV (50 Hz, 1 min.)      |

### Input data

#### Coil side

|                                         |                          |
|-----------------------------------------|--------------------------|
| Nominal input voltage U <sub>N</sub>    | 110 V DC                 |
| Input voltage range                     | 71.5 V DC ... 272.8 V DC |
| Drive and function                      | monostable               |
| Drive (polarity)                        | non-polarized            |
| Typical input current at U <sub>N</sub> | 4.1 mA                   |
| Typical response time                   | 7 ms                     |
| Typical release time                    | 3 ms                     |
| Coil resistance                         | 26600 Ω ±15 % (at 20 °C) |

### Output data

#### Switching

|                             |                       |
|-----------------------------|-----------------------|
| Contact switching type      | 2 changeover contacts |
| Type of switch contact      | Single contact        |
| Contact material            | AgNi                  |
| Maximum switching voltage   | 250 V AC/DC           |
| Minimum switching voltage   | 5 V (at 10 mA)        |
| Limiting continuous current | 8 A                   |
| Maximum inrush current      | 25 A (20 ms)          |
| Min. switching current      | 10 mA (At 5 V)        |

# REL-MR-110DC/21-21 - Single relay



2961202

<https://www.phoenixcontact.com/us/products/2961202>

|                                       |                        |
|---------------------------------------|------------------------|
| Interrupting rating (ohmic load) max. | 190 W (at 24 V DC)     |
|                                       | 85 W (at 48 V DC)      |
|                                       | 60 W (at 60 V DC)      |
|                                       | 44 W (at 110 V DC)     |
|                                       | 60 W (at 220 V DC)     |
|                                       | 2000 VA (for 250 V AC) |
| Switching capacity                    | 2 A (at 24 V, DC13)    |
|                                       | 0.2 A (at 250 V, DC13) |
|                                       | 3 A (at 24 V, AC15)    |
|                                       | 3 A (at 120 V, AC15)   |
|                                       | 3 A (at 250 V, AC15)   |
| Motor load according to UL 508        | 1/4 HP, 120 V AC       |
|                                       | 1/2 HP, 240 V AC       |

## Connection data

|                   |                          |
|-------------------|--------------------------|
| Connection method | Plug / solder connection |
|-------------------|--------------------------|

## Dimensions

### Item dimensions

|        |         |
|--------|---------|
| Width  | 12.7 mm |
| Height | 29 mm   |
| Depth  | 15.7 mm |

## Material specifications

|       |                  |
|-------|------------------|
| Color | white (RAL 9010) |
|-------|------------------|

## Environmental and real-life conditions

### Ambient conditions

|                                         |                  |
|-----------------------------------------|------------------|
| Degree of protection                    | RT III           |
| Ambient temperature (operation)         | -40 °C ... 85 °C |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C |

## Approvals

### Corrosive gas test

|                |                            |
|----------------|----------------------------|
| Identification | ISA-S71.04. G3 Harsh Group |
|                | EN 60068-2-60              |

## Standards and regulations

|                       |            |
|-----------------------|------------|
| Standards/regulations | IEC 60664  |
|                       | EN 50178   |
|                       | EN 61810-1 |

## Mounting

# REL-MR-110DC/21-21 - Single relay




2961202

<https://www.phoenixcontact.com/us/products/2961202>


|                   |                                                                        |
|-------------------|------------------------------------------------------------------------|
| Assembly note     | Can be aligned without spacing ( $> 70\text{ °C} \geq 2.5\text{ mm}$ ) |
| Mounting position | any                                                                    |

## Drawings

Dimensional drawing




Diagram




- ① DC coils
- ② AC coils

Operating voltage range




Interrupting rating




Electrical service life

Diagram



Service life reduction factor with various cos phi

Diagram



Permissible humidity for operation and storage.


The maximum permissible ambient temperature as specified in the data sheet must be observed.

Area A: Ice buildup at ambient temperatures  $\leq 0^{\circ}\text{C}$  must be prevented

Area B: Condensation at ambient temperatures  $> 0^{\circ}\text{C}$  must be prevented

On 30 full days that are naturally distributed across an entire year, a humidity level of 95% is permissible at an ambient temperature  $\leq 25^{\circ}\text{C}$ .

Circuit diagram




# REL-MR-110DC/21-21 - Single relay



2961202

<https://www.phoenixcontact.com/us/products/2961202>

Drilling plan/solder pad geometry



a = pitch division 2.5 mm

# REL-MR-110DC/21-21 - Single relay



2961202

<https://www.phoenixcontact.com/us/products/2961202>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2961202>



**cUL Recognized**

Approval ID: FILE E 228652



**UL Recognized**

Approval ID: FILE E 228652



**UL Recognized**

Approval ID: FILE E 228652



**VDE Zeichengenehmigung**

Approval ID: 40007758



**cUL Recognized**

Approval ID: FILE E 228652



**cULus Recognized**

Approval ID: E172140

# REL-MR-110DC/21-21 - Single relay



2961202

<https://www.phoenixcontact.com/us/products/2961202>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27371601 |
| ECLASS-15.0 | 27371601 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC001437 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39122300 |
|-------------|----------|

# REL-MR-110DC/21-21 - Single relay



2961202

<https://www.phoenixcontact.com/us/products/2961202>

## Environmental product compliance

|                                         |                                          |
|-----------------------------------------|------------------------------------------|
| EU RoHS                                 |                                          |
| Fulfills EU RoHS substance requirements | Yes, No exemptions                       |
| China RoHS                              |                                          |
| Environment friendly use period (EFUP)  | EFUP-E                                   |
|                                         | No hazardous substances above the limits |
| EU REACH SVHC                           |                                          |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt%               |
| EF3.1 Climate Change                    |                                          |
| CO2e kg                                 | 0.192 kg CO2e                            |

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)