

# PSR-SCP- 24DC/FSP2/2X1/1X2 - Coupling relay



2986575

<https://www.phoenixcontact.com/us/products/2986575>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Safe coupling relay for SIL 2 high- and low-demand applications, couples digital output signals to the periphery, two enabling current paths, one signal contact, module for safe state off applications, integrated test pulse filter, plug-in screw connection, width: 17.5 mm

## Your advantages

- Narrow 17.5 mm housing
- Up to SIL 2 in accordance with EN 61508
- Easy proof test according to IEC 61508 thanks to integrated signal contact
- Long service life thanks to filtering of controller test pulses
- Force-guided contacts in accordance with EN 50205
- 2 enabling current paths
- Couples digital output signals from failsafe controllers to I/O devices (valves, etc.) for electrical isolation and power adaptation



## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 2986575       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | DN01          |
| Product key                          | DNA161        |
| GTIN                                 | 4046356553322 |
| Weight per piece (including packing) | 136.3 g       |
| Weight per piece (excluding packing) | 130.11 g      |
| Customs tariff number                | 85364190      |
| Country of origin                    | DE            |

# PSR-SCP- 24DC/FSP2/2X1/1X2 - Coupling relay



2986575

<https://www.phoenixcontact.com/us/products/2986575>

## Technical data

### Product properties

|                         |                                                                                      |
|-------------------------|--------------------------------------------------------------------------------------|
| Product type            | Coupling relay                                                                       |
| Product family          | PSRclassic                                                                           |
| Application             | Safe switch off                                                                      |
|                         | High demand                                                                          |
|                         | Low demand                                                                           |
| Control                 | 1-channel                                                                            |
| Mechanical service life | 10x 10 <sup>6</sup> cycles                                                           |
| Relay type              | Electromechanical relay with force-guided contacts in accordance with IEC/EN 61810-3 |

### Insulation characteristics

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution  | 2   |

### Times

|                                        |                                                    |
|----------------------------------------|----------------------------------------------------|
| Typ. starting time with U <sub>s</sub> | 50 ms (with U <sub>s</sub> when controlled via A1) |
| Typical release time                   | 50 ms (with U <sub>s</sub> when controlled via A1) |
| Recovery time                          | 1 s                                                |

### Electrical properties

|                                                 |                                                                                                          |
|-------------------------------------------------|----------------------------------------------------------------------------------------------------------|
| Maximum power dissipation for nominal condition | 2.4 W                                                                                                    |
| Nominal operating mode                          | 100% operating factor                                                                                    |
| Rated insulation voltage                        | 250 V AC                                                                                                 |
| Rated surge voltage/insulation                  | Safe isolation, reinforced insulation 6 kV between the control circuits (A1/A2), (31/32), (13/14, 23/24) |

### Supply

|                                                     |                                                             |
|-----------------------------------------------------|-------------------------------------------------------------|
| Designation                                         | A1/A2                                                       |
| Rated control circuit supply voltage U <sub>s</sub> | 24 V DC -15 % / +10 %                                       |
| Rated control supply current I <sub>s</sub>         | typ. 55 mA (typ. with U <sub>s</sub> )                      |
| Power consumption at U <sub>s</sub>                 | typ. 1.32 W                                                 |
| Inrush current                                      | max. 100 mA (typ. with U <sub>s</sub> )                     |
| Filter time                                         | max. 5 ms (in the event of voltage dips at U <sub>s</sub> ) |
|                                                     | max. 2 ms (Test pulse width; high test pulse at A1/A2)      |
|                                                     | ≥ 100 ms (Test pulse rate, high test pulse)                 |
|                                                     | Test pulse rate = 80 x Test pulse width                     |
|                                                     | max. 5 ms (Test pulse width; low test pulse at A1/A2)       |
|                                                     | ≥ 50 ms (Test pulse rate; low test pulse at A1/A2)          |
|                                                     | Test pulse rate = 15 x Test pulse width                     |
| Protective circuit                                  | Surge protection                                            |
|                                                     | Suppressor diode, 33 V (A1 - A2)                            |

# PSR-SCP- 24DC/FSP2/2X1/1X2 - Coupling relay



2986575

<https://www.phoenixcontact.com/us/products/2986575>

## Output data

Relay: Enabling current paths (13/14, 23/24)

|                             |                                                    |
|-----------------------------|----------------------------------------------------|
| Output description          | 2 x N/O, undelayed                                 |
| Number of outputs           | 2                                                  |
| Contact switching type      | 2 enabling current paths                           |
| Contact material            | AgCuNi, + 0.2 µm Au                                |
| Switching voltage           | min. 15 V AC/DC<br>max. 250 V AC/DC                |
| Switching power             | min. 75 mW                                         |
| Inrush current              | max. 5 A                                           |
| Switching capacity          | 5 A (24 V (DC13))<br>5 A (230 V (AC15))            |
| Limiting continuous current | 5 A                                                |
| Sq. Total current           | 50 A <sup>2</sup> (observe derating)               |
| Switching frequency         | max. 0.5 Hz                                        |
| Mechanical service life     | 10 <sup>7</sup> cycles                             |
| Output fuse                 | 10 A gL/gG (High demand)<br>4 A gL/gG (Low demand) |

Relay: 31/32

|                             |                             |
|-----------------------------|-----------------------------|
| Output description          | 1 N/C signal contact        |
| Number of outputs           | 1                           |
| Contact switching type      | 1 confirmation current path |
| Contact material            | AgCuNi, + 0.2 µm Au         |
| Switching power             | min. 75 mW                  |
| Inrush current              | max. 100 mA                 |
| Limiting continuous current | 100 mA                      |
| Mechanical service life     | 10 <sup>7</sup> cycles      |
| Output fuse                 | 150 mA (fast-blow)          |

## Connection data

Connection technology

|           |     |
|-----------|-----|
| pluggable | yes |
|-----------|-----|

Conductor connection

|                                  |                                             |
|----------------------------------|---------------------------------------------|
| Connection method                | Screw connection                            |
| Conductor cross-section rigid    | 0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |
| Conductor cross-section flexible | 0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |
| Conductor cross-section AWG      | 24 ... 12                                   |
| Stripping length                 | 7 mm                                        |
| Screw thread                     | M3                                          |
| Tightening torque                | 0.5 Nm ... 0.6 Nm                           |

# PSR-SCP- 24DC/FSP2/2X1/1X2 - Coupling relay



2986575

<https://www.phoenixcontact.com/us/products/2986575>

## Signaling

|                           |                |
|---------------------------|----------------|
| Operating voltage display | 1 x yellow LED |
|---------------------------|----------------|

## Dimensions

|        |          |
|--------|----------|
| Width  | 17.5 mm  |
| Height | 99 mm    |
| Depth  | 114.5 mm |

## Material specifications

|                  |                   |
|------------------|-------------------|
| Color (Housing)  | yellow (RAL 1018) |
| Housing material | PA                |

## Characteristics

### Safety data

|                            |   |
|----------------------------|---|
| Stop category (EN 60204-1) | 0 |
|----------------------------|---|

### Safety data: EN ISO 13849

|                        |                                                                                |
|------------------------|--------------------------------------------------------------------------------|
| Performance level (PL) | c (Diagnostic coverage (DC) of the control unit at A1/A2 must be $\geq 90\%$ ) |
|------------------------|--------------------------------------------------------------------------------|

### Safety data: EN 50156

|                              |   |
|------------------------------|---|
| Safety Integrity Level (SIL) | 2 |
|------------------------------|---|

### Safety data: IEC 61508 - High demand

|                              |                                                                                                            |
|------------------------------|------------------------------------------------------------------------------------------------------------|
| Safety Integrity Level (SIL) | 2 (max. 10% of the entire SIL; diagnostic coverage (DC) of the control unit at A1/A2 must be $\geq 90\%$ ) |
|------------------------------|------------------------------------------------------------------------------------------------------------|

### Safety data: IEC 61508 - Low demand

|                              |                                                                                                            |
|------------------------------|------------------------------------------------------------------------------------------------------------|
| Safety Integrity Level (SIL) | 2 (max. 10% of the entire SIL; diagnostic coverage (DC) of the control unit at A1/A2 must be $\geq 90\%$ ) |
|------------------------------|------------------------------------------------------------------------------------------------------------|

### Safety data: EN IEC 62061

|                              |                                                                                                            |
|------------------------------|------------------------------------------------------------------------------------------------------------|
| Safety Integrity Level (SIL) | 1 (max. 10% of the entire SIL; diagnostic coverage (DC) of the control unit at A1/A2 must be $\geq 90\%$ ) |
|------------------------------|------------------------------------------------------------------------------------------------------------|

## Environmental and real-life conditions

### Ambient conditions

|                                                |                                                     |
|------------------------------------------------|-----------------------------------------------------|
| Degree of protection                           | IP20                                                |
| Min. degree of protection of inst. location    | IP54                                                |
| Ambient temperature (operation)                | -20 °C ... 55 °C (observe derating)                 |
| Ambient temperature (storage/transport)        | -40 °C ... 70 °C                                    |
| Maximum altitude                               | $\leq 2000$ m (Above sea level)                     |
| Max. permissible humidity (storage/transport)  | 75 % (on average, 85% infrequently, non-condensing) |
| Max. permissible relative humidity (operation) | 75 % (on average, 85% infrequently, non-condensing) |
| Shock                                          | 15g                                                 |
| Vibration (operation)                          | 10 Hz ... 150 Hz, 2g                                |

# PSR-SCP- 24DC/FSP2/2X1/1X2 - Coupling relay



2986575

<https://www.phoenixcontact.com/us/products/2986575>

## Approvals

CE

|                |              |
|----------------|--------------|
| Identification | CE-compliant |
|----------------|--------------|

## Mounting

|                   |                   |
|-------------------|-------------------|
| Mounting type     | DIN rail mounting |
| Mounting position | any               |

# PSR-SCP- 24DC/FSP2/2X1/1X2 - Coupling relay




2986575

<https://www.phoenixcontact.com/us/products/2986575>

## Drawings

Circuit diagram



Block diagram


# PSR-SCP- 24DC/FSP2/2X1/1X2 - Coupling relay

2986575

<https://www.phoenixcontact.com/us/products/2986575>




Circuit diagram



Single-channel connection with integration of the confirmation current path

Circuit diagram



Two-channel connection with integration of the confirmation current path

# PSR-SCP- 24DC/FSP2/2X1/1X2 - Coupling relay



2986575

<https://www.phoenixcontact.com/us/products/2986575>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2986575>



**DNV GL**

Approval ID: TAA00002UC



**cULus Listed**

Approval ID: E140324



**Functional Safety**

Approval ID: 968/EZ 365.11/24

# PSR-SCP- 24DC/FSP2/2X1/1X2 - Coupling relay



2986575

<https://www.phoenixcontact.com/us/products/2986575>

## Classifications

### ECLASS

|                   |          |
|-------------------|----------|
| ECLASS-13.0       | 27371819 |
| ECLASS-15.0       | 27371819 |
| ECLASS-15.0 ASSET | 27250101 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC001449 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39122200 |
|-------------|----------|

# PSR-SCP- 24DC/FSP2/2X1/1X2 - Coupling relay



2986575

<https://www.phoenixcontact.com/us/products/2986575>

## Environmental product compliance

### EU RoHS

|                                         |              |
|-----------------------------------------|--------------|
| Fulfills EU RoHS substance requirements | Yes          |
| Exemption                               | 7(a), 7(c)-I |

### China RoHS

|                                        |                                                                                                                                                                                                                                   |
|----------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-50                                                                                                                                                                                                                           |
|                                        | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |                                      |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1)                 |
| SCIP                                | ab3cdbf8-f1d5-4306-8965-a56b3a796f13 |

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)