


UKH 95-PE/N - Installation protective conductor terminal block



3009176

<https://www.phoenixcontact.com/us/products/3009176>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Installation protective conductor terminal block, Screws with hexagonal socket, PE/N block, consisting of a green-yellow protective conductor terminal block and a blue terminal block with screw bridge, nom. voltage: 1000 V, nominal current: 232 A, Screw connection, Rated cross section: 95 mm², cross section: 25 mm² - 95 mm², mounting type: NS 35/7,5, NS 35/15, NS 32, color: green-yellow

Your advantages

- Reliable cable connection is ensured by three-point centering of the conductor in the prismatic sleeve base
- Low contact resistance of the contact surface due to ribbing
- Screw locking by means of spring-loaded elements in the clamping part

Commercial data

Item number	3009176
Packing unit	5 pc
Minimum order quantity	1 pc
Sales key	BE13
Product key	BE1321
GTIN	4017918091705
Weight per piece (including packing)	592.6 g
Weight per piece (excluding packing)	593.2 g
Customs tariff number	85369010
Country of origin	PL

UKH 95-PE/N - Installation protective conductor terminal block



3009176

<https://www.phoenixcontact.com/us/products/3009176>

Technical data

Notes

General	Screws with hexagonal socket
---------	------------------------------

Product properties

Product type	Ground terminal block
Number of connections	2
Number of rows	1
Potentials	1

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated surge voltage	8 kV
Maximum power dissipation for nominal condition	7.54 W

Connection data

PEN function	yes
Grounding foot	Yes
Number of connections per level	2
Nominal cross section	95 mm ²
Rated cross section AWG	3/0

Level 1 above 1 below 1

Connection method	Screw connection
Screw thread	M8
Note	Please observe the current carrying capacity of the DIN rails.
Tightening torque	15 ... 20 Nm
Stripping length	33 mm
Connection in acc. with standard	IEC 60947-7-2
Conductor cross-section rigid	25 mm ² ... 95 mm ²
Cross section AWG	2 ... 3/0 (converted acc. to IEC)
Conductor cross-section flexible	35 mm ² ... 95 mm ²
Conductor cross-section, flexible [AWG]	1/0 ... 3/0 (converted acc. to IEC)
Conductor cross-section flexible (ferrule without plastic sleeve)	35 mm ² ... 95 mm ²
Flexible conductor cross-section (ferrule with plastic sleeve)	35 mm ² ... 95 mm ²
Nominal cross section	95 mm ²
Nominal current	232 A
Maximum load current	232 A (with 95 mm ² conductor cross-section)
Nominal voltage	1000 V
Note	Note: Product releases, connection cross sections and notes on connecting aluminum cables can be found in the download area.


UKH 95-PE/N - Installation protective conductor terminal block



3009176

<https://www.phoenixcontact.com/us/products/3009176>

Dimensions

Dimensional drawing	
Width	50 mm
Height	83 mm
Depth on NS 32	104 mm
Depth on NS 35/7,5	99 mm
Depth on NS 35/15	106.5 mm

Material specifications

Color	green-yellow
Flammability rating according to UL 94	V0
Insulating material group	I
Insulating material	PA

Mechanical properties

General

Terminal block mounting	15 Nm ... 20 Nm (PE foot with mounting screw, M8)
-------------------------	---

Mechanical data

Open side panel	No
-----------------	----

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

Standards and regulations

Connection in acc. with standard	IEC 60947-7-2
----------------------------------	---------------

Mounting

Mounting type	NS 35/7,5 NS 35/15 NS 32
Terminal block mounting	15 Nm ... 20 Nm (PE foot with mounting screw, M8)


UKH 95-PE/N - Installation protective conductor terminal block

3009176

<https://www.phoenixcontact.com/us/products/3009176>

Drawings

Dimensional drawing



UKH 95-PE/N - Installation protective conductor terminal block



3009176

<https://www.phoenixcontact.com/us/products/3009176>

Approvals

📄 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3009176>



EAC

Approval ID: KZ7500651131219505

UKH 95-PE/N - Installation protective conductor terminal block



3009176

<https://www.phoenixcontact.com/us/products/3009176>

Classifications

ECLASS

ECLASS-13.0	27250110
ECLASS-15.0	27250110

ETIM

ETIM 10.0	EC001329
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

UKH 95-PE/N - Installation protective conductor terminal block



3009176

<https://www.phoenixcontact.com/us/products/3009176>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com