

# PSBJ 6-T BU - Test plug strip

3070329

<https://www.phoenixcontact.com/us/products/3070329>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Test plug strip, number of positions: 1, color: blue

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 3070329       |
| Packing unit                         | 10 pc         |
| Minimum order quantity               | 10 pc         |
| Sales key                            | BE19          |
| Product key                          | BE1Z3X        |
| GTIN                                 | 4046356870887 |
| Weight per piece (including packing) | 5.62 g        |
| Weight per piece (excluding packing) | 5.62 g        |
| Customs tariff number                | 85366990      |
| Country of origin                    | PL            |

# PSBJ 6-T BU - Test plug strip

3070329

<https://www.phoenixcontact.com/us/products/3070329>



## Technical data


### Product properties

|                     |                          |
|---------------------|--------------------------|
| Product type        | Test plug terminal block |
| Number of positions | 1                        |

### Connection data

|                    |                  |
|--------------------|------------------|
| Test socket torque | M3               |
| Connection method  | Screw connection |

### Dimensions

|                     |                                                                                    |
|---------------------|------------------------------------------------------------------------------------|
| Dimensional drawing |  |
| Width               | 6 mm                                                                               |
| Height              | 6 mm                                                                               |
| Depth               | 15 mm                                                                              |
| Screw thread        | M3                                                                                 |

### Material specifications

|       |                 |
|-------|-----------------|
| Color | blue (RAL 5015) |
|-------|-----------------|

### Environmental and real-life conditions

#### Ambient conditions

|                                          |                                                                           |
|------------------------------------------|---------------------------------------------------------------------------|
| Ambient temperature (operation)          | -60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)       |
| Ambient temperature (storage/transport)  | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly)           | -5 °C ... 70 °C                                                           |
| Ambient temperature (actuation)          | -5 °C ... 70 °C                                                           |
| Permissible humidity (storage/transport) | 30 % ... 70 %                                                             |

### Mounting

|              |    |
|--------------|----|
| Screw thread | M3 |
|--------------|----|


# PSBJ 6-T BU - Test plug strip

3070329

<https://www.phoenixcontact.com/us/products/3070329>



## Drawings



# PSBJ 6-T BU - Test plug strip



3070329

<https://www.phoenixcontact.com/us/products/3070329>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27250304 |
| ECLASS-15.0 | 27250304 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC002555 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 20122000 |
|-------------|----------|

## Environmental product compliance

### EU RoHS

|                                         |      |
|-----------------------------------------|------|
| Fulfills EU RoHS substance requirements | Yes  |
| Exemption                               | 6(c) |

### China RoHS

|                                        |                                                                                                                                                                                                                                   |
|----------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-50                                                                                                                                                                                                                           |
|                                        | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |                                      |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1)                 |
| SCIP                                | 5bcd796f-5fb3-418c-aa8c-16dc928d1bf1 |

### EF3.1 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 0.082 kg CO2e |
|---------|---------------|